

UTC UNISONIC TECHNOLOGIES CO., LTD

TL084

LINEAR INTEGRATED CIRCUIT

LOW NOISE QUAD J-FET **OPERATIONAL AMPLIFIER**


DESCRIPTION

The UTC TL084 is a high speed J-FET input quad operational amplifier. It incorporates well matched, high voltage J-FET and bipolar transistors on a monolithic integrated circuit. The device features high slew rates, low input bias and offset current, and low offset voltage temperature coefficient.

FEATURES

- * Low Power Consumption
- * Wide Common-Mode (Up To V_{CC} +) and Differential Voltage Range
- * Low Input Bias and Offset Current
- * Low Noise eN = $15^{nV}/\sqrt{H_z}$ (typ.)
- * Output Short-Circuit Protection
- * High Input Impedance J-FET Input Stage
- * Low Harmonic Distortion: 0.01% (typ.)
- * Internal Frequency Compensation
- * Latch up Free Operation

ORDERING INFORMATION



Ordering Number		Daakaaa	Dealing	
Lead Free	Halogen Free	Package	Packing	
TL084L-D14-T	TL084G-D14-T	DIP-14	Tube	
TL084L-S14-R	TL084G-S14-R	SOP-14	Tape Reel	
TL084L-P14-R	TL084G-P14-R	TSSOP-14	Tape Reel	


TL084G- <u>D14-T</u>	(1)Packing Type (2)Package Type (3)Green Package	(1) T: Tube, R: Tape Reel (2) D14: DIP-14, S14: SOP-14, P14: TSSOP-14 (3) G: Halogen Free and Lead Free, L: Lead Free	

MARKING


DIP-14	SOP-14 / TSSOP-14		
14 13 12 11 10 8 > Date Code UTC □□□□□ L: Lead Free TL084 → G: Halogen Free UTC □□□□ Lot Code 1 2 3 4 5 6 7	14 13 12 11 10 9 8 Date Code UTC □□□□ L: Lead Free TL084 → G: Halogen Free ● □□ → Lot Code 1 2 3 4 5 6 7		

TL084

■ PIN CONFIGURATIONS



SCHEMATIC DIAGRAM



■ ABSOLUTE MAXIMUM RATINGS (T_A=25°C, unless otherwise specified)

PARAMETER		SYMBOL	RATING	UNIT
PAKAMETER		STIMBOL	RATING	UNIT
Supply Voltage (Note 2)		V _{CC}	±18	V
Input Voltage (Note 3)		V _{IN}	±15	V
Differential Input Voltage (Note 4)		V _{I(DIFF)}	±30	V
Power Dissipation	DIP-14		800	mW
	SOP-14	PD	580	mW
	TSSOP-14		460	mW
Output Short-Circuit Duration (Note 5)			Infinite	
Operating Temperature		T _{OPR}	-40 ~ +125 (Note 6)	
Storage Temperature		T _{STG}	-65 ~ +150	°C

Notes: 1. Absolute maximum ratings are those values beyond which the device could be permanently damaged. Absolute maximum ratings are stress ratings only and functional device operation is not implied.

 All voltage values, except differential voltage, are with respect to the zero reference level (ground) of the supply voltages where the zero reference level is the midpoint between V_{CC}- and V_{CC}+.

3. The magnitude of the input voltage must never exceed the magnitude of the supply voltage or 15 volts, whichever is less.

4. Differential voltages are at the non-inverting input terminal with respect to the inverting input terminal.

5. The output may be shorted to ground or to either supply. Temperature and/or supply voltages must be limited to ensure that the dissipation rating is not exceeded.

6. It is guarantee by design, not 100% be tested.


■ ELECTRICAL CHARACTERISTICS (V_{CC}=±15V, T_A=25°C, unless otherwise specified)


PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Input Offset Voltage	V _{I(OFF)}	$R_{S} \leq 10 k\Omega$, V_{CM} =0V		5	15	mV
Temperature Coefficient of Input Offset Voltage	$\Delta V_{\text{I(OFF)}}$	Rs=50Ω		10		µV/∘C
Input Offset Current (Note)	I _{I(OFF)}	V _{CM} =0V		5	200	рА
Input Bias Current (Note1)	I _{I(BIAS)}	V _{CM} =0V		30	400	pА
Input Common Mode Voltage	V _{I(CM)}		±10	-12~+15		V
	V _{O(SW)}	$T_A=25^{\circ}C, R_L=2k\Omega,$	±10	±12		V
Output Voltago Swing		$T_A=25^{\circ}C, R_L=10k\Omega$	±12	±13.5		V
Output Voltage Swing		$T_{MIN} \le T_A \le T_{MAX}, R_L = 2k\Omega$	±10			V
		$T_{MIN} \le T_A \le T_{MAX}, R_L = 10 k\Omega$	±12			V
Large Signal Voltage Gain	Gv	$R_L \ge 2k\Omega$, V_{OUT} =±10V	25	150		V/mV
Gain Bandwidth Product	GBw			1		MHz
Input Resistance	R _{IN}			10 ¹²		Ω
Common Mode Rejection Ratio	CMR	$R_{S} \leq 10 k\Omega$	70	100		dB
Supply Voltage Rejection Ratio	SVR	$R_{S} \leq 10 k\Omega$	70	100		dB
Supply Current	Icc	No Load		1.4	2.8	mA
Channel Separation	V01/V02	G _V =100		120		dB
Slew Rate	SR	V _{IN} =10V, R _L =2kΩ, C _L =100pF, unity gain	2.0			V/µs
Rise Time	t _R			0.1		μs
Overshoot Factor	K _{ov}	V_{IN} =20mV, R _L =2k Ω , C _L =100pF, unity gain		10		%
Equivalent Input Noise Voltage	eN	R _S =100Ω, f=1KHz		25		nV/√H _z

Note: The Input bias currents are junction leakage currents, which approximately double for every 10°C increase in the junction temperature.



PARAMETER MEASUREMENT INFORMATION





Gain-of-10 Inverting Amplifier




TL084

Maximum Peak-to

Maximum Peak-to Peak Output Voltage vs Frequency Maximum Peak-to Peak Output Voltage (V) ±15 R_L=2kΩ V_{cc}=±15V T_A=25°¢ ±12.5 ±10 _=±10V V_{\sim} ±7.5 ±5 :±5' 'cc ±2.5 0 100 1K 10K 100K 1M 10M Frequency (Hz) Maximum Peak-to Peak Output Voltage vs Supply Voltage Maximum Peak-to Peak Output Voltage (V) ±15 R_L=10kΩ T_A=25°C ±12.5 ±10 ±7.5 ±5 ±2.5 0 2 0 4 6 8 10 12 14 16 Supply Voltage (±V) Supply Current Per Amplifier vs Supply Voltage 2 1.8 1.6 Supply Current (mA) 1.4 1.2 1 0.8

TYPICAL CHARACTERISTICS





T_A=25°C

No signal

14 16

No load

10 12

Supply Voltage (±V)

0.6

0.4

0.2

0 0 2 4 6 8

UTC assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all UTC products described or contained herein. UTC products are not designed for use in life support appliances, devices or systems where malfunction of these products can be reasonably expected to result in personal injury. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. UTC reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

