



REV.	ECN NO.	REVISED	DATE

NOTE:

1.MATERIAL:

a.HOUSING:ABS TRANSPARENT

b.SPRING:MUSIC WIRE





(SURFACE PLATING: NI100u"~120u")

SEE ORDERING INFORMATION

2.ELECTRIC:

a.DIELECTRIC VOLTAGE: 270V AC ONE SEC LEVEL

b.OPERATING TEMPERATURE: -40° C~ +80° C



ORDERING INFORMATION

BH-AA-B\*\*\*010

电池盒

电池型号

SMT 180° TYPE

PLATING:

A-Au1U"

J-Ni100U"~120U"

K-Sn100U"~120U"

MATERIAL:

1A-PP BLACK

1B-PA66 BLACK

2A-PPA BROWN

2B-PPA BLACK

3A-PPS BROWN

3B-PPS BLACK

4A-LCP WHITE

4B-LCP BLACK

5B-ABS TRANSPARENT



UNLESS OTHERWISE SPECIFIED TOLERANCES		<b>MYOUNG 美阳</b> <a href="http://www.meiyangdz.com">www.meiyangdz.com</a>	
DECIMALS: X :±0.30 X.X :±0.25 X.XX :±0.20 X.XXX :±0.10	ANGLES: X :±1° X.X :±0.5°	DSND YangFeng	DATE 2020-12-09
WEIGHT:		CHKD ZhouRuicai	DATE 2020-12-09
SHEET 1 OF 1		APVD XueShunyong	DATE 2020-12-09
SCALE:		SIZE: A4	VIEW:
UNIT: mm		REV.: A/1	OBJECT: MY
TITLE: 电池盒BH-AA-2J 半剥透明 (线长250mm)		PART NO.: BH-AA-B5BJ010	
DRAW NO.:WD-CP-0109			

2	SPRING	2	MUSIC WIRE, 0.5MM	NI-Plating
1	HOUSING	1	ABS	TRANSPARENT
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR