

RABS206G

FAST RECOVERY BRIDGE RECTIFIERS



<b>VOLTAGE:</b> 600 Volts	<b>CURRENT:</b> 2.0 Amper	<b>ABS</b>	<b>Marking &amp; Schematic diagram</b>
---------------------------	---------------------------	------------	--

**FEATURES**

- Glass passivated die construction
- low forward voltage drop
- High surge current capability
- Good soft recovery features are good for EMC
- Plastic material-UL flammability 94V-0

**MECHANICAL DATA**

- **Case:** ABS
- **Terminals:** Plated Leads Solderable per MIL-STD-202, Method 208
- **Polarity:** As Marked on Case
- **Mounting Position:** Any
- **Lead Free:** For RoHS / Lead Free Version
- **Weight:** App. 0.1 grams ( 0.0035 ounce)

**TYPICAL APPLICATIONS**

- For use in switch power supply ,high frequency inverters , PD power supply applications

**Remark:**

- ①. NH=niuhang trademark
- ②. FF=Product line code,According to actual changes  
YWW=Data code,According to actual changes
- ③. RABS206G=Modle
- ④. "- +"=Polarity mark

Single phase, half wave, 60Hz, resistive or inductive load. For capacitive load, derate current by 20%

**Maximum Ratings (Ratings at 25°C ambient temperature unless otherwise specified )**

Parameter	Symbol	RABS206G	Unit
Maximum Repetitive Peak Reverse Voltage	$V_{RRM}$	600	V
Maximum RMS Voltag	$V_{RMS}$	420	V
Maximum DC Blocking Voltage	$V_{DC}$	600	V
Maximum Average Forward Rectified Current @ TC=100°C (see fig.1)	$I_{F(AV)}$	2	A
Peak Forward Surge Current 8.3ms Single Half Sine-wave Superimposed On Rate Load (JEDEC Method)	$I_{FSM}$	70	A
Current Squared Time Per Diode (t<8.3ms)	$I^2t$	20.34	A <sup>2</sup> sec

**Electrical Characteristcs (Ratings at 25°C ambient temperature unless otherwise specified )**

Parameter	Test Conditions	Symbol	RABS206G			Unit
			Min.	Typ.	Max.	
Maximum Forward Voltage Per Diode (Note 1)	Ta=25°C IF= 2.0 A	$V_{FM}$	--	--	0.98	V
Maximum DC Reverse Current at Rated DC Blocking Voltage (Note 1)	Ta=25°C VR= 600 V	$I_{RRM}$	--	--	5	uA
	Ta=125°C VR= 600 V		--	--	500	
Maximum Reverse Recovery Time (Note 3)	IF=0.5A, IR=1.0A, IRR=0.25A	$T_{RR}$	--	--	350	nS
Typical Junction Capacitance Per Diode	4V,1MHz	$C_J$	--	40	--	pF

**Thermal Characteristcs (Ratings at 25°C ambient temperature unless otherwise specified )**

Parameter	Symbol	RABS206G		Unit
Operating Junction Temperature Range	$T_J$	-55	to 150	°C
Storage Temperature Range	$T_{STD}$	-55	to 150	°C
Typical thermal resistance (Note 2)	$R_{\theta JA}$	62.5		°C/W
	$R_{\theta JL}$	25.0		

- Notes:
1. Pulse test: 300 μs pulse width, 1% duty cycle
  2. Mounted on glass epoxy PC board with 4x1.5"x1.5" (3.81x3.81 cm) copper pad.

RABS206G

FAST RECOVERY BRIDGE RECTIFIERS



RATING AND CHARACTERISTIC CURVES




Fig.1-FORWARD CURRENT DERATING CURVE




Fig.2- TYPICAL INSTANTANEOUS FORWARD




Fig.3- TYPICAL REVERSE CHARACTERISTICS




Fig.4- TYPICAL JUNCTION CAPACITANCE




Fig.5-MAX. NON-REPETITIVE SURGE CURRENT




Fig.6- TEST CIRCUIT DIAGRAM AND REVERSE RECOVERY TIME CHARACTERISTIC

RABS206G

FAST RECOVERY BRIDGE RECTIFIERS



OUTLINE DRAWINGS				ABS																																																																																												
				<table border="1"> <thead> <tr> <th colspan="7">OUTLINE DIMENSIONS</th> </tr> <tr> <th rowspan="2">Dim.</th> <th colspan="3">Milimeters</th> <th colspan="3">Inches</th> </tr> <tr> <th>Min.</th> <th>Typ.</th> <th>Max.</th> <th>Min.</th> <th>Typ.</th> <th>Max.</th> </tr> </thead> <tbody> <tr> <td>A</td> <td>4.300</td> <td>-</td> <td>4.500</td> <td>0.169</td> <td>-</td> <td>0.177</td> </tr> <tr> <td>B</td> <td>6.000</td> <td>-</td> <td>6.500</td> <td>0.236</td> <td>-</td> <td>0.252</td> </tr> <tr> <td>C</td> <td>3.800</td> <td>-</td> <td>4.400</td> <td>0.150</td> <td>-</td> <td>0.173</td> </tr> <tr> <td>D</td> <td>4.900</td> <td>-</td> <td>5.400</td> <td>0.193</td> <td>-</td> <td>0.213</td> </tr> <tr> <td>E</td> <td>0.550</td> <td>-</td> <td>0.850</td> <td>0.022</td> <td>-</td> <td>0.033</td> </tr> <tr> <td>F</td> <td>1.220</td> <td>-</td> <td>1.450</td> <td>0.048</td> <td>-</td> <td>0.056</td> </tr> <tr> <td>G</td> <td>-</td> <td>-</td> <td>1.500</td> <td>-</td> <td>-</td> <td>0.059</td> </tr> <tr> <td>H</td> <td>0.300</td> <td>-</td> <td>0.800</td> <td>0.012</td> <td>-</td> <td>0.031</td> </tr> <tr> <td>J</td> <td>0.150</td> <td>-</td> <td>0.250</td> <td>0.006</td> <td>-</td> <td>0.010</td> </tr> <tr> <td>K</td> <td>0.030</td> <td>-</td> <td>0.150</td> <td>0.001</td> <td>-</td> <td>0.006</td> </tr> </tbody> </table>			OUTLINE DIMENSIONS							Dim.	Milimeters			Inches			Min.	Typ.	Max.	Min.	Typ.	Max.	A	4.300	-	4.500	0.169	-	0.177	B	6.000	-	6.500	0.236	-	0.252	C	3.800	-	4.400	0.150	-	0.173	D	4.900	-	5.400	0.193	-	0.213	E	0.550	-	0.850	0.022	-	0.033	F	1.220	-	1.450	0.048	-	0.056	G	-	-	1.500	-	-	0.059	H	0.300	-	0.800	0.012	-	0.031	J	0.150	-	0.250	0.006	-	0.010	K	0.030	-	0.150	0.001	-	0.006
OUTLINE DIMENSIONS																																																																																																
Dim.	Milimeters			Inches																																																																																												
	Min.	Typ.	Max.	Min.	Typ.	Max.																																																																																										
A	4.300	-	4.500	0.169	-	0.177																																																																																										
B	6.000	-	6.500	0.236	-	0.252																																																																																										
C	3.800	-	4.400	0.150	-	0.173																																																																																										
D	4.900	-	5.400	0.193	-	0.213																																																																																										
E	0.550	-	0.850	0.022	-	0.033																																																																																										
F	1.220	-	1.450	0.048	-	0.056																																																																																										
G	-	-	1.500	-	-	0.059																																																																																										
H	0.300	-	0.800	0.012	-	0.031																																																																																										
J	0.150	-	0.250	0.006	-	0.010																																																																																										
K	0.030	-	0.150	0.001	-	0.006																																																																																										
RECOMMENDED LAYOUT DRAWINGS				ABS																																																																																												
				<table border="1"> <thead> <tr> <th colspan="7">RECOMMENDED LAYOUT DIMENSIONS</th> </tr> <tr> <th rowspan="2">Dim.</th> <th colspan="3">Milimeters</th> <th colspan="3">Inches</th> </tr> <tr> <th>Min.</th> <th>Typ.</th> <th>Max.</th> <th>Min.</th> <th>Typ.</th> <th>Max.</th> </tr> </thead> <tbody> <tr> <td>A</td> <td>-</td> <td>6.200</td> <td>-</td> <td>-</td> <td>0.244</td> <td>-</td> </tr> <tr> <td>B</td> <td>-</td> <td>4.000</td> <td>-</td> <td>-</td> <td>0.157</td> <td>-</td> </tr> <tr> <td>C</td> <td>-</td> <td>2.000</td> <td>-</td> <td>-</td> <td>0.079</td> <td>-</td> </tr> <tr> <td>D</td> <td>-</td> <td>1.000</td> <td>-</td> <td>-</td> <td>0.039</td> <td>-</td> </tr> </tbody> </table>			RECOMMENDED LAYOUT DIMENSIONS							Dim.	Milimeters			Inches			Min.	Typ.	Max.	Min.	Typ.	Max.	A	-	6.200	-	-	0.244	-	B	-	4.000	-	-	0.157	-	C	-	2.000	-	-	0.079	-	D	-	1.000	-	-	0.039	-																																										
RECOMMENDED LAYOUT DIMENSIONS																																																																																																
Dim.	Milimeters			Inches																																																																																												
	Min.	Typ.	Max.	Min.	Typ.	Max.																																																																																										
A	-	6.200	-	-	0.244	-																																																																																										
B	-	4.000	-	-	0.157	-																																																																																										
C	-	2.000	-	-	0.079	-																																																																																										
D	-	1.000	-	-	0.039	-																																																																																										
PACKING INFORMATION				ABS																																																																																												
Package Method	Reel Size (mm)	Quantity (pcs/reel)	Inner Box Size LxWxH(mm)	Quantity (pcs/Inner Box)	Outer Carton Size LxWxH(mm)	Quantity (pcs/carton)																																																																																										
Tape Reel	Φ330	5000	340x340x40	10000	360x360x260	60000																																																																																										

**RABS206G**


**FAST RECOVERY BRIDGE RECTIFIERS**



**Recommended wave soldering condition**

Product	Peak Temperature	Soldering Time
Pb-free devices	260 +0/-5 °C	5 +1/-1 seconds

**Recommended temperature profile for IR reflow**



Profile feature	Sn-Pb eutectic Assembly	Pb-free Assembly
Average ramp-up rate (Tsmmax to Tp)	3°C/second max.	3°C/second max.
Preheat -Temperature Min(TS min) -Temperature Max(TS max) -Time(ts min to ts max)	100°C 150°C 60-120 seconds	150°C 200°C 60-180 seconds
Time maintained above: -Temperature (TL) - Time (tL)	183°C 60-150 seconds	217°C 60-150 seconds
Peak Temperature(TP)	240 +0/-5 °C	260 +0/-5 °C
Time within 5°C of actual peak temperature(tp)	10-30 seconds	20-40 seconds
Ramp down rate	6°C/second max.	6°C/second max.
Time 25 °C to peak temperature	6 minutes max.	8 minutes max.

Note : All temperatures refer to topside of the package, measured on the package body surface.

## RABS206G

## FAST RECOVERY BRIDGE RECTIFIERS

**Disclaimer**

- Reproducing and modifying information of the document is prohibited without permission from niuhang Electronics co., LTD
- Niuhan Electronics co., LTD. reserves the rights to make changes of the content herein the document anytime without notification.
- Niuhan Electronics co., LTD. disclaims any and all liability arising out of the application or use of any product including damages incidentally and consequentially occurred.
- Niuhan Electronics co., LTD. does not assume any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.
- Applications shown on the herein document are examples of standard use and operation. Customers are responsible in comprehending the suitable use in particular applications. Niuhan Electronics co., LTD. makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.
- The products shown herein are not designed and authorized for equipments requiring high level of reliability or relating to human life and for any applications concerning life-saving or life-sustaining, such as medical instruments, transportation equipment, aerospace machinery et cetera. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Niuhan Electronics co., LTD. for any damages resulting from such improper use or sale.
- When the appearance of the product and chip size does not change, in order to product the customer quality, change the internal structure and the production process Niuhan can not notify