MSKSEMI美森科













PLED

ESD

TVS

TSS

MOV

1N4001W-1N4007W

Product specification





FEATURES

- Ideal for surface mount applications
- Easy pick and place
- Built-in strain relief
- High surge current capability

MECHANICAL DATA

- Case: Molded plastic
- Epoxy: UL 94V-0 rate flame retardant
- Terminals: Solder plated, solderable per MIL-STD-202F, method 208 guranteed
- Polarity: Color band denotes cathode end
- Mounting position: Any

Reference News

PACKAGE OUTLINE	Circuit	PINNING		
0		PIN	DESCRIPTION	
SOD-123FL		1	Cathode	
		2	Anode	

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 2.5 °C ambient temperature unless otherwise specified.

Single phase half-wave 60 Hz, resistive or inductive load, for capacitive load current derate by 20%.

Parameter		SYMBOLS	1N4001W A1	1N4002W A2	1N4003W A3	1N4004W A4	1N4005W A5	1N4006W A6	1N4007W A7	UNITS
Maximum repetitive peak reverse v	oltage	Vrrm	50	100	200	400	600	800	1000	VOLTS
Maximum RMS voltage		Vrms	35	70	140	280	420	560	700	VOLTS
Maximum DC blocking voltage		Vdc	50	100	200	400	600	800	1000	VOLTS
Maximum average forward rectified Ta=65 C (NOTE 1)	current at	l(AV)				1.0		·	·	Amp
Peak forward surge current										
8.3ms single half sine-wave superimposed on rated		IFSM	25.0						Amps	
load (JEDEC Method) T∟=25 C										
Maximum instantaneous forward vol	tage at 1.0A	Vf	1.0			Volts				
Maximum DC reverse current at	Ta=25℃		10.0							
rated DC blocking voltage	Ta=125℃	IR	50.0					μA		
Typical junction capacitance (NOTE	E 2)	J				4				pF
Typical thermal resistance (NOTE 3	3)	R9ja				180				K/W
Operating junction and storage tem	perature range	Tj,Tstg			-65	i to +150				°C

Note: 1. Averaged over any 20ms period.

2.Measured at 1MHz and applied reverse voltage of 4.0V D.C.

3. Thermal resistance from junction to ambient at 0.375" (9.5mm)lead length, P.C.B. mounted



ELECTRICAL CHARACTERISTICS CURVE




FIG.2-TYPICAL FORWARD CURRENT DERATING CURVE






FIG.4-MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT








Copyright© Msksemi Incorporated




PACKAGE MECHANICAL DATA



Dimensions in millimeters

Suggested Pad Layout



Note:

1.Controlling dimension: in millimeters.

2.General tolerance:±0.05mm.

3. The pad layout is for reference purposes only.

REEL SPECIFICATION

P/N	PKG	QTY
1N4001W-1N4007W	SOD-123FL	3000

Attention

■ Any and all MSKSEMI Semiconductor products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your MSKSEMI Semiconductor representative nearest you before using any MSKSEMI Semiconductor products described or contained herein in such applications.

MSKSEMI Semiconductor assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all MSKSEMI Semiconductor products described or contained herein.

Specifications of any and all MSKSEMI Semiconductor products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.

MSKSEMI Semiconductor. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with someprobability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits anderror prevention circuits for safedesign, redundant design, and structural design.

■ In the event that any or all MSKSEMI Semiconductor products (including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from theauthorities concerned in accordance with the above law.

■ No part of this publication may be reproduced or transmitted in any form or by any means, electronic or

mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of MSKSEMI Semiconductor.

Information (including circuit diagrams and circuit parameters) herein is for example only ; it is not guaranteed for volume production. MSKSEMI Semiconductor believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements intellectual property rights or other rights of third parties.

Any and all information described or contained herein are subject to change without notice due to

product/technology improvement, etc. Whendesigning equipment, referto the "Delivery Specification" for the MSKSEMI Semiconductor productthat you intend to use.