

5MHz, 287µA, RRIO, Zero-Drift Operational Amplifiers

Features

- Low offset Voltage: 10µV (Max.)
- Zero Drift: 0.05µV/°C (Max.)
- Low Quiescent Current: 287µA/ch
- Gain Bandwidth Product: 5.0MHz
- Single Supply: 1.8V ~ 5.5V
- Dual Supply: ±0.9V ~ ±2.75V
- Slew Rate: 4.0V/µs
- Rail-to-Rail Input and Output (RRIO)
- Unity Gain Stable
- EMI/RFI Filtered Inputs
- Extended Temperature Ranges
 From -40°C to +125°C
- Small Packaging
 COS8628 available in SOT23-5/SOP-8
 COS8629 available in SOP-8/MSOP-8
 COS8630 available in SOP14/TSSOP14

Applications

- Sensor Conditioning
- Temperature Measurements
- Transducers
- Test Equipment
- Medical Instrumentation
- Battery Powered Instruments
- A/D converters

General Description

The COS8628 (single), COS8629 (dual) and COS8630 (quad) are low-noise, zero-drift, precision operational amplifiers operated on 1.8 to 5.5 single supply or $\pm 0.9V$ to $\pm 2.75V$ dual supplies. COS862x family use chopper stabilized technique to provide very low offset voltage (less than 10µV maximum) and near zero drift over temperature. Despite their low quiescent current, the COS862x family provides excellent overall performance and versatility. They have both rail-to-rail input and output range. The output voltage swing extends to within 1mV of each rail, providing the maximum output dynamic range with excellent overdrive recovery. COS862x family is unity gain stable and has a gain bandwidth product of 5.0MHz (typical). These features make the devices an ideal choice for driving high-precision, analog- to-digital converters (ADCs) or buffering the output of high-resolution, digital-to-analog converters (DACs).


Rev1.0

Copyright@2020 Cosine Nanoelectronics Inc. All rights reserved

The information provided here is believed to be accurate and reliable. Cosine Nanoelectronics assumes no reliability for inaccuracies and omissions. Specifications described and contained here are subjected to change without notice on the purpose of improving the design and performance. All of this information described herein should not be implied or granted for any third party.



1. Pin Configuration and Functions



Pin Functions

Name	me Description Note	
+Vs	Positive power supply	A bypass capacitor of 0.1μ F as close to the part as possible should be placed between power supply pins or between supply pins and ground.
-Vs	-Vs Negative power supply If it is not connected to ground, bypass it with capacitor of 0.1µF as close to the part as post	
-IN	Negative input	Inverting input of the amplifier. Voltage range of this pin can go from -Vs -0.3V to +Vs + 0.3V.
+IN	Positive input	Non-inverting input of the amplifier. This pin has the same voltage range as –IN.
OUT	Output	The output voltage range extends to within millivolts of each supply rail.
NC	No connection	

2. Ordering Information

Channel	Model	Order Number	Package	Package Option	Marking Information
1	0059639	COS8628TR	SOT23-5	Tape and Reel, 3000	COS8628
I	1 COS8628	COS8628SR	SOP-8	Tape and Reel, 4000	COS8628SR
	COS8629SRA			COS8629SR	
2	COS8629	COS8629SRB	SOP-8	Tape and Reel, 4000	COS8629SR
		COS8629SRC			COS8629SR
4	4 COS8630 -	COS8630SR	SOP14	Tape and Reel, 2500	COS8630SR
4		COS8630TR	TSSOP14	Tape and Reel, 2500	COS8630TR



3. Product Specification

3.1 Absolute Maximum Ratings⁽¹⁾

Parameter	Rating	Units
Power Supply: +Vs to -Vs	6	V
Input Voltage	-Vs -0.5V to +Vs + 0.5V	V
Input Current ⁽²⁾	±10	mA
Storage Temperature Range	-65 to 150	°C
Junction Temperature	150	°C
Operating Temperature Range	-40 to 125	°C
ESD Susceptibility, HBM	2000	V

(1) Stresses exceeding the absolute maximum ratings may damage the device. The device may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only.

(2) Input terminals are diode-clamped to the power-supply rails. Input signals that can swing more than 0.5V beyond the supply rails should be current-limited to 10mA or less.

3.2 Thermal Data

Parameter	Rating	Unit
Package Thermal Resistance	190 (SOT23-5) 206 (MSOP8) 155 (SOP8) 105 (TSSOP14) 82 (SOP14)	°C/W

3.3 Recommended Operating Conditions

Parameter	Rating	Unit
DC Supply Voltage	1.8V ~ 5.5V	V
Input common-mode voltage range	-Vs ~ +Vs	V
Operating ambient temperature	-40 to +85	°C



3.4 Electrical Characteristics

(+V_S=+5V, -V_S=0, V_{CM}=V_S/2, T_A=+25°C, R_L=10k Ω to V_S/2, unless otherwise noted)

Parameter	Symbol	Conditions	Min	Тур	Мах	Unit
Input Characteristics	1					1
		COS862xA		±2	±10	
Input Offset Voltage	Vos	COS862xB			±20	μV
		COS862xC			±100	
Input Offset Voltage Drift	ΔV _{OS} /ΔT	-40 to 125°C		±0.005	±0.05	µV/°C
Input Bias Current	Ів			±30		pА
Input Offset Current	los			±30		pА
Common-Mode Voltage Range	V _{CM}	V _S = 5.5V	-0.1		5.6	V
Common-Mode Rejection Ratio	CMRR	V _{CM} =0.1V to 4.9V		120		dB
Open-Loop Voltage Gain	AOL	Vo=0.2V to 4.8V		145		dB
Output Characteristics						
Output Voltage Swing from Beil		$R_L=100k\Omega$		1		mV
Output Voltage Swing from Rail		R _L =10kΩ		8		mV
Short-Circuit Current	I _{SR}	Sourcing		21		mA
Short-Circuit Current	I _{sк}	Sinking		22		mA
Power Supply						
Operating Voltage Range			1.8		5.5	V
Power Supply Rejection Ratio	PSRR	$V_{\rm S}$ = 1.8V to 5.5V		120		dB
Quiescent Current / Amplifier	IQ	V _S = 5.0V		287		μA
Dynamic Performance						
Gain Bandwidth Product	GBWP	G=+1		5.0		MHz
Slew Rate	SR	G = +1 , 2V Output Step		4.0		V/µs
Noise Performance						
Voltage Noise Density	en	f=1kHz		20		nV/√H:



4.0 Application Notes

Driving Capacitive Loads

Driving large capacitive loads can cause stability problems for voltage feedback op amps. As the load capacitance increases, the feedback loop's phase margin decreases, and the closed loop bandwidth is reduced. This produces gain peaking in the frequency response, with overshoot and ringing in the step response. A unity gain buffer (G = +1) is the most sensitive to capacitive loads, but all gains show the same general behavior.

When driving large capacitive loads with these op amps (e.g., > 100 pF when G = +1), a small series resistor at the output (R_{ISO} in Figure 1) improves the feedback loop's phase margin (stability) by making the output load resistive at higher frequencies. It does not, however, improve the bandwidth.

To select R_{ISO} , check the frequency response peaking (or step response overshoot) on the bench. If the response is reasonable, you do not need R_{ISO} . Otherwise, start R_{ISO} at 1 k Ω and modify its value until the response is reasonable.




Figure 1. Indirectly Driving Heavy Capacitive Load

An improvement circuit is shown in Figure 2. It provides DC accuracy as well as AC stability. R_F provides the DC accuracy by connecting the inverting signal with the output, C_F and R_{ISO} serve to counteract the loss of phase margin by feeding the high frequency component of the output signal back to the amplifier's inverting input, thereby preserving phase margin in the overall feedback loop.




Figure 2. Indirectly Driving Heavy Capacitive Load with DC Accuracy



For noninverting configuration, there are two others ways to increase the phase margin: (a) by increasing the amplifier's gain or (b) by placing a capacitor in parallel with the feedback resistor to counteract the parasitic capacitance associated with inverting node, as shown in Figure 3.




Figure 3. Adding a Feedback Capacitor in the Noninverting Configuration

Power-Supply Bypassing and Layout

The COS862x operates from a single +1.8V to +5.5V supply or dual ±0.9V to ±2.75V supplies. For single-supply operation, bypass the power supply +Vs with a 0.1 μ F ceramic capacitor which should be placed close to the +Vs pin. For dual-supply operation, both the +Vs and the -Vs supplies should be bypassed to ground with separate 0.1 μ F ceramic capacitors. 2.2 μ F tantalum capacitor can be added for better performance.

The length of the current path is directly proportional to the magnitude of parasitic inductances and thus the high frequency impedance of the path. High speed currents in an inductive ground return create an unwanted voltage noise. Broad ground plane areas will reduce the parasitic inductance. Thus a ground plane layer is important for high speed circuit design.

Typical Application Circuits

Differential Amplifier

The circuit shown in Figure 4 performs the differential function. If the resistors ratios are equal (R₄ / R₃ = R₂ / R₁), then $V_{OUT} = (V_{IP} - V_{IN}) \times R_2 / R_1 + V_{REF}$.






Figure 4. Differential Amplifier

Low Pass Active Filter

When receiving low-level signals, limiting the bandwidth of the incoming signals into the system is often required. The simplest way to establish this limited bandwidth is to place an RC filter at the noninverting terminal of the amplifier. If even more attenuation is needed, a multiple pole filter is required. The Sallen-Key filter can be used for this task, as Figure 5. For best results, the amplifier should have a bandwidth that is 8 to 10 times the filter frequency bandwidth. Failure to follow this guideline can result in reduction of phase margin. The large values of feedback resistors can couple with parasitic capacitance and cause undesired effects such as ringing or oscillation in high-speed amplifiers. Keep resistors value as low as possible and consistent with output loading consideration.






Figure 5. Two-Pole Low-Pass Sallen-Key Active Filter



5. Package Information


5.1 SOT23-5 (Package Outline Dimensions)





Symbol		nsions imeters	Dimensions In Inches	
	Min	Max	Min	Max
A	1.050	1.250	0.041	0.049
A1	0.000	0.100	0.000	0.004
A2	1.050	1.150	0.041	0.045
b	0.300	0.400	0.012	0.016
С	0.100	0.200	0.004	0.008
D	2.820	3.020	0.111	0.119
E	1.500	1.700	0.059	0.067
E1	2.650	2.950	0.104	0.116
е	0.950)TYP	0.03	7TYP
e1	1.800	2.000	0.071	0.079
Ĺ	0.700	REF	0.028REF	
L1	0.300	0.600	0.012	0.024
θ	0°	8°	0°	8°


5.2 SOP8 (Package Outline Dimensions)



Symbol		nsions meters	Dimensions In Inches		
	Min	Max	Min	Max	
А	1.350	1.750	0.053	0.069	
A1	0.100	0.250	0.004	0.010	
A2	1.350	1.550	0.053	0.061	
В	0.330	0.510	0.013	0.020	
С	0.190	0.250	0.007	0.010	
D	4.780	5.000	0.188	0.197	
E	3.800	4.000	0.150	0.157	
E1	5.800	6.300	0.228	0.248	
е	1.27	DTYP	0.050TYP		
L	0.400	1.270	0.016	0.050	
θ	0°	8°	0°	8°	




5.3 MSOP8 (Package Outline Dimensions)



A2 A

Symbol		nsions meters	Dimensions In Inches		
	Min	Max	Min	Max	
A	0.800	1.200	0.031	0.047	
A1	0.000	0.200	0.000	0.008	
A2	0.760	0.970	0.030	0.038	
b	0.30	TYP	0.012	12 TYP	
С	0.15	TYP	0.006 TYP		
D	2.900	3.100	0.114	0.122	
е	0.65	TYP	0.026	STYP	
E	2.900	3.100	0.114	0.122	
E1	4.700	5.100	0.185	0.201	
L	0.410	0.650	0.016	0.026	
θ	0°	6°	0°	6°	

5.4 SOP14 (Package Outline Dimensions)




R1		
RI		Sy
+	θ	
→ h -		

Symbol	Dimensions In Millimeters				
-	MIN	NOM	MAX		
A	1.35	1.60	1.75		
A1	0.10	0.15	0.25		
A2	1.25	1.45	1.65		
A3	0.55	0.65	0.75		
b	0.36		0.49		
b1	0.35	0.40	0.45		
С	0.16		0.25		
c1	0.15	0.20	0.25		
D	8.53	8.63	8.73		
E	5.80	6.00	6.20		
E1	3.80	3.90	4.00		
e		1.27 BS0	0		
L	0.45	0.60	0.80		
L1		1.04 RE			
L2		0.25 BS0	2		
R	0.07				
R1	0.07				
h	0.30	0.40	0.50		
θ	0°		8°		
0 1	6°	8°	10°		
θ2	6°	8°	10°		
03	5°	7 °	9°		
04	5°	7 °	9°		



5.5 TSSOP14 (Package Outline Dimensions)



Symbol	Dimensions In Millimeters					
	MIN	MIN NOM				
A		—	1.20			
A1	0.05	—	0.15			
A2	0.90	1.00	1.05			
A3	0.34	0.44	0.54			
b	0.20	—	0.28			
b1	0.20	0.22	0.24			
С	0.10		0.19			
c1	0.10	0.13	0.15			
D	4.86	4.96	5.06			
E	6.20	6.40	6.60			
E1	4.30	4.40	4.50			
е		0.65 BSC	2			
L	0.45	0.60	0.75			
L1		1.00 REF	Ŧ			
L2		0.25 BSC)			
R	0.09	-	—			
R1	0.09	·				
S	0.20					
θ1	0°	_	8°			
θ2	10°	12°	14°			
θ3	10°	12°	14°			

6. Related Parts

Part Number	Description
COS6041/2/4	24kHz, 0.5µA, RRIO Op Amps, 1.8 to 5.5V Supply
COS1347/2347/4347	350kHz, 15µA, RRIO Op Amps, 1.8 to 5.5V Supply
COS6001/2/4	1.5MHz, 50µA, RRIO Op Amps, 1.8 to 5.5V Supply
COS1314/2314/4314	3MHz, 150µA, RRIO Op Amps, 1.8 to 5.5V Supply
COS821/2/4	5MHz, 300µA, RRIO Op Amps, 1.8 to 5.5V Supply
COS1374/2374/4374	7MHz, 500µA, RRIO Op Amps, 1.8 to 5.5V Supply
COS721/2/4	10MHz, 650µA, RRIO Op Amps, 2.1 to 5.5V Supply
COS1333/2333/4333	0.35MHz, 18µA, RRIO Op Amps, 1.8 to 5.5V Supply, Zero Drift, Vos<20µV