



MBR20150CT THRU MBR20200CT

Reverse Voltage - 150 to 200 Volts Forward Current - 20.0 Ampere

SCHOTTKY BARRIER RECTIFIER

Features

- ◆ The plastic package carries Underwriters Laboratory Flammability Classification 94V-0
- ◆ Construction utilizes void-free molded plastic technique
- ◆ Low reverse leakage
- ◆ High forward surge current capability
- ◆ High temperature soldering guaranteed: 250°C, 0.25"(6.35mm) from case for 10 seconds

Mechanical Data

Case : JEDEC TO-220AB Molded plastic body

Terminals : Solder plated, solderable per MIL-STD-750, Method 2026


Polarity : Polarity symbol marking on body

Mounting Position : Any

Weight : 0.080 ounce, 2.24 grams

TO-220AB

ROHS
COMPLIANT



Dimensions in inches and (millimeters)

Maximum Ratings And Electrical Characteristics

Ratings at 25°C ambient temperature unless otherwise specified.

Single phase half-wave 60Hz, resistive or inductive load, for capacitive load current derate by 20%.

Parameter	SYMBOLS	MDD MBR 20150CT	MDD MBR 20200CT	UNITS
Marking Code				
Maximum repetitive peak reverse voltage	V _{RRM}	150	200	V
Maximum RMS voltage	V _{RMS}	135	140	V
Maximum DC blocking voltage	V _{DC}	150	200	V
Maximum average forward rectified current (see fig.1)	I _(AV)	20.0		A
Peak forward surge current 8.3ms single half sine-wave superimposed on rated load (JEDEC Method)	I _{FSM}	150		A
Maximum instantaneous forward voltage at 10.0A	V _F	0.95		V
Maximum DC reverse current T _A =25°C at rated DC blocking voltage T _A =100°C	I _R	0.2 50.0		mA
Typical thermal resistance (NOTE 2)	R _{θJC}	1.5		°C/W
Operating junction temperature range	T _J	-55 to +150		°C
storage temperature range	T _{STG}	-55 to +150		°C

Note: 1. Measured at 1MHz and applied reverse voltage of 4.0V D.C.

2. Thermal resistance from junction to case.



MBR20150CT THRU MBR2020CT

Reverse Voltage - 150 to 200 Volts Forward Current - 20.0 Ampere

Ratings And Characteristic Curves

FIG.1 TYPICAL FORWARD CHARACTERISTICS




FIG.2 FORWARD DERATING CURVE






FIG.3 TYPICAL REVERSE CHARACTERISTICS



The curve above is for reference only.