

Transient Voltage Suppressors for ESD protection

DESCRIPTION

The SLPESDU3311D5N is designed to protect voltage sensitive components from ESD and transient voltage events. Excellent clamping capability, low leakage, and fast response time, make these parts ideal for ESD protection on designs where board space is at a premium.

This device has been specifically designed to protect sensitive components which are connected to data and transmission lines from overvoltage caused by ESD (electrostatic discharge), CDE (Cable Discharge Events), and EFT (electrical fast transients).


ORDERING INFORMATION

- ♦ Device: SLPESDU3311D5N
- ♦ Package: SOD-523

♦ Marking: 3C

- ♦ Material: Halogen free
- ♦ Packing: Tape & Reel
- ♦Quantity per reel: 3,000pcs

PIN CONFIGURATION



FEATURES

♦IEC61000-4-2 (ESD) ±30kV (Air),

±30kV (Contact)

- ♦ Peak power dissipation: 60W (8/20µs)
- ♦Protects one I/O line
- ♦Low clamping voltage
- ♦Working voltages : 3.3V
- ♦Low leakage current

MACHANICAL DATA

- ♦ SOD-523 package
- ♦ Flammability Rating: UL 94V-0
- ✦High temperature soldering guaranteed: 260℃/10s
- \diamond Packaging: Tape and Reel
- ♦Reel size: 7 inch

APPLICATIONS

- ♦ Cell Phone Handsets and Accessories
- Microprocessor based equipment
- ♦ Personal Digital Assistants (PDA's)
- Notebooks, Desktops, and Servers
- ♦Portable Instrumentation
- ♦Networking and Telecom
- \diamond Serial and Parallel Ports
- \diamond Peripherals

PACKAGE OUTLINE





ABSOLUTE MAXIMUM RATING							
Symbol	Parameter	Value	Units				
V _{ESD}	ESD per IEC 61000-4-2 (Contact) ESD per IEC 61000-4-2 (Air)	±30 ±30	kV				
P _{PP}	Peak Pulse Power (8/20µs)	60	W				
T _{OPT}	Operating Temperature	-40~150	°C				
T _{STG}	Storage Temperature	-40~150	°C				

ELECTRICAL CHARACTERISTICS (Tamb=25°C)								
Symbol	Parameter	Test Condition	Min	Тур	Max	Units		
V _{RWM}	Reverse Working Voltage				3.3	V		
V_{BR}	Reverse Breakdown Voltage	I _T = 1mA	3.6			V		
I _R	Reverse Leakage Current	V _{RWM} = 3.3V			1.0	μA		
V _c	Clamping Voltage	I _{PP} = 1A, t _p = 8/20μs			6.5	V		
Vc	Clamping Voltage	$I_{PPmax} = 5A$, $t_p = 8/20\mu s$			12.0	V		
V _{CTLP}	TLP Clamping Voltage	I_{PP} = 16A IEC61000-4-2 Level 4 equivalent (\pm 8kV Contact, \pm 15kV Air)		9		V		
CJ	Junction Capacitance	V _R = 0V, f = 1MHz			16.5	pF		



ELECTRICAL CHARACTERISTICS CURVE

