



SS22F THRU SS2200F

Reverse Voltage - 20 to 200 Volts Forward Current - 2.0 Ampere



SURFACE MOUNT SCHOTTKY BARRIER RECTIFIER

Features

- ◆ The plastic package carries Underwriters Laboratory Flammability Classification 94V-0
- ◆ For surface mounted applications
- ◆ Metal silicon junction,majority carrier conduction
- ◆ Low power loss,high efficiency
- ◆ Built-in strain relief,ideal for automated placement
- ◆ High forward surge current capability
- ◆ High temperature soldering guaranteed:
260 °C/10 seconds at terminals

SMAF

ROHS
COMPLIANT



Mechanical Data

Case^{*}: JEDEC SMAF molded plastic body

Terminals^{*}: Solderable per MIL-STD-750,Method 2026

Polarity^{*}: Color band denotes cathode end

Mounting Position^{*}: Any

Weight : 0.00095 ounce, 0.027grams

Dimensions in inches and (millimeters)

Maximum Ratings And Electrical Characteristics

Ratings at 25°C ambient temperature unless otherwise specified.

Single phase half-wave 60Hz,resistive or inductive load,for capacitive load current derate by 20%.

Parameter	SYMBOLS	MDD SS22F	MDD SS23F	MDD SS24F	MDD SS25F	MDD SS26F	MDD SS28F	MDD SS210F	MDD SS2150F	MDD SS2200F	UNITS
Marking Code											
Maximum repetitive peak reverse voltage	V _{RRM}	20	30	40	50	60	80	100	150	200	V
Maximum RMS voltage	V _{RMS}	14	21	28	35	42	56	70	105	140	V
Maximum DC blocking voltage	V _{DC}	20	30	40	50	60	80	100	150	200	V
Maximum average forward rectified current	I _(AV)										A
Peak forward surge current 8.3ms single half sine-wave superimposed onrated load (JEDEC Method)	I _{FSM}										A
Maximum instantaneous forward voltage at 2.0A	V _F			0.55		0.70		0.85		0.95	V
Maximum DC reverse current T _A =25°C at rated DCblocking voltage T _A =100°C	I _R				0.5				0.3		mA
					5.0				3.0		
Typical junction capacitance (NOTE 1)	C _J		160				80				pF
Typical thermal resistance (NOTE 2)	R _{θJA}					80.0					°C/W
Operating junction temperature range	T _J		- 5 5 t o + 1 2 5				- 5 5 t o + 1 5 0				°C
Storage temperature range	T _{STG}					- 5 5 t o + 1 5 0					°C

Note:1.Measured at 1MHz and applied reverse voltage of 4.0V D.C.

2.P.C.B. mounted with 2.0"x2.0"(5.0x5.0cm) copper pad areas



SS22F THRU SS2200F

Reverse Voltage - 20 to 200 Volts Forward Current - 2.0 Ampere

Typical Characteristics

Fig.1 Forward Current Derating Curve




Fig.2 Typical Reverse Characteristics




Fig.3 Typical Forward Characteristic




Fig.4 Typical Junction Capacitance




Fig.5 Maximum Non-Repetitive Peak Forward Surge Current





Fig.6- Typical Transient Thermal Impedance




The curve above is for reference only.



SS22F THRU SS2200F

Reverse Voltage - 20 to 200 Volts Forward Current - 2.0 Ampere

Packing information




Item	Symbol	Tolerance	SMAF
Carrier width	A	0.1	2.80
Carrier length	B	0.1	4.75
Carrier depth	C	0.1	1.42
Sprocket hole	d	0.05	1.50
7" Reel outside diameter	D	2.0	178.00
7" Reel inner diameter	D1	min	54.40
Feed hole diameter	D2	0.5	13.00
Sprocket hole position	E	0.1	1.75
Punch hole position	F	0.1	5.05
Punch hole pitch	P	0.1	4.00
Sprocket hole pitch	P0	0.1	4.00
Embossment center	P1	0.1	2.00
Overall tape thickness	T	0.1	0.30
Tape width	W	0.3	8.00
Reel width	W1	1.0	12.30

Note: Devices are packed in accordance with EIA standard RS-481-A and specifications listed above.

Reel packing

PACKAGE	REEL SIZE	REEL (pcs)	COMPONENT SPACING (m/m)	BOX (pcs)	INNER BOX (m/m)	REEL DIA, (m/m)	CARTON SIZE (m/m)	CARTON (pcs)	APPROX. GROSS WEIGHT (kg)
SMAF	7"	3,000	4.0	6,000	210*208*203	178	400*265*400	120,000	10.0

Suggested Pad Layout



Symbol	Unit (mm)	Unit (inch)
A	1.8	0.071
B	1.6	0.063
C	3.8	0.150
D	2.2	0.087
E	5.4	0.213