

PRODUCT-DETAILS

SH201-C25NA

SH201-C25NA Miniature Circuit Breaker - 1+NP - C - 25 A



General Information

Extended Product Type	SH201-C25NA
Product ID	2CDS211103R0254
EAN	4016779630917
Catalog Description	SH201-C25NA Miniature Circuit Breaker - 1+NP - C - 25 A
Long Description	<p>Compact Home SH200 miniature circuit breakers are current limiting. They have two different tripping mechanisms, the delayed thermal tripping mechanism for overload protection and the electromechanic tripping mechanism for short circuit protection.</p> <p>They are available in different characteristics (B,C), configurations (1P,1P+N,2P,3P,3P+N,4P), breaking capacities (up to 6 kA at 230/400 V AC) and rated currents (up to 40 A). All MCBs of the product range SH200 comply with IEC/EN 60898-1, allowing the use for residential applications.</p>

Technical

Standards	IEC/EN 60898-1
Tripping Characteristic	C
Rated Operational Voltage	acc. to IEC 60898-1 230 V AC
Operational Voltage	Maximum (Incl. Tolerance) 253 V AC Minimum 12 V AC
Rated Insulation Voltage (U _i)	acc. to IEC/EN 60664-1 440 V
Rated Impulse Withstand Voltage (U _{imp})	4 kV at 2000 m 5 kV at Sea Level 6.2 kV

Dielectric Test Voltage	50/60 Hz, 1 min: 2 kV
Input Voltage Type	AC
Rated Current (I _n)	25 A
Rated Short-Circuit Capacity	(AC) 6 kA (230 / 400 V AC) 10 kA (230 V AC) 6 kA
Rated Conditional Short-Circuit Current (I _{nc})	(230 V) 10 kA (400 V) 10 kA
Rated Frequency (f)	50 / 60 Hz
Power Loss	6.4 W at Rated Operating Conditions per Pole 3.2 W
Power Supply Connection	Arbitrary
Contact Position Indication	ON / OFF
Energy Limiting Class	3
Electrical Endurance	20000 AC cycle
Mechanical Endurance	20000 cycle
Number of Poles	1+N
Number of Protected Poles	1
Overvoltage Category	III
Position of Neutral Terminals	Right
Tightening Torque	2 N·m
Actuator Type	Toggle
Screw Terminal Type	Cage Terminal
Actuator Marking	I / O
Actuator Material	Insulation Group II, Black, Sealable
Housing Material	Insulation Group II, RAL 7035
Mounting on DIN Rail	TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715
Mounting Position	any
Recommended Screw Driver	Pozidriv 2
Accessories Available	No
Connecting Capacity	Conductor 25 / 25 mm ² Flexible with Ferrule 0.75 ... 16 mm ² Flexible 0.75 ... 16 mm ² Rigid 0.75 ... 25 mm ² Stranded 0.75 ... 25 mm ²
Installation Size	acc. to DIN 43880 1
Terminal Type	Screw Terminals

Environmental

Ambient Air Temperature	Operation -25 ... +55 °C Storage -40 ... +70 °C
Reference Ambient Air Temperature	30 °C
Degree of Protection	IP20 Enclosure with Cover IP40
Pollution Degree	2
Environmental Conditions	28 cycles with 55 °C / 90-96 % and 25 °C / 95-100 %
Resistance to Vibrations acc. to IEC 60068-2-6	5g, 20 cycles at 5 ... 150 ... 5 Hz with load 0.8 In
Resistance to Shock acc. to IEC 60068-2-27	25g 2 shocks 13 ms

RoHS Status	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
RoHS Information	2CDK400030D0201
REACH Declaration	9AKK107492A1906
Environmental Information	2CDK400030D0201

Dimensions

Width in Number of Modular Spacings	2
Product Net Width	35 mm
Product Net Height	85 mm
Product Net Depth / Length	69 mm
Product Net Weight	0.25 kg
Pole Net Weight	0.125 kg
Built-In Depth (t ₂)	69 mm

Ordering

Minimum Order Quantity	1 piece
Package Level 1 Units	carton 5 piece
Package Level 1 Gross Weight	1.29 kg

Certificates and Declarations

Certification Agency	EN IEC
Declaration of Conformity - CE	2CDK400607D2703

Installation

Instructions and Manuals	2CDS207105P0001
--------------------------	-----------------

Popular Downloads

Data Sheet, Technical Information	2CSC400030D0202
-----------------------------------	-----------------

Classifications

ETIM 8	EC000042 - Miniature circuit breaker (MCB)
ETIM 9	EC000042 - Miniature circuit breaker (MCB)
EPLAN Catalog Tree	Electrical engineering / Protection devices / General
EPLAN Function Definition	NO contact / NO contact, 2 connection points / NO contact, leading 3N_4N Circuit breaker / Single circuit breaker / Circuit breaker 1_2
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Business
CN8	8536 20 10
UNSPSC	39121603

eClass	V11.0 : 27141901
IDEA Granular Category Code (IGCC)	4897 >> Miniature circuit breakers
Object Classification Code	F

Categories

Low Voltage Products and Systems → Modular DIN Rail Products → Miniature Circuit Breakers MCBs → Miniature Circuit Breakers MCBs

