

PRODUCT-DETAILS

## CAL5X-11 CAL5X-11 Auxiliary contact block



Extended Product Type	CAL5X-11
Product ID	1SBN019020R1011
EAN	3471522387929
Catalog Description	CAL5X-11 Auxiliary contact block
Long Description	CAL5X-11 is a 2-pole side mounted auxiliary contact block equipped with screw terminals and can be fitted on AX0680 ontactors and NX contactor relays. CAL5X auxiliary contact block can be clipped onto the right- and/or left-hand side of the contactors or the contactor relays and bears the corresponding function marking. CAL5X-11 is available with 1 N.O. and 1 N.C. instantaneous contacts for standard industrial environments.
Ordering	
	2 piece
Ordering Minimum Order Quantity Customs Tariff Number	2 piece 85030099
Minimum Order Quantity	
Minimum Order Quantity Customs Tariff Number	85030099
Minimum Order Quantity Customs Tariff Number Product Main Type	85030099

Dimensions	
Product Net Width	12 mm
Product Net Depth / Length	60 mm
Product Net Height	74 mm
Product Net Weight	0.05 kg

Technical	
Maximum Electrical Switching Frequency	(AC-15) 1200 cycles per hou (DC-13) 900 cycles per hou
Maximum Mechanical Switching Frequency	3600 cycles per hou
Number of Auxiliary Contacts NC	1
Number of Auxiliary Contacts NO	1
Rated Insulation Voltage (U <sub>i</sub> )	acc. to IEC 60947-5-1 and VDE 0110 (Gr. C) 690 V
Rated Operational Current AC-15 (I <sub>e</sub> )	(690 V) 2 A (24 / 127 V) 6 A (220 / 240 V) 4 A (380 / 400 V) 3 A
Rated Operational Current DC-13 (I <sub>e</sub> )	(24 V) 6 A / 144 W (110 V) 0.55 A / 60 W (125 V) 0.55 A / 69 W (220 V) 0.30 A / 66 W (250 V) 0.30 A / 75 W (400 V) 2.8 A / 134 W (500 V) 1 A / 72 W
Rated Operational Voltage	Auxiliary Circuit 690 V Main Circuit 690 V
Rated Short-time Withstand Current Low Voltage (I <sub>cw</sub> )	for 0.1 s 140 A for 1 s 100 A
Suitable For	AX06 AX09 AX12 AX18 AX25 AX32 AX40 AX50 AX50 AX50 AX50 AX50 AX50 AX50 AX5
Terminal Type	Screw Terminals

Environmental	
Conventional Free-air Thermal Current (I <sub>th</sub> )	acc. to IEC 60947-5-1, O = 40 °C 16 A
RoHS Information	2CMT2021-006277
WEEE B2C / B2B	Business To Business
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Certificates and Declarations	
CB Certificate	CB_CN28662
CCC Certificate	CCC_2013010304656838

2023/08/23

Subject to change without notice

## CAL5X-11

CCS Certificate	CCS_GZ13T00025
CQC Certificate	CQC2013010304656838
cUL Certificate	UL-CA-L252354-45-61406102-5
Declaration of Conformity - CCC	2020980304001061
Declaration of Conformity - CE	1SBD250013U1000
EAC Certificate	EAC_RU C-DE ME77 B03562
UL Certificate	UL-US-L252354-15-61406102-5

Container Information	
Package Level 1 Units	2 piece
Package Level 1 Width	100 mm
Package Level 1 Depth / Length	106 mm
Package Level 1 Height	35 mm
Package Level 1 Gross Weight	0.12 kg
Package Level 1 EAN	3471522387929
Package Level 2 Units	120 piece
Package Level 2 Width	220 mm
Package Level 2 Depth / Length	380 mm
Package Level 2 Height	300 mm
Package Level 2 Gross Weight	7.2 kg

eClass	V11.0 : 27371302
E-Number (Finland)	3708080
ETIM 6	EC000041 - Auxiliary contact block
ETIM 7	EC000041 - Auxiliary contact block
ETIM 8	EC000041 - Auxiliary contact block
ETIM 9	EC000041 - Auxiliary contact block
IDEA Granular Category Code (IGCC)	4743 >> Auxiliary contact block
Object Classification Code	к
UNSPSC	39121522

## Categories

Low Voltage Products and Systems  $\rightarrow$  Control Products  $\rightarrow$  Contactors  $\rightarrow$  Block Contactors Accessories



4