

PRODUCT-DETAILS

# SKT160-80

## NATURAL TIE 80N 160MM OEM PACK




---

### General Information

Extended Product Type	SKT160-80
Product ID	7TCA300040R0002
EAN	5415022209976
Catalog Description	NATURAL TIE 80N 160MM OEM PACK
Long Description	Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F), Length of 160mm (6.30 Inches), Width of 2.5mm (0.098 Inch), Thickness of 1.1mm (0.043 Inch), Tensile Strength Rating of 80 Newtons (18 Pounds). Bulk Pack

---

### Ordering

EAN	5415022209976
UPC	753554016248
Country of Origin	Thailand (TH)
Selling Unit of Measure	each

---

### Dimensions

Product Net Width	0.0984 in 2.5 mm
Product Net Depth / Length	6.3 in 160 mm

---

### Container Information

Package Level 1 Units	1000 piece
Package Level 1 Width	9.45 in 240 mm
Package Level 1 Height	3.25 in 83 mm
Package Level 1 Depth / Length	11.81 in 300 mm
Package Level 2 Units	45000 piece
Package Level 2 Width	15.1 in 384 mm
Package Level 2 Height	14.2 in 361 mm
Package Level 2 Depth / Length	22.6 in 574 mm

## Additional Information

Application	For Temperatures up to 85 Degrees Celsius (185 F). The right cable tie for control panels and wiring harness applications.
Brand / Label	Spec-Kon
Bundle Diameter	0.059 to 1.57 in 1.5 to 40 mm
Color	Natural
Effective Date	20131129
Lock Type	Plastic Pawl
Material	Nylon/Polyamide 6.6
Product Name	OTHER PLASTIC ITEM
Product Type	General Purpose
RoHS Date	9AKK107991A8067
Special Functions	Cost effective and easy to install
Standards	UL E49405
Tensile Strength	18 lb 80 N
Thickness	0.043 in 1.1 mm

## Certificates and Declarations

Data Sheet, Technical Information	SKT160-80
Declaration of Conformity - CE	9AKK107492A9842

## Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
ETIM 8	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

## Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

