



DATA SHEET

BAT54CM

- ◇ High Conductance
- ◇ Low Current Leakage
- ◇ Small Outline Surface Mount Package
- ◇ RoHS compliant / Green EMC

Device	Device Marking
BAT54CM	KL3

Circuit Diagram



MAXIMUM RATINGS (Ta = 25 °C)


Symbol	Parameter	Value	Units
V _{RRM}	Peak Repetitive Reverse Voltage	30	V
V _{RWM}	Working Peak Reverse Voltage	30	V
V _{R(RMS)}	RMS Reverse Voltage	21	V
I _O	Average Forward Current	200	mA
I _{FSM}	Non-repetitive Peak Forward Surge Current @ t=8.3ms	600	mA
I _{FRM}	Repetitive Peak Forward Current @ t≤1s, δ≤0.5	300	mA
P _D	Power Dissipation	150	mW
R _{θJA}	Thermal Resistance from Junction to Ambient	667	°C/W
T _j	Junction Temperature	125	°C
T _{stg}	Storage Temperature	-55~+150	°C

ELECTRICAL CHARACTERISTICS (Ta = 25 °C)


Symbol	Parameter	Test Conditions	Min	Typ	Max	Units
V _(BR)	Reverse voltage	I _R =100 μ A	30			V
I _R	Reverse current	V _R =25V			2	uA
V _F	Forward voltage	I _F =0.1mA			0.24	V
		I _F =1mA			0.32	
		I _F =10mA			0.4	
		I _F =30mA			0.5	
		I _F =100mA			1	
C _{tot}	Total capacitance	V _R =1V, f=1.0MHz			10	pF
T _{rr}	Reverse recovery time	I _F = I _R =10mA, I _{R(REC)} =1mA			5	nS

TYPICAL CHARACTERISTICS


Forward Characteristics




Reverse Characteristics



Capacitance Characteristics



Power Derating Curve




ORDERING INFORMATION

Device	Package	Shipping	Tape wide	Emboss pitch	Tape specification	Notes
BAT54CM	SOT723	Tape & Reel 8000pcs /7" Reel	8mm	4mm	Conductive	


PACKAGE DIMENSIONS

Package outline : SOT723

Top view




Side view




SYMBOL	DIMENSIONS IN MILLIMETER	
	MIN	MAX
A	0.430	0.500
A1	0.000	0.050
b	0.170	0.270
b1	0.270	0.370
c	0.080	0.150
D	1.150	1.250
E	1.150	1.250
E1	0.750	0.850
e	0.800 TYP.	
θ	0°	7°

Front view



Soldering Pattern



Notice:

1. Lead plating: Pb free solder
2. Lead thickness includes solder plating
3. Lead frame: CAC-5
4. Other Tolerance: ±0.05
5. Dimensions are exclusive of Burrs, Mold Flash and Tie Bar extrusions
6. Unit: mm