



Features


- Epitaxial Planar Die Construction
- Ideal for Low Power Amplification and Switching

Ordering Information

- Shipping Qty:3000/7inch Tape& Reel



Circuit Diagram



Absolute Maximum Ratings NPN 5551 (Tamb=25°C unless otherwise specified)



| Symbol | Parameter | Value | Units |
|-----------------------------------|--|------------|-------|
| V _{CBO} | Collector-Base Voltage | 60 | V |
| V _{CEO} | Collector-Emitter Voltage | 40 | V |
| V _{EBO} | Emitter-Base Voltage | 6 | V |
| I _C | Collector Current -Continuous | 0.6 | A |
| P _C | Collector Power Dissipation | 0.2 | W |
| R _{θJA} | Thermal Resistance from Junction to Ambient | 625 | °C/W |
| T _J , T _{stg} | Operation Junction and Storage Temperature Range | -55 ~ +150 | °C |









Electrical Characteristics NPN 4401 (TA=25°C unless otherwise specified)

| Parameter | Symbol | Test conditions | Min | Max | Unit |
|--------------------------------------|----------------|---|------|------|---------|
| Collector-base breakdown voltage | $V_{(BR)CBO}$ | $I_C = 100 \mu A, I_E = 0$ | 60 | | V |
| Collector-emitter breakdown voltage | $V_{(BR)CEO}$ | $I_C = 1 mA, I_B = 0$ | 40 | | V |
| Emitter-base breakdown voltage | $V_{(BR)EBO}$ | $I_E = 100 \mu A, I_C = 0$ | 6 | | V |
| Collector cut-off current | I_{CBO} | $V_{CB} = 50 V, I_E = 0$ | | 0.1 | μA |
| Collector cut-off current | I_{CEO} | $V_{CE} = 35 V, I_B = 0$ | | 0.5 | μA |
| Emitter cut-off current | I_{EBO} | $V_{EB} = 5 V, I_C = 0$ | | 0.1 | μA |
| DC current gain | $h_{FE(1)}$ | $V_{CE} = 1 V, I_C = 0.1 mA$ | 20 | | |
| | $h_{FE(2)}$ | $V_{CE} = 1 V, I_C = 1 mA$ | 40 | | |
| | $h_{FE(3)}$ | $V_{CE} = 1 V, I_C = 10 mA$ | 80 | | |
| | $h_{FE(4)}$ | $V_{CE} = 1 V, I_C = 150 mA$ | 100 | 300 | |
| | $h_{FE(5)}$ | $V_{CE} = 2 V, I_C = 500 mA$ | 40 | | |
| Collector-emitter saturation voltage | $V_{CE(sat)1}$ | $I_C = 150 mA, I_B = 15 mA$ | | 0.4 | V |
| | $V_{CE(sat)2}$ | $I_C = 500 mA, I_B = 50 mA$ | | 0.75 | V |
| Base-emitter saturation voltage | $V_{BE(sat)1}$ | $I_C = 150 mA, I_B = 15 mA$ | 0.75 | 0.95 | V |
| | $V_{BE(sat)2}$ | $I_C = 500 mA, I_B = 50 mA$ | | 1.2 | V |
| Transition frequency | f_T | $V_{CE} = 10 V, I_C = 20 mA, f = 100 MHz$ | 250 | | MHz |
| Output capacitance | C_{ob} | $V_{CB} = 5 V, I_E = 0, f = 1 MHz$ | | 6.5 | pF |
| Delay time | t_d | $V_{CC} = 30 V,$ | | 15 | nS |
| Rise time | t_r | $V_{BE} = 2 V, I_C = 150 mA, I_{B1} = 15 mA$ | | 20 | nS |
| Storage time | t_s | $V_{CC} = 30 V, I_C = 150 mA, I_{B1} = -I_{B2} = 15 mA$ | | 225 | nS |
| Fall time | t_f | | | 30 | nS |


Typical Performance Characteristics (TA=25°C unless otherwise Specified)







Outline Drawing - SOT363 (unit: mm)



| SOT-363 | | |
|---------|------|------|
| Dim | Min | Max |
| A | 2.00 | 2.20 |
| B | 1.15 | 1.35 |
| C | 0.85 | 1.05 |
| D | 0.15 | 0.35 |
| E | 0.25 | 0.40 |
| G | 0.60 | 0.70 |
| H | 0.02 | 0.10 |
| J | 0.05 | 0.15 |
| K | 2.20 | 2.40 |

Mounting Pad Layout-SOT363 (unit: mm)

