




2.4 GHz low pass filter matched to BLUENRG-LP-LPS (BLUENRG-3x5Vx, BLUENRG-3x5Ax, BLUENRG-332xx) in QFN and CSP packages

Chip scale package on glass 6 bumps

Pin-out top diagram (top view - bumps down)



Features

- Integrated impedance matching to BLUENRG-LP-LPS (BLUENRG-3x5Vx, BLUENRG-3x5Ax, BLUENRG-332xx) in QFN and CSP packages
- 50 Ω nominal impedance on antenna side
- Deep rejection harmonics filter
- Low insertion loss
- Small footprint
- Low profile ≤ 630 μm after reflow
- High RF performances
- RF BOM and area reduction
- ECOPACK2 compliant component

Applications

- Bluetooth 5
- OpenThread
- Zigbee[®]
- IEEE 802.15.4
- Optimized for BLUENRG-LP-LPS (BLUENRG-3x5Vx, BLUENRG-3x5Ax, BLUENRG-332xx) in QFN and CSP packages

Product status link

MLPF-NRG-01D3

Description

The MLPF-NRG-01D3 integrates an impedance matching network and harmonics filter. The matching impedance network has been tailored to maximize the RF performances of BLUENRG-LP-LPS (BLUENRG-3x5Vx, BLUENRG-3x5Ax, BLUENRG-332xx) in QFN and CSP packages. This device uses STMicroelectronics IPD technology on non-conductive glass substrate which optimizes RF performances.



1 Characteristics

Table 1. Absolute ratings (T_{amb} = 25 °C)

Symbol	Parameter	Value	Unit
P _{IN}	Input power RF _{IN}	10	dBm
V _{ESD}	ESD ratings human body model (JESD22-A114-C), all I/O one at a time while others connected to GND	2000	V
T _{OP}	Maximum operating temperature	-40 to +105	°C

Table 2. Impedances (T_{amb} = 25 °C)

Symbol	Parameter		Unit		
		Min.	Тур.	Max.	Offic
Z _{IN}	STM32WBxx single-ended impedance	-	Matched to BLUENRG-LP-LPS (BLUENRG-3x5Vx, BLUENRG-3x5Ax, BLUENRG-332xx) in QFN and CSP packages	-	Ω
Z _{OUT}	Antenna impedance	-	50	-	Ω

Table 3. Electrical characteristics and RF performances (T_{amb} = 25 °C)

Symbol	Parameter		Value			Unit
Зуппоп			Min.	Тур.	Max.	O I III
f	Frequency range		2400		2500	MHz
IL	Insertion loss IS ₂₁ I			0.9	1.1	dB
RL _{IN}	Input return loss IS ₁₁	Input return loss IS ₁₁ I		13		dB
RLOUT	Output return loss IS ₂₂ I		12	14		dB
	$\begin{tabular}{lll} Attenuation at 2fo \\ (4800-5000) MHz \\ \hline \\ Attenuation at 3fo \\ (7200-7500) MHz \\ \hline \\ Attenuation at 4fo \\ (9600-10000) MHz \\ \hline \\ Attenuation at 5fo \\ (12000-12500) MHz \\ \hline \end{tabular}$		31	37		dB
Att			42	43		dB
All			38	40		dB
		32	34		dB	


DS14044 - Rev 3 page 2/13





1.1 RF measurement
















DS14044 - Rev 3 page 3/13







DS14044 - Rev 3 page 4/13



2 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions and product status are available at: www.st.com. ECOPACK is an ST trademark.

2.1 CSPG package information




Figure 9. CSPG package outline (bottom view - bumps up)

Table 4. CSPG 6 bumps mechanical data

	Dimensions					
Ref.	Millimeters					
	Min.	Тур.	Max.			
A	0.580	0.630	0.680			
A1	0.180	0.205	0.230			
A2	0.380	0.400	0.420			
b	0.230	0.255	0.280			
D	1.550	1.600	1.650			
D1		0.577				
D2		0.577				
E	0.950	1.000	1.050			
E1		0.500				
fD1		0.223				
fD2		0.223				
fE1		0.250				
fE2		0.250				

DS14044 - Rev 3 page 5/13







Table 5. Pad description top view (pads down)

Pad ref	Pad name	Description
A1	OUT	Antenna
A2	GND4	Ground
А3	IN	BLUENRG-LP-LPS (BLUENRG-3x5Vx, BLUENRG-3x5Ax, BLUENRG-332xx) in QFN and CSP packages
B1	GND3	Ground
B2	GND2	Ground
В3	GND1	Ground

Figure 12. Tape and reel outline



DS14044 - Rev 3 page 6/13



Table 6. Tape and reel mechanical data

	Dimensions					
Ref	Millimeters					
	Min	Тур	Max			
A0	1.06	1.09	1.12			
В0	1.66	1.69	1.72			
D0	1.40	1.50	1.60			
F	3.45	3.50	3.55			
K0	0.69	0.72	0.75			
P0	3.90	4.00	4.10			
P1	1.95	2.00	2.05			
P2	1.95	2.00	2.05			
W	7.90	8.00	8.30			

DS14044 - Rev 3 page 7/13



Recommendation on PCB assembly

3.1 Land pattern

Layout example using a QFN package for the BLUENRG-LP-LPS shipset.




Figure 13. PCB land pattern recommendations

Transmission line between MLPF and antenna is dimensioned to 50 ohms characteristic impedance.

Transmission line between STM32 and MLPF is dimensioned to 57 ohms characteristic impedance.

Theses transmission line characteristics impedances have to be followed as close as possible.

Moreover, lines physical dimensions will have to be tuned according to specific PCB stack up if different from the one presented in datasheet to keep expected characteristic impedance values.

Name Material Type Thickness Dk
Top Overlay
Top Solder Solder Resist Solder Mask 0.030mm 3.5

1 Top Layer Copper Signal 0.035mm
Dielectric 1 FR-4 Core 0.508mm 4.3

2 Bottom Layer Copper Signal 0.035mm
Bottom Overlay


Overlay
Overlay
Overlay

Figure 14. PCB stack-up recommendations

DS14044 - Rev 3 page 8/13



3.2 Stencil opening design



3.3 Solder paste

- 1. Halide-free flux qualification ROL0 according to ANSI/J-STD-004.
- 2. "No clean" solder paste is recommended.
- 3. Offers a high tack force to resist component movement during high speed.
- 4. Use solder paste with fine particles: powder particle size 20-38 μm.

3.4 Placement

- Manual positioning is not recommended.
- It is recommended to use the lead recognition capabilities of the placement system, not the outline centering
- 3. Standard tolerance of ±0.05 mm is recommended.
- 4. 1.0 N placement force is recommended. Too much placement force can lead to squeezed out solder paste and cause solder joints to short. Too low placement force can lead to insufficient contact between package and solder paste that could cause open solder joints or badly centered packages.
- 5. To improve the package placement accuracy, a bottom side optical control should be performed with a high resolution tool.
- 6. For assembly, a perfect supporting of the PCB (all the more on flexible PCB) is recommended during solder paste printing, pick and place and reflow soldering by using optimized tools.

3.5 PCB design preference

- 1. To control the solder paste amount, the closed via is recommended instead of open vias.
- 2. The position of tracks and open vias in the solder area should be well balanced. A symmetrical layout is recommended, to avoid any tilt phenomena caused by asymmetrical solder paste due to solder flow away.


DS14044 - Rev 3 page 9/13





3.6 Reflow profile

Figure 17. ST ECOPACK recommended soldering reflow profile for PCB mounting



Note: Minimize air convection currents in the reflow oven to avoid component movement.

Note: More information is available in the application note:

• AN2348 Flip-Chip: "Package description and recommendations for use"

DS14044 - Rev 3 page 10/13



4 Ordering information

Table 7. Ordering information

Order code	Marking	Package	Weight	Base qty.	Delivery mode
MLPF-NRG-01D3	UB	CSPG	1.82 mg	5000	Tape and reel

DS14044 - Rev 3 page 11/13



Revision history

Table 8. Document revision history

Date	Revision	Changes
29-Jul-2022	1	Initial release.
09-Aug-2022	2	Updated Figure 13 and Figure 14.
25-Nov-2022	3	Updated Section 3.1 Land pattern.

DS14044 - Rev 3 page 12/13



IMPORTANT NOTICE - READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgment.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2022 STMicroelectronics - All rights reserved

DS14044 - Rev 3 page 13/13