MMS006PP3 Datasheet

DC-20 GHz GaAs MMIC SP2T Non-Reflective Switch

Released May 2017





Contents

1	Revis	sion History	. 1
		Revision 1.0	
2		uct Overview	
		Applications	
	2.2	Key Features	. 2
3	Elect	rical Specifications	. 3
	3.1	Absolute Maximum Ratings	. 3
	3.2	Specified Electrical Performance	. 3
	3.3	Typical Performance Curves	. 3
	3.4	Control Voltages	. 5
	3.5	Example Driver Circuit	. 5
4	Pack	age Specification	. 6
	4.1	Package Outline Drawing	. 6
	4.2	Package Information	. 6
	4.3	Pin Descriptions	. 6
5	Hand	dling Recommendations	. 8
6	Evalu	uation Board Information	. 9
7	Orde	ering Information	10



1 Revision History

The revision history describes the changes that were implemented in the document. The changes are listed by revision, starting with the most current publication.

1.1 Revision **1.0**

Revision 1.0 was published in May 2017. It was the first publication of this document.




2 Product Overview

The MMS006PP3 is a DC-to-20 GHz, non-reflective gallium arsenide (GaAs) pseudomorphic high-electron-mobility transistor (pHEMT) single pole double throw (SPDT) monolithic microwave integrated circuit (MMIC) switch in a plastic leadless 3 mm \times 3 mm surface-mount package. The switch delivers over 40 dB of isolation across the DC-to-20 GHz band while maintaining a low insertion loss of less than 2.0 dB. Also available in die form as the MMS006AA, the RF ports are internally matched to 50 Ω , which allows for easy integration into multi-chip modules (MCMs).

The following illustration shows the primary functional diagram of the MMA006PP3 device.

Figure 1 • Functional Diagram



2.1 Applications

The MMS006PP3 device is designed for the following applications.

- Test instrumentation
- Military radar, radio, EW, and ECM applications
- General purpose microwave applications

2.2 Key Features

The following are key features of the MMS006PP3 device:

- Non-reflective topology
- Broadband performance: DC–20 GHz
- Fast switching: 10 ns
- Low insertion loss: 1.2 dB at 10 GHz
- Excellent isolation: 42 dB at 10 GHz
- Compact 16-lead plastic QFN package: 3 mm × 3 mm × 0.85 mm
- High input P1dB: 25 dBm
- High input IP3: 43 dBm



3 Electrical Specifications

This section details the electrical specifications of the MMS006PP3 device.

3.1 Absolute Maximum Ratings

The following table lists the absolute maximum ratings of the MMS006PP3 device.

Table 1 • Absolute Maximum Ratings

Parameter	Rating
Storage temperature	−65 °C to 150 °C
Operating temperature	–40 °C to 85 °C
Control voltage range (CTLA/CTLB)	0.5 V to -7.5 VDC
RF input power	30 dBm
Hot switching power	7 dBm
Channel temperature	150 °C
Thermal resistance (insertion loss path)	100 °C/W
Thermal resistance (terminated path)	180 °C/W
ESD sensitivity (HBM)	Class 1A

3.2 Specified Electrical Performance

The following table lists the specified electrical performance of the MMS006PP3 device at 25 °C, where V_{CONTROL} (CTLA/CTLB) is 0 V, –5 V. The system is 50 Ω .

Table 2 • Specified Electrical Performance

Parameter	Frequency	Min	Тур	Max	Unit
Operational frequency range		DC		20	GHz
Insertion loss (all states)	DC-20 GHz		2.0	2.25	dB
Return loss (on state)	DC-20 GHz		-10		dB
Isolation	DC-20 GHz	35	40		dB
TRISE, TFALL	DC-20 GHz (10% to 90% and 90% to 10% RF)		10		ns
Ton, Toff	DC–20 GHz (50% control to 90% RF and 50% control to 90% RF)		10		ns
Input power for P1 dB	1 GHz–20 GHz		25		dBm
Input third order intercept (IIP3)	2 GHz–20 GHz (two-tone input power, 7 dBm/tone)		43		dBm

3.3 Typical Performance Curves

The following graphs show the typical performance curves of the MMS006PP3 device.



Figure 2 • Insertion Loss vs. Temperature




Figure 4 • Return Loss




Figure 6 • Input Third Order Intercept Point




Figure 3 • Isolation





Figure 5 • 0.1 dB and 1 dB Compression Point





3.4 Control Voltages

The following tables list the control voltages of the MMS006PP3 device.

Table 3 • Switch Control Truth Table

Control Input A	Control Input B	Signal Path Condition: RF Common to RF1	Signal Path Condition: RF Common to RF2
High	Low	On	Off
Low	High	Off	On


Table 4 • Digital Control Voltages

State	Bias Condition
Low	–3 V to 0 V
High	−5.0 V to −4.2 V

3.5 Example Driver Circuit

The following illustration shows an example of a possible control voltage driver circuit.

Figure 7 • Driver Circuit Example






4 Package Specification

This section details the package specifications of the MMS006PP3 device.

4.1 Package Outline Drawing

The following illustration shows the package outline of the MMS006PP3 device. Dimensions are in millimeters [inches].

Figure 8 • Package Outline



4.2 Package Information

The following table lists the package information for the MMS006PP3 device. For additional packaging information, contact your Microsemi sales representative.

Table 5 • Package Information

Part Number	Package Body Material	Lead Finish	MSL Rating	Package Marking
MMS006PP3	Low-stress injection molded plastic	100% matte Sn	TBD	MMS 006
				wwyy

4.3 Pin Descriptions

The following table describes the pins of the MMS006PP3 device.

Table 6 • Pin Description Information

Pin Number	Pin Name	Description
1, 5, 9, 12, 16	N/C	These pins should be connected to PCB RF ground to maximize isolation.
2, 4, 6, 8, 13, 15	GND	Package bottom has an exposed metal paddle that must be connected to PCB RF ground.
3, 7, 14	RFC, RF1, RF2	This pin is DC-coupled and matched to 50 Ω . Blocking capacitors are required if RF line potential is not equal to 0 V.



Pin Number	Pin Name	Description
10	CTLB	For details, see Switch Control Truth Table (see page 5) and Digital Control Voltages (see page 5).
11	CTLA	For details, see Switch Control Truth Table (see page 5) and Digital Control Voltages (see page 5).
Backside paddle	RF/DC GND	RF/DC ground.



5 Handling Recommendations

Gallium arsenide integrated circuits are sensitive to electrostatic discharge (ESD) and can be damaged by static electricity. It is recommended to follow all procedures and guidelines outlined in the Microsemi application note ANO1 GaAs MMIC Handling and Die Attach Recommendations.



6 Evaluation Board Information

The circuit board used in the application should be generated with proper RF circuit design techniques. Signal lines at the RF port should have $50~\Omega$ impedance and the package ground leads and backside ground paddle should be connected directly to the ground plane as shown (or similar).

Figure 9 • Evaluation Board




Table 7 • Materials for Evaluation PCB MMS006PP3E

Item	Description
J1, J2, RFC, RF1, RF2	Amphenol end launch SMA RF connector. P/N: 132255RP
J3	Surface mount header pin. P/N: 95278-102-04LF for A, B, GND
R1, R2	100 $Ω$ resistor, 0603 package
U1	MMS006PP3
PCB ¹	Evaluation PCB: 1.29 inches x 1.55 inches

¹ Circuit board material: Rogers 4350.



7 Ordering Information

The following table lists the ordering information for the MMS006PP3 device.

Table 8 • Ordering Information

Part Number	Package
MMS006PP3	3 mm × 3 mm plastic QFN package
MMS006PP3E	Evaluation board for MMS006PP3





Microsemi Corporate Headquarters

One Enterprise, Aliso Viejo, CA 92656 USA Within the USA: +1 (800) 713-4113 Outside the USA: +1 (949) 380-6100 Fax: +1 (949) 215-4996 Email: sales.support@microsemi.com www.microsemi.com

© 2017 Microsemi Corporation. All rights reserved. Microsemi and the Microsemi logo are trademarks of Microsemi Corporation. All other trademarks and service marks are the property of their respective owners.

Microsemi makes no warranty, representation, or guarantee regarding the information contained herein or the suitability of its products and services for any particular purpose, nor does Microsemi assume any liability whatsoever arising out of the application or use of any product or circuit. The products sold hereunder and any other products sold by Microsemi have been subject to limited testing and should not be used in conjunction with mission-critical equipment or applications. Any performance specifications are believed to be reliable but are not verified, and Buyer must conduct and complete all performance and other testing of the products, alone and together with, or installed in, any end-products. Buyer shall not rely on any data and performance specifications or parameters provided by Microsemi. It is the Buyer's responsibility to independently determine suitability of any products and to test and verify the same. The information provided by Microsemi hereunder is provided "as is, where is" and with all faults, and the entire risk associated with such information is entirely with the Buyer. Microsemi does not grant, explicitly or implicitly, to any party any patent rights, licenses, or any other IP rights, whether with regard to such information itself or anything described by such information. Information provided in this document is proprietary to Microsemi, and Microsemi reserves the right to make any changes to the information in this document or to any products and services at any time without notice.

Microsemi Corporation (Nasdaq: MSCC) offers a comprehensive portfolio of semiconductor and system solutions for aerospace & defense, communications, data center and industrial markets. Products include high-performance and radiation-hardened analog mixed-signal integrated circuits, FPGAs, SoCs and ASICs; power management products; timing and synchronization devices and precise time solutions, setting the world's standard for time; voice processing devices; RF solutions; discrete components; enterprise storage and communication solutions; security technologies and scalable anti-tamper products; Ethernet solutions; Power-over-Ethernet ICs and midspans; as well as custom design capabilities and services. Microsemi is headquartered in Aliso Viejo, California, and has approximately 4,800 employees globally. Learn more at www.microsemi.com.