


# MSC050SDA070BCT Zero Recovery Silicon Carbide Schottky Dual Diode

### **Product Overview**

The silicon carbide (SiC) power Schottky barrier diodes (SBD) product line from Microsemi increases your performance over silicon diode solutions while lowering your total cost of ownership for high-voltage applications. The MSC050SDA070BCT is a 700 V, 50 A SiC dual common cathode SBD in a three-lead TO-247 package shown below.



#### **Features**

The following are key features of the MSC050SDA070BCT device:

- No reverse recovery
- · Low forward voltage
- · Low leakage current
- · Avalanche energy rated
- RoHS compliant

#### **Benefits**

The following are benefits of the MSC050SDA070BCT device:

- · High switching frequency
- Low switching losses
- Low noise (EMI) switching
- Higher reliability systems
- · Increased system power density

#### **Applications**

The MSC050SDA070BCT device is designed for the following applications:

- Power factor correction (PFC)
- Anti-parallel diode
  - Switch-mode power supply
  - Inverters/converters
  - Motor controllers
- · Freewheeling diode
  - Switch-mode power supply
  - Inverters/converters
- · Snubber/clamp diode



# **Electrical Specifications**

This section shows the specifications for the MSC050SDA070BCT device. All ratings are per leg.

## **Absolute Maximum Ratings**

The following table shows the absolute maximum ratings for the MSC050SDA070BCT device.

All ratings:  $T_C = 25$  °C unless otherwise specified.

**Table 1 • Absolute Maximum Ratings** 

Symbol	Parameter	Ratings	Unit
V <sub>R</sub>	Maximum DC reverse voltage	700	V
V <sub>RRM</sub>	Maximum peak repetitive reverse voltage	700	
V <sub>RWM</sub>	Maximum working peak reverse voltage	700	
I <sub>F</sub>	Maximum DC forward current (T <sub>c</sub> = 25 °C)	88	А
	Maximum DC forward current (T <sub>c</sub> = 135 °C)	39	
	Maximum DC forward current (T <sub>c</sub> = 145 °C)	32	
I <sub>FRM</sub>	Repetitive peak forward surge current ( $T_c$ = 25 °C, $t_p$ = 8.3 ms, half sine wave)	128	
I <sub>FSM</sub>	Non-repetitive forward surge current ( $T_c = 25$ °C, $t_p = 8.3$ ms, half sine wave)	124	
P <sub>tot</sub>	Power dissipation (T <sub>c</sub> = 25 °C)	283	W
	Power dissipation (T <sub>c</sub> = 110 °C)	123	
T <sub>J</sub> , T <sub>STG</sub>	Operating and storage temperature range	-55 to 175	°C
T <sub>L</sub>	Lead temperature for 10 seconds	300	
E <sub>AS</sub>	Single-pulse avalanche energy (starting $T_J$ = 25 °C, L = 0.08 mH, peak $I_L$ = 50 A)	100	mJ

The following table shows the thermal and mechanical characteristics of the MSC050SDA70BCT device.

**Table 2 • Thermal and Mechanical Characteristics** 

Symbol	Characteristic	Min	Тур	Max	Unit
R <sub>θJC</sub>	Junction-to-case thermal resistance		0.37	0.53	°C/W
W <sub>T</sub>	Package weight		0.22		OZ



Symbol	Characteristic	Min	Тур	Max	Unit
			5.9		g
	Mounting torque, 6-32 or M3 screw			10	lbf-in
				1.1	N-m

### **Electrical Performance**

The following table shows the static characteristics of the MSC050SDA070BCT device.

**Table 3 • Static Characteristics** 

Symbol	Characteristic	Test Conditions	Тур	Max	Unit
V <sub>F</sub>	Forward voltage	I <sub>F</sub> = 50 A, T <sub>J</sub> = 25 °C	1.5	1.8	V
		I <sub>F</sub> = 50 A, T <sub>J</sub> = 175 °C	1.9		
I <sub>RM</sub>	Reverse leakage current	V <sub>R</sub> = 700 V, T <sub>J</sub> = 25 °C	15	200	μА
		V <sub>R</sub> = 700 V, T <sub>J</sub> = 175 °C	250		
Q <sub>C</sub>	Total capacitive charge	V <sub>R</sub> = 400 V, T <sub>J</sub> = 25 °C	133		nC
C <sub>J</sub>	Junction capacitance	V <sub>R</sub> = 1 V, T <sub>J</sub> = 25 °C, f = 1 MHz	2034		pF
	Junction capacitance	V <sub>R</sub> = 200 V, T <sub>J</sub> = 25 °C, f = 1 MHz	248		
	Junction capacitance	V <sub>R</sub> = 400 V, T <sub>J</sub> = 25 °C, f = 1 MHz	216		



### **Performance Curves**

This section shows the typical performance curves for the MSC050SDA070BCT device.




Figure 1 • Maximum Transient Thermal Impedance




Figure 2 • Forward Current vs Forward Voltage




Figure 3 • Max Forward Current vs Case Temp






Figure 4 • Max Power Dissipation vs Case Temp




Figure 5 • Reverse Current vs. Reverse Voltage




Figure 6 ● Total Capacitive Charge vs. V<sub>R</sub>




Figure 7 • Junction Capacitance vs  $V_R$ 



# **Package Specification**

This section outlines the package specification for the MSC050SDA070BCT device.

## **Package Outline Drawing**

This section shows the TO-247 package drawing of the MSC050SDA070BCT device. Dimensions are in millimeters and (inches).




Figure 8 • Package Outline Drawing

The following table shows the TO-247 dimensions and should be used in conjunction with the package outline drawing.

Table 4 • Dimensions

Symbol	Min. (mm)	Max. (mm)	Min. (in.)	Max (in.)
А	4.69	5.31	0.185	0.209
В	1.49	2.49	0.059	0.098
С	2.21	2.59	0.087	0.102
D	0.40	0.79	0.016	0.031
Е	5.38	6.20	0.212	0.244
F	3.50	3.81	0.138	0.150



Symbol	Min. (mm)	Max. (mm)	Min. (in.)	Max (in.)	
G	6.15 BSC		0.242 BSC		
Н	20.80	21.46	0.819	0.845	
I	19.81	20.32	0.780	0.800	
J	4.00	4.50	0.157	0.177	
К	1.01	1.40	0.040	0.055	
L	2.87	3.12	0.113	0.123	
М	1.65	2.13	0.065	0.084	
N	15.49	16.26	0.610	0.640	
0	13.50	14.50	0.531	0.571	
Р	16.50	17.50	0.650	0.689	
Q	5.45 BSC		0.215 BSC		
R	2.00	2.75	0.079	0.108	
S	7.10	7.50	0.280	0.295	
Terminal 1	Anode 1				
Terminal 2	Common cathode				
Terminal 3	Anode 2				
Terminal 4	Common cathode				





#### Microsemi

2355 W. Chandler Blvd. Chandler, AZ 85224 USA

Within the USA: +1 (480) 792-7200 Fax: +1 (480) 792-7277

www.microsemi.com © 2020 Microsemi and its corporate affiliates. All rights reserved. Microsemi and the Microsemi logo are trademarks of Microsemi Corporation and its corporate affiliates. All other trademarks and service marks are the property of their respective owners.

Microsemi's product warranty is set forth in Microsemi's Sales Order Terms and Conditions. Information contained in this publication is provided for the sole purpose of designing with and using Microsemi products. Information regarding device applications and the like is provided only for your convenience and may be superseded by updates. Buyer shall not rely on any data and performance specifications or parameters provided by Microsemi. It is your responsibility to ensure that your application meets with your specifications. THIS INFORMATION IS PROVIDED "AS IS." MICROSEMI MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION, INCLUDING BUT NOT LIMITED TO ITS CONDITION, QUALITY, PERFORMANCE, NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. IN NO EVENT WILL MICROSEMI BE LIABLE FOR ANY INDIRECT, SPECIAL, PUNITIVE, INCIDENTAL OR CONSEQUENTIAL LOSS, DAMAGE, COST OR EXPENSE WHATSOEVER RELATED TO THIS INFORMATION OR ITS USE, HOWEVER CAUSED, EVEN IF MICROSEMI HAS BEEN ADVISED OF THE POSSIBILITY OR THE DAMAGES ARE FORESEEABLE. TO THE FULLEST EXTENT ALLOWED BY LAW, MICROSEMI'S TOTAL LIABILITY ON ALL CLAIMS IN RELATED TO THIS INFORMATION OR ITS USE WILL NOT EXCEED THE AMOUNT OF FEES, IF ANY, YOU PAID DIRECTLY TO MICROSEMI FOR THIS INFORMATION. Use of Microsemi devices in life support, mission-critical equipment or applications, and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend and indemnify Microsemi from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microsemi intellectual property rights unless otherwise stated.

Microsemi Corporation, a subsidiary of Microchip Technology Inc. (Nasdaq: MCHP), and its corporate affiliates are leading providers of smart, connected and secure embedded control solutions. Their easy-to-use development tools and comprehensive product portfolio enable customers to create optimal designs which reduce risk while lowering total system cost and time to market. These solutions serve more than 120,000 customers across the industrial, automotive, consumer, aerospace and defense, communications and computing markets. Headquartered in Chandler, Arizona, the company offers outstanding technical support along with dependable delivery and quality. Learn more at www.microsemi.com.

053-4115 | February 2020 | Released