# DATASHEET

# ITR8307/S17/TR8(B)

Features

- Fast response time
- High sensitivity
- Cut-Off visible wavelength
- Thin
- Compact
- Pb free
- This product itself will remain within RoHS compliant version.
- Compliance with EU REACH.
- Compliance Halogen Free .(Br <900 ppm ,Cl <900 ppm , Br+Cl < 1500 ppm).

#### Description

**ITR8307/S17/TR8(B)** is a light reflection switch which includes a GaAs IR-LED transmitter and a NPN photo-transistor with a high photosensitive receiver for short distance, operating in the infrared range. Both components are mounted side- by- side in a plastic package.

#### Applications

- Camera
- VCR
- Floppy disk driver
- Cassette type recorder
- Various microcomputer control equipment

#### **Device Selection Guide**

Device No.	Chip Material		
IR	GaAlAs		
PT	Silicon		



EVERLIGHT

# Absolute Maximum Ratings (Ta=25°C)

	Parameter	Symbol	Ratings	Unit
	Power Dissipation at(or below) 25°C Free Air Temperature	Pd	75	mW
Input	Reverse Voltage	V <sub>R</sub>	5	V
	Forward Current	$I_{\mathrm{F}}$	50	mA
	Peak Forward Current (*1) Pulse width $\leq 100 \mu s$ , Duty cycle=1%	$I_{\mathrm{FP}}$	1	A
Output	Collector Power Dissipation	P <sub>C</sub>	75	mW
	Collector Current	I <sub>C</sub>	50	mA
	Collector-Emitter Voltage	B V <sub>CEO</sub>	30	V
	Emitter-Collector Voltage	B V <sub>ECO</sub>	5	V
Operating	Temperature	Topr	-25~+85	°C
Storage T	emperature	Tstg	-30~+90	°C
Lead Soldering Temperature (*2) (1/16 inch form body for 5 seconds)		Tsol	260	°C

**Notes:** (\*1) tw=100 µsec., T=10 msec. (\*2) t=5 Sec


# Electro-Optical Characteristics (Ta=25°C)

Parameter		Symbol	Min.	Тур.	Max.	Unit	Conditions	
Input	Forward Voltage	$V_{\mathrm{F}}$		1.2	1.6	V	I <sub>F</sub> =20mA	
	Reverse Current	I <sub>R</sub>			10	$\mu A$	V <sub>R</sub> =5V	
	Peak Wavelength	$\lambda_{\mathrm{P}}$		940		nm		
Output	Dark C urrent	I <sub>CEO</sub>			100	nA	V <sub>CE</sub> =10V	
	C-E Saturation Voltage	V <sub>CE</sub> (sat)			0.4	V	I <sub>C</sub> =2mA ,Ee=1mW/cm <sup>2</sup>	
Transfer Characteristics	Light Current	I <sub>C(ON)</sub>	0.18		0.30	mA	V <sub>CE</sub> =5V, I <sub>F</sub> =10mA	
	Leakage Current	ICEOD			1	μA		
	Rise time	t <sub>r</sub>		20		$\mu$ sec	V <sub>CE</sub> =2V,I <sub>C</sub> =100 μ A	
	Fall time	t <sub>f</sub>		20		$\mu$ sec	$R_L=1K\Omega$	


# Rank

Conditions :  $I_F=10mA$  V<sub>CE</sub>=5V Unit:  $\mu A$ 


Bin number	Min	Max
B1	180	250
B2	230	300




## Typical Electrical/Optical/Characteristics Curves for IR




## **Typical Electro/Optical/Characteristics Curves for PT**





EVERLIGHT

#### **Package Dimension**



#### Notes:


- 1.All dimensions are in millimeters
- 2. Tolerances unless dimensions  $\pm 0.15$  mm
- 3.Lead spacing is measured where the lead emerge from the package
- 4. Above specification may be changed without notice. EVERLIGHT will reserve authority on material change

for above specification

- 5. These specification sheets include materials protected under copyright of EVERLIGHT corporation . Please don't reproduce or cause anyone to reproduce them without EVERLIGHT's consent
- 6.When using this product, please observe the absolute maximum ratings and the instructions for use outlined in these specification sheets. EVERIGHT assumes no responsibility for any damage resulting from use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.




# **Taping Dimension:**




General Tolerance ±0.1 UNIT:mm

# **Reel Dimensions**



# **Note:** The tolerances unless mentioned is $\pm 0.1$ mm, Unit = mm


#### **Moisture Resistant Packaging**



## **Packing Quantity Specification**

- 1. 1000 Pcs/ 1Reel
- 2. 15 Reel /1 Box
- 3. 2 Box/ 1 Carton

#### **Label Form Specification**



- · CPN: Customer's Product Number
- · P/N: Product Number
- · QTY: Packing Quantity
- · CAT: Luminous Intensity Rank
- HUE: Dom. Wavelength Rank
- · REF: Forward Voltage Rank
- · LOT No: Lot Number
- · X: Month
- · Reference: Identify Label Number

## DISCLAIMER

- 1. EVERLIGHT reserves the right(s) on the adjustment of product material mix for the specification.
- 2. The product meets EVERLIGHT published specification for a period of twelve (12) months from date of shipment.
- 3. The graphs shown in this datasheet are representing typical data only and do not show guaranteed values.
- 4. When using this product, please observe the absolute maximum ratings and the instructions for using outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from the use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
- 5. These specification sheets include materials protected under copyright of EVERLIGHT. Reproduction in any form is prohibited without obtaining EVERLIGHT's prior consent.
- 6. This product is not intended to be used for military, aircraft, automotive, medical, life sustaining or life saving applications or any other application which can result in human injury or death. Please contact authorized Everlight sales agent for special application request.