


100A 100V N-channel Enhancement Mode Power MOSFET

1 Description

These N-channel enhancement mode power mosfets used advanced split gate trench technology design, provided excellent $R_{DS(on)}$ and low gate charge. Which accords with the RoHS standard.




2 Features

- Fast switching
- Low on resistance
- Low gate charge
- High avalanche current
- Low reverse transfer capacitances
- 100% single pulse avalanche energy test
- 100% ΔV_{DS} test

3 Applications

- Synchronous rectification in SMPS
- Hard switching and high speed circuit
- Power tools
- UPS
- Motor control



4 Electrical Characteristics

4.1 Absolute Maximum Ratings (Tc=25°C, unless otherwise noted)

| Parameter | Symbol | Rating | | | | Units |
|--|-------------------|------------|--------------------------|--------------------------|------------|-------|
| | | DHS065 N10 | DHS065N10I DHS065N10E | DHS065N10B DHS065N10D | DHS065N10F | |
| Drain-to-Source Voltage | V_{DSS} | 100 | | | | V |
| Gate-to-Source Voltage | V_{GSS} | ± 20 | | | | V |
| Continuous Drain Current | $T_C=25^\circ C$ | 100 | | | | A |
| | $T_C=100^\circ C$ | 70 | | | | A |
| Pulsed Drain Current ⁽¹⁾ | I_{DM} | 400 | | | | A |
| Single Pulse Avalanche Energy ⁽⁴⁾ | E_{AS} | 420 | | | | mJ |
| Avalanche Current ⁽⁴⁾ | I_{AS} | 41 | | | | A |
| Power Dissipation | $T_a=25^\circ C$ | 2 | 2 | 2 | 2 | W |
| | $T_C=25^\circ C$ | 172 | 172 | 172 | 35 | W |
| Isolation Voltage | V_{ISO} | / | | | 2500 | V |
| Junction Temperature Range | T_j | -55~175 | | | | °C |
| Storage Temperature Range | T_{stg} | -55~175 | | | | °C |

4.2 Thermal Characteristics

| Parameter | Symbol | Rating | | | | Units |
|---|------------|------------|--------------------------|--------------------------|------------|-------|
| | | DHS052 N10 | DHS052N10I DHS052N10E | DHS052N10B DHS052N10D | DHS052N10F | |
| Thermal Resistance, Junction to Case-sink | R_{thJC} | 0.87 | 0.87 | 0.87 | 4.29 | °C/W |
| Thermal Resistance, Junction to Ambient | R_{thJA} | 75 | 75 | 75 | 75 | °C/W |

4.3 Electrical Characteristics (Tc=25°C, unless otherwise noted)

| Parameter | Symbol | Test Condition | Value | | | Units |
|---|---------------------|--|-------|------|------|-------|
| | | | Min | Typ | Max | |
| Off Characteristics | | | | | | |
| Drain-to-Source Breakdown Voltage | BV _{DSS} | I _D =250μA, V _{GS} =0V | 100 | -- | -- | V |
| Drain-to-Source Leakage Current | I _{DSS} | V _{DS} =100V, V _{GS} =0V, T _C =25°C | -- | -- | 1 | μA |
| | | V _{DS} =100V, V _{GS} =0V, T _C =125 | -- | -- | 100 | μA |
| Gate-to-Source Leakage Current | I _{GSS} | V _{GS} =±20V, V _{DS} =0V | -- | -- | ±100 | nA |
| On Characteristics | | | | | | |
| Gate Threshold Voltage | V _{GS(th)} | V _{DS} =V _{GS} , I _D =250μA | 2 | 3 | 4 | V |
| Drain-to-Source on-state Resistance | R _{DS(on)} | V _{GS} =10V, I _D =50A | -- | 6.5 | 7.8 | mΩ |
| Dynamic Characteristics | | | | | | |
| Input Capacitance | C _{iss} | V _{GS} =0V, V _{DS} =30V, f=1.0MHz | -- | 4027 | -- | pF |
| Output Capacitance | C _{oss} | | -- | 374 | -- | |
| Reverse Transfer Capacitance | C _{rss} | | -- | 73 | -- | |
| Gate Resisitance | R _G | V _{DD} =0V, V _{GS} =0V, F=1MHz | -- | 2.5 | -- | Ω |
| Switching Characteristics | | | | | | |
| Turn-on Delay Time | t _{d(on)} | I _D =43A, V _{DD} =50V, V _{GS} =10V, R _{GEN} =1.6Ω | -- | 19.5 | -- | nS |
| Turn-on Rise Time | t _r | | -- | 60.5 | -- | |
| Turn-off Delay Time | t _{d(off)} | | -- | 35.5 | -- | |
| Turn-off Fall Time | t _f | | -- | 58.9 | -- | |
| Total Gate Charge | Q _g | I _D =43A, V _{DD} =50V, V _{GS} =10V | -- | 53 | -- | nC |
| Gate-to-Source Charge | Q _{gs} | | -- | 25 | -- | |
| Gate-to-Drain("Miller") Charge | Q _{gd} | | -- | 6.2 | -- | |
| Drain-Source Diode Characteristics | | | | | | |
| Diode Forward Voltage ⁽³⁾ | V _{SD} | V _{GS} =0V, I _S =50A | -- | -- | 1.2 | V |
| Diode Forward Current | I _S | | -- | -- | 100 | A |
| Reverse Recovery Time ⁽³⁾ | t _{rr} | T _J =25°C, I _F =95A, di _F /dt=100A/μS, V _{GS} =0V | -- | 56 | -- | nS |
| Reverse Recovery Charge ⁽³⁾ | Q _{rr} | | -- | 48 | -- | nC |

Notes:

1: Repetitive rating, pulse width limited by maximum junction temperature.

2: Surface mounted on FR4 Board, t≤10sec.

3: Pulse width ≤ 300μs, duty cycle ≤ 2%.

4: L=0.5mH, I_D=41A, V_{DD}=50V, V_{GATE}=100V, Start T_J=25°C.

5 Typical characteristics diagrams




Fig 1. Output Characteristics




Fig 2. Transfer Characteristics




Fig 3. Rdson-Drain Current




Fig 4. Rdson-Junction Temperature




Fig 5. Gate Charge




Fig 6. Source-Drain Diode Forward

6 Typical characteristics diagrams(Continues)




Fig 7. Capacitance vs Vds




Fig 8. Safe Operation Area




Fig 9. Power De-rating




Fig 10. Current De-rating






Fig 11. Normalized Maximum Transient Thermal Impedance


6 Typical Test Circuit and Waveform




1) Gate Charge Test Circuit



2) . Gate Charge Waveform




3) Resistive Switching Test Circuit




4) Resistive Switching Waveforms


6 Typical Test Circuit and Waveform(continues)




5) Diode Reverse Recovery Test Circuit



6) Diode Reverse Recovery Waveform



7) . Unclamped Inductive Switching Test Circuit



8) Unclamped Inductive Switching Waveforms

7 Product Names Rules

D H S X X X N E X X F

LOGO Code: DH

Process Code:
Spilt Gate Trench: S

RDSON Specification Code
With 3 Digitals,
For Example:
045 on behalf of 4.5mΩ
050 on behalf of 5.0mΩ
155 on behalf of 15.5mΩ

Channel Polarity Code
N on behalf of N channel
P on behalf of P channel

Packaging Code
220F: F 220: Nothing
262: I 263: E
3P: D 247: B

Rated Voltage Code
With 2-3 Digitals,
For Example:
06 on behalf of 60V
08 on behalf of 80V
045 on behalf of 45V


Special Function Code
E on behalf of build-in ESD
Nothing on behalf of not ESD

8 Product Specifications and Packaging Models

| Product Model | Package Type | Mark Name | RoHS | Package | Quantity |
|---------------|--------------|------------|---------|-------------|----------|
| DHS065N10 | TO-220 | DHS065N10 | Pb-free | Tube | 1000/box |
| DHS065N10F | TO-220F | DHS065N10F | Pb-free | Tube | 1000/box |
| DHS065N10B | TO-251 | DHS065N10B | Pb-free | Tube | 3000/box |
| DHS065N10D | TO-252 | DHS065N10D | Pb-free | Tape & Reel | 2500/box |
| DHS065N10I | TO-262 | DHS065N10I | Pb-free | Tube | 1000/box |
| DHS065N10E | TO-263 | DHS065N10E | Pb-free | Tape & Reel | 800/box |


9 Dimensions

TO-251B PACKAGE OUTLINE DIMENSIONS



| Symbol | Dimensions In Millimeters | | Dimensions In Inches | |
|--------|---------------------------|-------|----------------------|--------|
| | min. | max. | min. | max. |
| a | 2.20 | 2.40 | 0.087 | 0.0946 |
| b | 0.46 | 0.58 | 0.018 | 0.023 |
| C | 2.45 | 2.65 | 0.097 | 0.104 |
| D | 0.80 | 0.90 | 0.032 | 0.035 |
| d | 6.30 | 6.70 | 0.248 | 0.264 |
| D1 | 5.00 | 5.50 | 0.197 | 0.217 |
| D2 | TYP 4.83 | | TYP 0.190 | |
| A | 5.80 | 6.20 | 0.228 | 0.244 |
| e | 2.19 | 2.39 | 0.086 | 0.094 |
| L | 10.40 | 11.00 | 0.4098 | 0.4334 |
| B | 3.50 | 3.70 | 0.1379 | 0.1458 |
| L2 | 1.5 | 1.8 | 0.059 | 0.071 |
| Φ | 1.10 | 1.30 | 0.0433 | 0.0512 |
| h | 0.00 | 0.30 | 0.000 | 0.012 |
| V | 5.25 | 5.85 | 0.207 | 0.230 |
| E | 0.60 | 0.80 | 0.0236 | 0.0315 |


TO-252B PACKAGE OUTLINE DIMENSIONS



| Symbol | Dimensions In Millimeters | | Dimensions In Inches | |
|--------|---------------------------|-------|----------------------|-------|
| | min. | max. | min. | max. |
| a | 2.20 | 2.40 | 0.087 | 0.095 |
| b | 0.46 | 0.58 | 0.018 | 0.023 |
| c | 0.70 | 0.90 | 0.028 | 0.035 |
| D | 0.80 | 1.00 | 0.032 | 0.039 |
| d | 6.30 | 6.70 | 0.248 | 0.264 |
| D1 | 5.00 | 5.50 | 0.197 | 0.217 |
| D2 | TYP 4.83 | | TYP 0.190 | |
| A | 5.80 | 6.20 | 0.228 | 0.244 |
| e | 2.19 | 2.39 | 0.086 | 0.094 |
| L | 9.40 | 10.40 | 0.370 | 0.409 |
| B | 2.6 | 3.2 | 0.102 | 0.126 |
| L2 | 1.5 | 1.8 | 0.059 | 0.071 |
| θ | 0 | 8 | 0 | 8 |
| h | 0 | 0.3 | 0 | 0.012 |
| V | 5.25 | 5.85 | 0.207 | 0.230 |
| E | 0.6 | 0.8 | 0.024 | 0.032 |


9 Dimensions(continues)

TO-220C PACKAGE OUTLINE DIMENSIONS



| Symbol | Dimensions In Millimeters | | Dimensions In Inches | |
|--------|---------------------------|-------|----------------------|-------|
| | min. | max. | min. | max. |
| A | 8.80 | 9.30 | 0.346 | 0.366 |
| B | 9.70 | 10.30 | 0.382 | 0.406 |
| C | 4.25 | 4.75 | 0.167 | 0.187 |
| D | 1.20 | 1.45 | 0.047 | 0.057 |
| E | 0.40 | 0.60 | 0.016 | 0.024 |
| H | 2.54 TYP | | 0.100 TYP | |
| W | 0.60 | 0.95 | 0.024 | 0.037 |
| W1 | 1.05 | 1.45 | 0.041 | 0.057 |
| W2 | 1.20 | 1.60 | 0.047 | 0.063 |
| L | 12.60 | 13.40 | 0.496 | 0.528 |
| L1 | 2.45 | 2.95 | 0.096 | 0.116 |
| L2 | 3.45 | 3.95 | 0.136 | 0.156 |
| L3 | 8.15 | 8.65 | 0.321 | 0.341 |
| Φ | 3.50 | 3.90 | 0.138 | 0.154 |


TO-220F PACKAGE OUTLINE DIMENSIONS



| Symbol | Dimensions In Millimeters | | Dimensions In Inches | |
|--------|---------------------------|-------|----------------------|-------|
| | min. | max. | min. | max. |
| A | 8.80 | 9.30 | 0.346 | 0.366 |
| B | 10.00 | 10.50 | 0.394 | 0.413 |
| C | 4.30 | 4.90 | 0.169 | 0.193 |
| D | 2.30 | 2.70 | 0.091 | 0.106 |
| L | 15.55 | 16.15 | 0.612 | 0.636 |
| h | 0.40 | 0.60 | 0.016 | 0.024 |
| L1 | 3.15 | 3.55 | 0.124 | 0.140 |
| L2 | 12.65 | 13.35 | 0.498 | 0.526 |
| W | 0.70 | 0.90 | 0.028 | 0.035 |
| W1 | 1.15 | 1.55 | 0.045 | 0.061 |
| H | 2.54 TYP | | 0.100 TYP | |
| E | 0.48 | 0.53 | 0.019 | 0.021 |
| Φ | 2.90 | 3.40 | 0.114 | 0.134 |
| E1 | 2.40 | 2.90 | 0.094 | 0.114 |
| F | 7.75 | 8.25 | 0.305 | 0.325 |
| F1 | 7.35 | 7.85 | 0.289 | 0.309 |


9 Dimensions(continues)

TO-262 PACKAGE OUTLINE DIMENSIONS



| Symbol | Dimensions In Millimeters | | Dimensions In Inches | |
|--------|---------------------------|-------|----------------------|--------|
| | min. | max. | min. | max. |
| A | 8.80 | 9.30 | 0.346 | 0.366 |
| B | 9.70 | 10.30 | 0.382 | 0.406 |
| C | 4.25 | 4.75 | 0.167 | 0.187 |
| D | 1.20 | 1.45 | 0.047 | 0.057 |
| E | 0.40 | 0.60 | 0.016 | 0.024 |
| L | 12.25 | 13.75 | 0.482 | 0.541 |
| L1 | 1.15 | 1.45 | 0.045 | 0.057 |
| E1 | 2.4 | 2.6 | 0.0945 | 0.1024 |
| W | 0.80 | 0.82 | 0.0315 | 0.034 |
| W1 | 1.20 | 1.30 | 0.047 | 0.051 |
| H | 2.54 TYP | | 0.200 TYP | |
| b | 5.50 | 6.50 | 0.216 | 0.256 |

TO-263 PACKAGE OUTLINE DIMENSIONS



| Symbol | Dimensions In Millimeters | | Dimensions In Inches | |
|--------|---------------------------|-------|----------------------|--------|
| | min. | max. | min. | max. |
| A | 8.80 | 9.30 | 0.346 | 0.366 |
| B | 9.70 | 10.30 | 0.382 | 0.406 |
| C | 4.25 | 4.75 | 0.167 | 0.187 |
| D | 1.20 | 1.45 | 0.047 | 0.057 |
| E | 0.40 | 0.60 | 0.016 | 0.024 |
| L | 1.90 | 2.30 | 0.075 | 0.091 |
| L1 | 1.15 | 1.45 | 0.045 | 0.057 |
| R | 0.24 | 0.26 | 0.0095 | 0.0102 |
| W | 0.80 | 0.82 | 0.0315 | 0.0323 |
| W1 | 1.20 | 1.30 | 0.047 | 0.051 |
| H | 2.54 TYP | | 0.200 TYP | |
| b | 5.50 | 6.50 | 0.216 | 0.256 |
| E1 | 2.4 | 2.6 | 0.0946 | 0.1024 |
| L2 | 5.20 | 5.80 | 0.205 | 0.228 |
| L3 | 2.20 | 3.20 | 0.087 | 0.126 |
| F | 0.03 | 0.23 | 0.0012 | 0.0091 |

10 Attentions

- Jiangsu Donghai Semiconductor Technology CO.,LTD. reserves the right to change the specification without prior notice! The customer should obtain the latest version of the information before making the order and verify that the information is complete and up to date.
- It is the responsibility of the purchaser for any failure or failure of any semiconductor product under certain conditions. It is the responsibility of the purchaser to comply with safety standards and to take safety measures in the system design and machine manufacturing of Donghai products in order to avoid potential risk of failure. Injury or property damage.
- Product promotion is endless, our company will be dedicated to provide customers with better products.

11 Appendix

Revision history:

| Date | REV. | Description | Page |
|------------|------|-------------|------|
| 2021.03.12 | 1.0 | Original | |