

## ► Features

- High Current Capability
- Low Forward Voltage Drop
- Low IR
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260°C


**SOD-323**


## ► Applications

The device is a single rectifier offering low VF and excellent high temperature stability.

## ► Mechanical Data

- Case: SOD-323  
Molding compound meets UL 94V-0 flammability rating, RoHS-compliant, halogen-free
- Terminals: Solder plated, solderable per MIL-STD-750, Method 2026
- Polarity: Cathode line denotes the cathode end



## ► Maximum Ratings (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	UNIT	VALUE
Maximum Repetitive Peak Reverse Voltage	V <sub>RRM</sub>	V	60
Maximum RMS Voltage	V <sub>RMS</sub>	V	42
Maximum DC blocking Voltage	V <sub>DC</sub>	V	60
Maximum average forward rectified current	I <sub>F(AV)</sub>	A	1.0
Non-repetitive Forward Surge Current @ t=8.3ms Half-sine wave	I <sub>FSM</sub>	A	10
Power Dissipation	P <sub>D</sub>	mW	250
Storage temperature	T <sub>stg</sub>	°C	-55 ~+150
Junction temperature	T <sub>j</sub>	°C	-55 ~+125
Typical Thermal Resistance	R <sub>θJ-A</sub>	°C /W	400

## ► Electrical Characteristics (Ta=25°C Unless otherwise specified)

PARAMETER	TEST CONDITIONS	SYMBOL	UNIT	Min	Typ	Max
Maximum forward voltage	I <sub>F</sub> =1.0A	V <sub>F</sub>	V	—	—	0.70
Maximum reverse current	V <sub>R</sub> =60V	I <sub>R</sub>	μA	—	—	100
Capacitance between terminals	V <sub>R</sub> =4V,f=1MHz	C <sub>T</sub>	pF	—	—	120

## ► Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)




Fig.1 Typical Instantaneous Forward Characteristics




Fig.2 Typical Reverse Characteristics




Fig.3 Typical Junction Capacitance





Fig.4 Power Derating Curve

## ► Ordering Information


PACKAGE	PACKAGE CODE	UNIT WEIGHT(g)	REEL(pcs)	BOX(pcs)	CARTON(pcs)	DELIVERY MODE
SOD-323	R1	0.0048	3000	30000	120000	7"

## ► Package Outline Dimensions (SOD-323)



Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	1.60	1.80	0.063	0.071
B	0.25	0.40	0.010	0.016
C	2.30	2.80	0.091	0.110
D	0.80	1.10	0.031	0.043
D <sub>1</sub>	0.80	0.90	0.031	0.035
E	1.20	1.40	0.047	0.055
F	0.08	0.18	0.003	0.007
L	0.475REF		0.019REF	
L <sub>1</sub>	0.25	0.40	0.010	0.016
H	-	0.14	-	0.006

## ► Suggested Pad Layout



Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
J	0.80	-	0.031	-
K	-	1.40	-	0.055
M	0.80	-	0.031	-