




RoHS


REV.	ECN NO.	DESCRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2023.09.05



**Product Characteristics**

<b>Blocks and Clips for Blade Fuses</b>	
<b>Compatible Fuses</b>	Automotive Blade Fuses
<b>Electrical Specifications</b>	Rated Voltage: 500 V
	Rated Current: From 15 to 30 A
<b>Molded Parts</b>	Insulation Block: Black Thermoplastic PET (UL94 V-0) and PA66 (UL94 V-0)
<b>Metal Parts</b>	PCB Terminals: Tin Plated Cu Alloy
<b>Electrical</b>	Insulation Resistance: 10,000 Megaohm Minimum at 500 VDC
	Contact Resistance: ≤ 5 mΩ Maximum
<b>Ambient Temperature</b>	-40 °C to 125 °C

ACTUAL SIZE



X.±0.50	X.°±	PART NO.: XF-508PVS-B	<b>XFCN</b> 兴飞连接器		
.X±0.25	.X°±				
.XX± 0.15	.XX°±				
.XXX±0.10	.XXX°±				
UNITS:	mm	TITLE: SMT MINI AUTO FUSE HOLDER	0769-82001899		
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN		APPD:	www.xfconn.com		
		CHKD:	DWG NO: /		
		DRAW: Tong.Deng	2023.09.05		SCALE NONE