

产品规格书

SPECIFICATIONS FOR PRODUCT

产品类型 TYPE : Quartz Crystal

产品规格 SPEC : 32.768KHz/2012/12.5PF/20PPM

产品型号 P/N : CJK08-327681220B20

日期 DATE : 2022/08/12

核准及签名			部パコ
R&D APPR. SIGNATURED			DEPT.
拟制	审核	批准	频率器件事业部
ISSUE	CHECK	APPROVAL	
Ivan 2022/08/12	Abbey 2022/08/12	Ken 2022/08/12	

江 苏 长 晶 科 技 **股 份** 有 限 公 司 JIANGSU CHANGJING ELECTRONICS TECHNOLOGY CO., LTD.

地址:中国江苏省南京江北新区产业技术研创园江淼路88号腾飞大厦C座13楼Add: 13Th Floor, C Block, Tengfei Building, No. 88 Jiangmiao Rd. Pukou District, Nanjing City, Jiangsu Province, China



JIANGSU CHANGJING ELECTRONICS TECHNOLOGY CO., LTD.

CJK08 Quartz Crystal

CJK08-327681220B20

1. Scope:

This specification applies to the RoHS/SONY compliance quartz crystal unit with a frequency of 32.768KHz which will be used in crystal oscillator applications.

2. Construction:

2.1 Type of Quartz Resonator: CJK08

3. Electrical Characteristics

3.1 Mode of Vibration:	+2°X-cut , Fundamental
3.2 Nominal frequency(F):	32.768KHz
3.3 Load Capacitance(CL):	12.5PF
3.4 Frequency Tolerance at 25	°C ±20ppm
3.5 Series Resistance(Rr):	80 KΩ Max
3.6 Quality Factor(Q):	13 KΩ Min
3.7 Turnover Temperature(To)	25 ℃± 5℃
3.8 Temperature Coefficient(K	: -0.035±0.005 ppm/℃²
3.9 Operation Temperature:	-40 ℃~ +85℃
3.10 Preservation Temperature:	-55 °C∼ +125°C
3.11 Shunt Capacitance(Co):	1.15PF Typical
3.12 Aging 1st Year(△f/f):	±3 ppm Max.
3.13 Shock Resistance:	±5 ppm Max.
3.14 Motional Capacitance(C ₁):	4.6fF Typical
3.15 Insulation Resistance:	500MΩ at DC 100V±15V
3.16 Drive Level:	0.5μW Max

Reliability Specifications

4. Reliability Specifications

This is the quality control and quality assurance and reliability tests performance data for the RoHS/SONY compliance 32.768KHz SMD2012 Quartz Crystal.

related to the specification and approval sheet provided by JSCJ.

Standard test condition (TEMP.: 20±5°C. Relative humidity: 65±20%)

For any discrepancy in GO/NG, test will be done at TEMP.25±2°C, R.H. 65±5%.

NO.	PROCESS	SPECIFICATION	TEST METHOD
4.1	Temperature Cycle (GB/T 2423.22-2002, Method Nb)	Frequency change after test ≤± 5ppm.Resonance resistance change after test ≤10ohms.	10 cycles from -55°C to 125°C. Measurement taken after DUT being left at room temperature for 24±2 hours.
4.2	Aa)	Frequency change after test ≤± 5ppm.Resonance resistance change after test ≤10ohms.	Spending 72 hrs at -55°C±3°C constant temperature. Measurement taken after DUT being left at room temperature for 24±2 hours.
	Ba)	Frequency change after test ≤± 5ppm.Resonance resistance change after test ≤10ohms.	Spending 72 hrs at 125°C±3°C constant temperature. Measurement taken after DUT being left at room temperature for 24±2 hours.
4.4	Humidity (GB/T 2423.3- 2006, Method Cab)	Frequency change after test ≤± 5ppm.Resonance resistance change after test ≤10ohms.	Spending 96 hrs at 40 °C \pm 3 °C, with 93 %R.H, Then keep the DUT in dry oven at 40 \pm 5 °C for 24 hour. Measurement taken after DUT being left at room temperature for 1 to 2 hours.
4.5	Vibration (GB/T 2423.10- 1995, Method Fc)	Frequency change after test ≤± 5ppm.Resonance resistance change after test ≤10ohms.	Apply 0.75mm vibration at sweep frequency 10^{\sim} 500 Hz, 10 cycles in each direction of 3 axis. Measurement taken after 1 hour.
4.6	Shock (GB/T 2423.5-1995, Method Ea)	Frequency change after test ≤± 5ppm.Resonance resistance change after test ≤10ohms.and exhibit no visible damage.	Peak 1000m/s2, normal width 6ms half sine wave form, 3.7m/s, 3 perpendicular axis of samples, 3 cycles / direction, total 18 cycles. Measurement taken after 1 hour.
	Drop (GB/T 2423.8-1995, Method Ed)	Frequency change after test ≤± 5ppm.Resonance resistance change after test ≤10ohms.and exhibit no visible damage.	Free drop to the steel plate with thickness of 3 mm from 0.75 m heights for 3 times.
4.8	Solderability (IEC60068-2-58,Test Td:)	Terminals shall be covered more then 95% with solder.	Passed through the re-flow oven under the following condition. Preheat 150 to 180°C for 60 to 120sec, and soldering time for 20s ± 5s at 235°C, peak soldering time for 10s ± 1s betweein 240 and 250°C. There is no need to do functional test. 8-12X magnifier.
4.9	Terminal Strength (JIS-C-6429 Method 1 & 2)	No visible damage	Mount on a glass-epoxy board (100x50x1.6mm), then bend to 2mm displacement (velocity 1mm/sec) and keep for 5 seconds. or pulling force 0.5kg for at least 60 seconds.
4.10	Resistance to Soldering Heat (IEC60068-2-58,Test Td: Table 4)	Frequency change after test ≤± 5ppm.Resonance resistance change after test ≤10ohms.	Passed through the re-flow oven under the following condition. Preheat 150 to 180°C for 60 to 120sec, and sodering time for 60s max at 235°C, peak soldering time for 20s max at 265°C max. Measurement taken after DUT being left at room temperature for at least 2 hours.
	OTHERS		


Notes: The above test items and judgment standards are for reference only, and the actual reliability report shall prevail.

Recommended Reflow soldering condition

5. Recommended Reflow soldering condition (SMD)

Solder profile

Peak: 260±5°C Soldering zone: 230°C or more, 30±10s. Pre-heating zone 1: 150 \sim 180°C, 90±30s




Temperature profile for reflow soldering

6. Soldering iron method


Bit temperature: 350±10℃ Application time of soldering iron:3+1 s. For other procedures, refer to IEC 60068-2-20.

Package Outline Dimensions

Units:mm





Suggested Pad Layout



Tape and Reel


CARRIER TYPE






Α	В	С	D	Е	F	G	Н	J	K	t
1. 4	2. 3	8. 0	3. 5	1. 75	4. 0	2. 0	4. 0	1. 5	0. 75	0. 25

REMARK



REEL: 3000 PCS/Reel



NOTICE

JSCJ reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to any product herein. JSCJ does not assume any liability arising out of the application or use of any product described herein.