





注：本板为禁止运输、复制、编辑文件，以及用其内容进行交流

REV	ECN NO.	CONTENT	CHK	DATE



Pitch Range In mm	Nominal Dimension In mm	Range
Over 6	Over 10	Over 30
TO 6	TO 10	TO 30
Over 10	Over 24	Over 60
TO 10	TO 24	TO 60
Over 100	Over 150	Over 100
TO 100	TO 150	TO 100
±0.15	±0.20	±0.30
±0.30	±0.50	±0.70
±1.00	±1.30	±2°

NOTES1:
UL Standard

1 Use group	B	C	D
Rated Current	20A	/	/
Rated Voltage	300V	/	/


2 Torque value: M3, 4.43Lb.in
3 Wire range: 22~12AWG

IEC Standard

1 Pollution Degree	3	2	2
Overvoltage Category	III	III	II
Rate Impulse Voltage(KV)	/	/	/
Rate Voltage(V)	/	400V	/
Rate Current(A)	/	17.5A	/

- NOTES2:
- Housing: PA66(UL94V-0)
 - Solder Pin: Copper alloy(Sn Plated)
 - Screw: Steel(M3, Ni Plated)
- NOTES3:
- Pitch: 8.25mm Poles: 02-24P
 - Operating temperature: -4.0°C~+105°C
 - RoHS Compliance

How to order



ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTE
DWG	CHK	DATE	UNITS	MM	SHEET/OF 1/1
APP	DATE	SCALE	1:1	A4	1/1
CIXI MAIXU ELECTRONICS CO.,LTD			NAME	HB825-8.25-XXP	
东莞市迈旭电子有限公司			DWGNO.		