





SEC :A-A




安装示意图



适用扁平电缆
Proper cable



反针印制线路板
PCB P.C.B Layout



正针印制线路板
PCB P.C.B Layout

- 1.FPC NOT MATING CONDITION BANNED CLOSURE
- 2.PART NO. LEGEND:

10C55V XX T X
① ② ③ ④

- ① Series Name : 10C55V=1.0 mm Pitch(H=5.5mm)Direction 180°
- ② Number of terminals :XX=04-36PIN
- ③ Plating : T:Plated Tin
- ④ Z:positive needle F: negative needle

- 3.PERFORMANCE
- 3.1:CURRENT RATING:0.4A/PIN.
- 3.2: VOLTAGE RATING: 200V (AC/DC)
- 3.3:CONTACT RESISTANCE: INITIAL VALUE 20mΩ Max
- 3.4: INSULATION RESISTANCE: 500MOHM Min.
- 3.5: DIELECTRIC WITHSTANDING VOLTAGE: 200V AC FOR 1MINUTE
- 3.6:DURABILITY: 20 TIMES Min
- 3.7:OPERATING TEMPERATURE:-40°C--+125°C
- OPERATING HUMIDITY RANGE:20% TO 85%
- Terminal Material:The Lin copper plates Tin
- Housing Material: PA9T UL 94V-0

NO.OF CKF	DIMA	DIMB	DIMC
4	3.00	5.10	7.00
5	4.00	6.20	8.00
6	5.00	7.10	9.00
7	6.00	8.10	10.00
8	7.00	9.10	11.00
9	8.00	10.10	12.00
10	9.00	11.10	13.00
11	10.00	12.10	14.00
12	11.00	13.10	15.00
13	12.00	14.10	16.00
14	13.00	15.10	17.00
15	14.00	16.10	18.00
16	15.00	17.10	19.00
17	16.00	18.10	20.00
18	17.00	19.10	21.00
19	18.00	20.10	22.00
20	19.00	21.10	23.00
21	20.00	22.10	24.00
22	21.00	23.10	25.00
23	22.00	24.10	26.00
24	23.00	25.10	27.00
25	24.00	26.10	28.00
26	25.00	27.10	29.00
27	26.00	28.10	30.00
28	27.00	29.00	31.00
29	28.00	30.10	32.00
30	29.00	31.10	33.00
31	30.00	32.10	34.00
32	31.00	33.10	35.00
33	32.00	34.10	36.00
34	33.00	35.10	37.00
35	34.00	36.10	38.00
36	35.00	37.10	39.00

new		2015/5/3		A	
ECN BO.		DESCRIPTION.		REV.	
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER	SCALT: 1/2	SCALE: 3:1
Mikey	Tom	Jerry	PART NAME 10C55VXXTX	UNLESS OTHERWISE SPECIFIED,TOLERANCE:	X. ±0.25 X.x ±0.20 X.xx ±0.15 ANGULAIR ±3
			MODEL NAME 10C55VXXTX		FILE.NO.
			3RD ANGLE PROJ	HanElectricity Co.,LTD	

瀚源