

May 2007

74ACTQ153 Quiet Series Dual 4-Input Multiplexer

Features

- Outputs source/sink 24mA
- ACTQ153 has TTL-compatible inputs
- Guaranteed simultaneous switching noise level and dynamic threshold performance
- Improved latch-up immunity

General Description


The ACTQ153 is a high-speed dual 4-input multiplexer with common select inputs and individual enable inputs for each section. It can select two lines of data from four sources. The two buffered outputs present data in the true (non-inverted) form. In addition to multiplexer operation, the ACTQ153 can act as a function generator and generate any two functions of three variables.

Ordering Information

Order Number	Package Number	Package Description
74ACTQ153SC	M16A	16-Lead Small Outline Integrated Circuit (SOIC), JEDEC MS-012, 0.150" Narrow

Device also available in Tape and Reel. Specify by appending suffix letter "X" to the ordering number.


Connection Diagram




Pin Description

Pin Names	Description
I _{0a} –1 _{3a}	Side A Data Inputs
I _{0b} -1 _{3b}	Side B Data Inputs
S ₀ , S ₁	Common Select Inputs
Ēa	Side A Enable Input
Ē _b	Side B Enable Input
Z _a	Side A Output
Z _b	Side B Output

Logic Symbols





FACT™, FACT Quiet Series™, and GTO™ are trademarks of Fairchild Semiconductor Corporation.

Functional Description

The ACTQ153 is a dual 4-input multiplexer. It can select two bits of data from up to four sources under the control of the common Select inputs $(S_0,\,S_1)$. The two 4-input multiplexer circuits have individual active-LOW Enables $(\overline{E}_a,\,\overline{E}_b)$ which can be used to strobe the outputs independently. When the Enables $(\overline{E}_a,\,\overline{E}_b)$ are HIGH, the corresponding outputs $(A_z,\,Z_b)$ are forced LOW. The ACTQ153 is the logic implementation of a 2-pole, 4-position switch, where the position of the switch is determined by the logic levels supplied to the Select inputs. The logic equations for the outputs are shown below.

$$\begin{split} Z_a &= \overline{E}_a \bullet (I_{0a} \bullet \overline{S}_1 \bullet \overline{S}_0 + I_{1a} \bullet \overline{S}_1 \bullet S_0 + \\ I_{2a} \bullet S_1 \bullet \overline{S}_0 + I_{3a} \bullet S_1 \bullet S_0) \end{split}$$

$$\begin{split} Z_b &= \overline{E}_b \bullet (I_{0\underline{b}} \bullet \overline{S}_1 \bullet \overline{S}_0 \bullet I_{1b} \bullet \overline{S}_1 \bullet S_0 + \\ I_{2b} \bullet S_1 \bullet \overline{S}_0 + I_{3b} \bullet S_1 \bullet S_0) \end{split}$$

Truth Table


Select Inputs			Inputs (a or b)				Outputs
S ₀	S ₁	Е	I ₀	I ₁	l ₂	l ₃	Z
Х	Х	Н	Х	Х	Х	Х	L
L	L	L	L	Х	Х	Х	L
L	L	L	Н	Х	Х	Х	Н
Н	L	L	Х	L	Х	Х	L
Н	L	L	Х	Н	Х	Х	Н
L	Н	L	Х	Х	L	Х	L
L	Н	L	Х	Х	Н	Х	Н
Н	Н	L	Х	Х	Х	L	L
Н	Н	L	Х	Х	Х	Н	Н

H = HIGH Voltage Level

L = LOW Voltage Level

X = Immaterial

Logic Diagram



Please note that this diagram is provided only for the understanding of logic operations and should not be used to estimate propagation delays.

Absolute Maximum Ratings

Stresses exceeding the absolute maximum ratings may damage the device. The device may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only.

Symbol	Parameter	Rating
V _{CC}	Supply Voltage	-0.5V to +7.0V
I _{IK}	DC Input Diode Current	
	$V_{I} = -0.5V$	–20mA
	$V_{I} = V_{CC} + 0.5V$	+20mA
V _I	DC Input Voltage	-0.5V to V _{CC} + 0.5V
lok	DC Output Diode Current	
	$V_{O} = -0.5V$	–20mA
	$V_{O} = V_{CC} + 0.5V$	+20mA
Vo	DC Output Voltage	-0.5V to V _{CC} + 0.5V
Io	DC Output Source or Sink Current	±50mA
I _{CC} or I _{GND}	DC V _{CC} or Ground Current per Output Pin	±50mA
T _{STG}	Storage Temperature -65°C	
	DC Latch-Up Source or Sink Current	±300mA
TJ	Junction Temperature	140°C

Recommended Operating Conditions

The Recommended Operating Conditions table defines the conditions for actual device operation. Recommended operating conditions are specified to ensure optimal performance to the datasheet specifications. Fairchild does not recommend exceeding them or designing to absolute maximum ratings.

Symbol	Parameter	Rating
V _{CC}	Supply Voltage	4.5V to 5.5V
VI	Input Voltage	0V to V _{CC}
Vo	Output Voltage	0V to V _{CC}
T _A	Operating Temperature	-40°C to +85°C
ΔV / Δt	Minimum Input Edge Rate:	125mV/ns
	V _{IN} from 0.8V to 2.0V, V _{CC} @ 4.5V, 5.5V	

DC Electrical Characteristics

				$T_A = -$	+25°C	T _A = -40°C to +85°C	
Symbol	Parameter	V _{CC} (V)	Conditions	Тур.	G	uaranteed Limits	Units
V _{IH}	Minimum HIGH Level	4.5	V _{OUT} = 0.1V	1.5	2.0	2.0	V
	Input Voltage	5.5	or V _{CC} – 0.1V	1.5	2.0	2.0	
V _{IL}	Maximum LOW Level	4.5	V _{OUT} = 0.1V	1.5	0.8	0.8	V
	Input Voltage	5.5	or V _{CC} – 0.1V	1.5	0.8	0.8	
V _{OH}	Minimum HIGH Level	4.5	$I_{OUT} = -50\mu A$	4.49	4.4	4.4	V
	Output Voltage	5.5		5.49	5.4	5.4	
			$V_{IN} = V_{IL}$ or V_{IH} :				
		4.5	$I_{OH} = -24mA$		3.86	3.76	
		5.5	$I_{OH} = -24 \text{mA}^{(1)}$		4.86	4.76	
V_{OL}	Maximum LOW Level	4.5	$I_{OUT} = 50\mu A$	0.001	0.1	0.1	V
	Output Voltage	5.5		0.001	0.1	0.1	
			$V_{IN} = V_{IL}$ or V_{IH} :				
		4.5	I _{OL} = 24mA		0.36	0.44	
		5.5	$I_{OL} = 24 \text{mA}^{(1)}$		0.36	0.44	
I _{IN}	Maximum Input Leakage Current	5.5	$V_I = V_{CC}$, GND		±0.1	±1.0	μA
I _{CCT}	Maximum I _{CC} /Input	5.5	$V_I = V_{CC} - 2.1V$	0.6		1.5	μA
I _{OLD}	Minimum Dynamic	5.5	V _{OLD} = 1.65V Max.			75	mA
I _{OHD}	Output Current ⁽²⁾	5.5	V _{OHD} = 3.85V Min.			– 75	mA
I _{CC}	Maximum Quiescent Supply Current	5.5	$V_{IN} = V_{CC}$ or GND		8.0	80.0	μA
V _{OLP}	Maximum HIGH Level Output Noise	5.0	Figures 1 & 2 ⁽³⁾⁽⁴⁾	1.1	1.5		V
V _{OLV}	Maximum LOW Level Output Noise	5.0	Figures 1 & 2 ⁽³⁾⁽⁴⁾	-0.6	-1.2		V
V_{IHD}	Minimum HIGH Level Dynamic Input Voltage	5.0	(3)(5)	1.9	2.2		V
V_{ILD}	Maximum LOW Level Dynamic Input Voltage	5.0	(3)(5)	1.2	0.8		V

Notes:

- 1. All outputs loaded; thresholds on input associated with output under test.
- 2. Maximum test duration 2.0ms, one output loaded at a time.
- 3. Worst case package.
- 4. Max number of outputs defined as (n). Data Inputs are driven 0V to 5V. One Data Input @ $V_{IN} = GND$.
- 5. Max number of Data Inputs (n) switching. (n–1) inputs switching 0V to 5V. Input-under-test switching: 5V to threshold (V_{ILD}) , 0V to threshold (V_{IHD}) , f = 1MHz.

AC Electrical Characteristics

				T _A = +25°C, C _L = 50pF		$T_A = -40$ °C to +85°C, $C_L = 50$ pF		
Symbol	Parameter	$V_{CC}(V)^{(6)}$	Min.	Тур.	Max.	Min.	Max.	Units
t _{PLH}	Propagation Delay, S _n to Z _n	5.0	3.0	7.0	11.5	2.0	13.5	ns
t _{PHL}	Propagation Delay, S _n to Z _n	5.0	3.0	7.0	11.5	2.5	13.5	ns
t _{PLH}	Propagation Delay, \overline{E}_n to Z_n	5.0	2.0	6.5	10.5	2.0	12.5	ns
t _{PHL}	Propagation Delay, \overline{E}_n to Z_n	5.0	3.0	6.0	9.5	2.5	11.0	ns
t _{PLH}	Propagation Delay, I _n to Z _n	5.0	2.5	5.5	9.5	2.0	11.0	ns
t _{PHL}	Propagation Delay, I _n to Z _n	5.0	2.0	5.5	9.5	2.0	11.0	ns

Note:

6. Voltage range 5.0 is 5.0V \pm 0.5V.

Capacitance

Symbol	Parameter	Conditions	Тур.	Units
C _{IN}	Input Capacitance	V _{CC} = 5.0V	4.5	pF
C _{PD}	Power Dissipation Capacitance	V _{CC} = 5.0V	65.0	pF

FACT Noise Characteristics

The setup of a noise characteristics measurement is critical to the accuracy and repeatability of the tests. The following is a brief description of the setup used to measure the noise characteristics of FACT.

Equipment:


Hewlett Packard Model 8180A Word Generator

PC-163A Test Fixture

Tektronics Model 7854 Oscilloscope

Procedure:

- 1. Verify Test Fixture Loading: Standard Load 50pF, 500Ω .
- Deskew the HFS generator so that no two channels have greater than 150 ps skew between them. This requires that the oscilloscope be deskewed first. It is important to deskew the HFS generator channels before testing. This will ensure that the outputs switch simultaneously.
- Terminate all inputs and outputs to ensure proper loading of the outputs and that the input levels are at the correct voltage.
- Set the HFS generator to toggle all but one output at a frequency of 1 MHz. Greater frequencies will increase DUT heating and effect the results of the measurement.
- Set the HFS generator input levels at 0V LOW and 3V HIGH for ACT devices and 0V LOW and 5V HIGH for AC devices. Verify levels with an oscilloscope.



Notes:

- V_{OHV} and V_{OLP} are measured with respect to ground reference
- 8. Input pulses have the following characteristics: f = 1MHz, $t_r = 3ns$, $t_f = 3ns$, skew < 150ps.

Figure 1. Quiet Output Noise Voltage Waveforms

V_{OLP}/V_{OLV} and V_{OHP}/V_{OHV}:

- Determine the quiet output pin that demonstrates the greatest noise levels. The worst case pin will usually be the furthest from the ground pin. Monitor the output voltages using a 50Ω coaxial cable plugged into a standard SMB type connector on the test fixture. Do not use an active FET probe.
- Measure V_{OLP} and V_{OLV} on the quiet output during the worst case transition for active and enable.
 Measure V_{OHP} and V_{OHV} on the quiet output during the worst case active and enable transition.
- Verify that the GND reference recorded on the oscilloscope has not drifted to ensure the accuracy and repeatability of the measurements.

VILD and VIHD:

- Monitor one of the switching outputs using a 50Ω coaxial cable plugged into a standard SMB type connector on the test fixture. Do not use an active FET probe.
- First increase the input LOW voltage level, V_{IL}, until the output begins to oscillate or steps out a min of 2ns. Oscillation is defined as noise on the output LOW level that exceeds V_{IL} limits, or on output HIGH levels that exceed V_{IH} limits. The input LOW voltage level at which oscillation occurs is defined as V_{II D}.
- Next decrease the input HIGH voltage level, V_{IH}, until the output begins to oscillate or steps out a min of 2ns. Oscillation is defined as noise on the output LOW level that exceeds V_{IL} limits, or on output HIGH levels that exceed V_{IH} limits. The input HIGH voltage level at which oscillation occurs is defined as V_{IHD}.
- Verify that the GND reference recorded on the oscilloscope has not drifted to ensure the accuracy and repeatability of the measurements.







Figure 2. Simultaneous Switching Test Circuit

Physical Dimensions

Dimensions are in inches (millimeters) unless otherwise noted.







M16AREVK

Figure 3. 16-Lead Small Outline Integrated Circuit (SOIC), JEDEC MS-012, 0.150" Narrow Package Number M16A





TRADEMARKS

The following are registered and unregistered trademarks Fairchild Semiconductor owns or is authorized to use and is not intended to be an exhaustive list of all such trademarks.

ACFx® i-Lo™ Across the board. Around the world.™ ImpliedDisconnect™ ActiveArray[™] IntelliMAX™ Bottomless™ ISOPLANAR™ Build it Now™ MICROCOUPLER™ CoolFET™ MicroPak™ CROSSVOLT™ MICROWIRE™ $\mathsf{CTL^{\mathsf{TM}}}$ Motion-SPM™ Current Transfer Logic™ MSX™ DOME™ MSXPro™ E²CMOS™ OCX^{TM} EcoSPARK®

OCXPro™ EnSigna™ OPTOLOGIC® FACT Quiet Series™ OPTOPLANAR® FACT[®] PACMAN™ FAST® PDP-SPM™ FASTr™ РОР™ FPS™ Power220® FRFET® Power247® GlobalOptoisolator™ PowerEdge™ GTO™

PowerSaver™ HiSeC™

Power-SPM™ PowerTrench®

Programmable Active Droop™ QFĚT QS™ QT Optoelectronics™ Quiet Series™ RapidConfigure™ RapidConnect™ ScalarPump™

SMART START™ SPM[®] STEALTH™ SuperFET™ SuperSOT™3 SuperSOT™6 SuperSOT™8 SyncFET™ ТСМ™

The Power Franchise®

TinyBuck™ TinyLogic[®] TINYOPTO™ TinyPower™ TinyWire™ TruTranslation™ μSerDes™ . UHC® UniFET™ VCX™ Wire™

TinyBoost™

DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS. NOR THE RIGHTS OF OTHERS. THESE SPECIFICATIONS DO NOT EXPAND THE TERMS OF FAIRCHILD'S WORLDWIDE TERMS AND CONDITIONS, SPECIFICALLY THE WARRANTY THEREIN, WHICH COVERS THESE PRODUCTS.

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION.

- 1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
 - 2. A critical component in any component of a life support, device, or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

PRODUCT STATUS DEFINITIONS

Definition of Terms

Datasheet Identification	Product Status	Definition
Advance Information	Formative or In Design	This datasheet contains the design specifications for product development. Specifications may change in any manner without notice.
Preliminary	First Production	This datasheet contains preliminary data; supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve design.
No Identification Needed	Full Production	This datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve design.
Obsolete	Not In Production	This datasheet contains specifications on a product that has been discontinued by Fairchild Semiconductor. The datasheet is printed for reference information only.

Rev. 126