



# SURFACE MOUNT SUPER FAST RECOVERY RECTIFIER

## E1A THRU E1J

VOLTAGE RANGE

50 to 600 Volts

CURRENT

1.0 Ampere



## Features

- Fast recovery glass passivated: chip 46mil
- Low forward voltage drop
- Low leakage current
- High forward surge capability
- High temperature soldering: 260°C/10S at terminals
- Component in accordance to RoHS 2002/95/1 and WEEE 2002/96/EC



## Mechanical Data

- Case: JEDEC SOD-123FL mold plastic  
Body over glass passivated chip
- Terminals: Solder plated, solderable per J-STD-002B and JESD22-B102D
- Polarity: Laser band denote cathode band
- Weight: 0.00063ounce, 0.018grams



## Maximum Ratings and Electrical Characteristics

- Ratings at 25°C ambient temperature unless otherwise specified
- Single Phase, half wave, 60Hz, resistive or inductive load
- For capacitive load derate current by 20%

TYPE NUMBER	SYMBOL	E1A	E1B	E1C	E1D	E1F	E1G	E1J	UNIT
Maximum Repetitive Peak Reverse Voltage	$V_{RRM}$	50	100	150	200	300	400	600	Volts
Maximum RMS Voltage	$V_{RMS}$	35	70	105	140	210	280	420	Volts
Maximum DC Blocking Voltage	$V_{DC}$	50	100	150	200	300	400	600	Volts
Maximum Average Forward Rectified Current At $T_A=100^\circ\text{C}$	$I_{(AV)}$	1.0							Amps
Peak Forward Surge Current 8.3ms single half sine wave superimposed on rated load (JEDEC Method)	$I_{FSM}$	30							Amps
Maximum Instantaneous Forward Voltage at 1.0A	$V_F$	0.95			1.25		1.70		Volts
Maximum DC Reverse Current at rated DC blocking voltage at	$T_A = 25^\circ\text{C}$	5.0							$\mu\text{Amps}$
	$T_A = 125^\circ\text{C}$	100							
Maximum Reverse Recovery Time <sup>(NOTE 1)</sup>	$T_{RR}$	35							nS
Typical Junction Capacitance <sup>(NOTE 3)</sup>	$C_j$	10			8				pF
Typical Thermal Resistance <sup>(NOTE 2)</sup>	$R_{\theta JA}$	60							$^\circ\text{C/W}$
	$R_{\theta JL}$	28							
Operating Junction Temperature	$T_J$	-55 to +150							$^\circ\text{C}$
Storage Temperature Range	$T_{STG}$	-55 to +150							$^\circ\text{C}$

Notes:

1. Reverse Recovery Test Conditions:  $I_f=0.5A, I_r=1.0A, I_{rr}=0.25A$ .
2. Polyimide PCB, 0.043"×0.047"(1.10mm×1.20mm). Copper, minimum recommended pad layout per.
3. Measured at 1.0MHz and applied reverse voltage of 4.0V.



# SURFACE MOUNT SUPER FAST RECOVERY RECTIFIER

## E1A THRU E1J

VOLTAGE RANGE

50 to 600 Volts

CURRENT

1.0 Ampere

Ratings and Characteristic Curves ( $T_A=25^\circ\text{C}$  unless otherwise noted)

FIG.1-TYPICAL FORWARD CURRENT DERATING CURVE




FIG.2-MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT




FIG.3-TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS




FIG.4-TYPICAL REVERSE CHARACTERISTICS




FIG.5-TYPICAL JUNCTION CAPACITANCE






FIG.6-TEST CIRCUIT DIAGRAM AND REVERSE RECOVERY TIME CHARACTERISTIC



- NOTES : 1. Rise Time=7ns max. Input Impedance= 1 magohm. 22pF  
2. Rise time=10ns max. Source Impedance= 50 ohms

SET TIME BASE FOR 50/100ns/cm



SURFACE MOUNT SUPER FAST RECOVERY RECTIFIER

E1A THRU E1J

VOLTAGE RANGE

50 to 600 Volts


CURRENT

1.0 Ampere

Package Outline Dimensions in inches (millimeters)


SOD-123FL

Unit: mm



UNIT		A	C	D	E	e	g	H <sub>E</sub>	$\angle$
mm	max	1.1	0.20	2.9	1.9	1.1	0.9	3.8	7°
	min	0.9	0.12	2.6	1.7	0.8	0.7	3.5	
mil	max	43	7.9	114	75	43	35	150	
	min	35	4.7	102	67	31	28	138	

The recommended mounting pad size





# SURFACE MOUNT SUPER FAST RECOVERY RECTIFIER

E1A THRU E1J

VOLTAGE RANGE


50 to 600 Volts

CURRENT

1.0 Ampere


## Packing Requirments

- PS black anti-static carrier tape packing



Specifications	Ao	Bo	Ko	Po	W	t1
SOD123FL	2.12±0.10	3.95±0.10	1.35±0.10	4.00±0.1	8.0±0.10	0.20±0.02

- 7 "antistatic plastic reel



DEVICE TYPE	07" Reel			
	Q'TY/REEL(pcs)	REEL/BOX	BOX/CARTOON	Q'TY/CARTON(pcs)
SOD123FL	3000	4	16	192000



SURFACE MOUNT SUPER FAST RECOVERY RECTIFIER

E1A THRU E1J


VOLTAGE RANGE

50 to 600 Volts

CURRENT

1.0 Ampere

Reflow Profile



Reflow Condition		Pb-Free Assembly
Pre Heat	Temperature Min.	+150°C
	Temperature Max.	+200°C
	Time(Min to Max)	60-180 secs.
Average ramp up rate(Liquidus Temp( $T_L$ ) to peak)		3°C/sec. Max.
$T_S(max)$ to $T_L$ - Ramp-up Rate		3°C/sec. Max.
Reflow	Temperature ( $T_L$ )(Liquidus)	+217°C
	Temperature ( $T_I$ )	60-150 secs.
Peak Temp ( $T_P$ )		+(260+0/-5)°C
Time within 5°C of actual Peak Temp ( $T_P$ )		25 secs.
Ramp-down Rate		6°C/sec. Max.
Time 25°C to peak Temp ( $T_P$ )		8 min. Max.
Do not exceed		+260°C



## SURFACE MOUNT SUPER FAST RECOVERY RECTIFIER

E1A THRU E1J

VOLTAGE RANGE	50 to 600 Volts
CURRENT	1.0 Ampere

### Disclaimer

The information presented in this document is for reference only. Chongqing changjie Electronic Technology Co., Ltd. reserves the right to make changes without notice for the specification of the products displayed herein to improve reliability, function or design or otherwise.

The product listed herein is designed to be used with ordinary electronic equipment or devices, and not designed to be used with equipment or devices which require high level of reliability and the malfunction of which would directly endanger human life (such as medical instruments, transportation equipment, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), Changjie or anyone on its behalf, assumes no responsibility or liability for any damages resulting from such improper use of sale.

This publication supersedes & replaces all information previously supplied. For additional information, please visit our website [http:// www.czlangjie.com](http://www.czlangjie.com) , or consult your nearest Langjie's sales office for further assistance.