

# mXT336UD-MAUHA1 1.0

## maXTouch 336-node Touchscreen Controller Product Brief

## Description

The mXT336UD-MAUHA1 1.0 uses a unique charge-transfer acquisition engine to implement Microchip's patented capacitive sensing method. Coupled with a state-of-the-art CPU, the entire touchscreen sensing solution can measure, classify and track a number of individual finger touches with a high degree of accuracy in the shortest response time. The mXT336UD-MAUHA1 1.0 allows for both mutual and self capacitance measurements, with the self capacitance measurements being used to augment the mutual capacitance measurements to produce reliable touch information.

### **Functional Safety**

- UL/IEC 60730 Class B support
- Self diagnostics at power-on and as periodic tests during operation
- Heartbeat (alive) signal output to host
- · Safety manual available

# maXTouch<sup>®</sup> Adaptive Sensing Touchscreen Technology

- Up to 14 X (transmit) lines and 24 Y (receive) lines for use by a touchscreen
- A maximum of 336 nodes can be allocated to the touch sensor
- Touchscreen size of 7.11 inches (16:9 aspect ratio), assuming a sensor electrode pitch of 6.5 mm. Other sizes are possible with different electrode pitches and appropriate sensor material
- Multiple touch support with up to 10 concurrent touches tracked in real time

## **Touch Sensor Technology**

- Discrete/out-cell support including glass and PET filmbased sensors
- On-cell/touch-on display support including TFT, LCD (ITPS, IPS) and OLED
- Synchronization with display refresh timing capability
- Support for standard (for example, Diamond) and proprietary sensor patterns (review of designs by Microchip or a Microchip-qualified touch sensor module partner is recommended)

### Front Panel Material and Design

- Works with PET or glass, including curved profiles (configuration and stack-up to be approved by Microchip or a Microchip-qualified touch sensor module partner)
- 10 mm glass (or 5 mm PMMA) with bare finger (dependent on screen size, touch size, configuration and stack-up)
- 6 mm glass (or 3 mm PMMA) with multi-finger 5 mm glove (2.7 mm PMMA equivalent) (dependent on screen size, touch size, configuration and stack-up)
- Support for non-rectangular sensor designs (for example, circular, rounded or with cutouts)

### **Touch Performance**

- Moisture/Water Compensation
  - No false touch with condensation or water drop up to 22 mm diameter
  - One-finger tracking with condensation or water drop up to 22 mm diameter
- Mutual capacitance and self capacitance
   measurements supported for robust touch detection
- P2P mutual capacitance measurements supported for extra sensitive multi-touch sensing
- Noise suppression technology to combat ambient, charger, and power-line noise
  - Up to 240  $V_{\mbox{\scriptsize PP}}$  between 1 Hz and 1 kHz sinusoidal waveform
  - Up to 20 V<sub>PP</sub> between 1 kHz and 1 MHz sinusoidal waveform
- Burst Frequency
  - Controlled Tx burst frequency drift over process and temperature range

- Scan Speed
  - Typical report rate for 10 touches ≥70 Hz (subject to configuration)
  - Initial touch latency <18 ms for first touch from idle (subject to configuration)
  - Configurable to allow for power and speed optimization

## **Enhanced Algorithms**

- · Lens bending algorithms to remove display noise
- · Touch suppression algorithms to remove unintentional large touches, such as palm
- Palm Recovery Algorithm for quick restoration to normal state

### **Power Saving**

- Programmable timeout for automatic transition from Active to Idle state
- · Pipelined analog sensing detection and digital processing to optimize system power efficiency

## **Application Interfaces**

- I<sup>2</sup>C interface with support for Standard mode (up to 100 kHz), Fast mode (up to 400 kHz), Fast-mode Plus (up to 1 MHz)
- Interrupt to indicate when a message is available
- Additional SPI Debug Interface to read the raw data for tuning and debugging purposes

## **Power Supply**

- Digital (Vdd) 3.3V nominal
- Digital I/O (VddIO) 3.3V nominal
- Analog (AVdd) 3.3V nominal
- High voltage internal X line drive (XVdd) 6.6V with internal voltage pump (XVdd connected to AVdd if voltage pump not used)

## Package

• 56-pin XQFN 6 × 6 × 0.4 mm, 0.35 mm pitch

### **Operating Temperature**


• −40°C to +85°C

### **Design Services**

- Review of device configuration, stack-up and sensor patterns
- · Custom firmware versions can be considered

## **PIN CONFIGURATION**


Pin Configuration – 56-pin XQFN



## 1.0 PACKAGING INFORMATION

## 1.1 Package Marking Information

1.1.1 56-PIN XQFN




## 1.1.2 ORDERABLE PART NUMBERS

The product identification system for maXTouch devices is described in "Product Identification System". That section also lists example part numbers for the device.

## 1.2 Package Details


## 56-Lead Extremely Thin Quad Flatpack No-Lead Package (TWB) - 6x6x0.4 mm Body [XQFN] With 4.5x4.5 mm Exposed Pad; Atmel Legacy Global Package Code ZIX



Microchip Technology Drawing C04-21448 Rev A Sheet 1 of 2

## 56-Lead Extremely Thin Quad Flatpack No-Lead Package (TWB) - 6x6x0.4 mm Body [XQFN] With 4.5x4.5 mm Exposed Pad; Atmel Legacy Global Package Code ZIX

**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



|                         | Units                 |      | MILLIMETERS |       |  |  |
|-------------------------|-----------------------|------|-------------|-------|--|--|
| Dimension               | Limits                | MIN  | NOM         | MAX   |  |  |
| Number of Terminals     | lumber of Terminals N |      | 56          |       |  |  |
| Pitch                   | е                     |      | 0.35 BSC    |       |  |  |
| Overall Height          | Α                     | -    | -           | 0.400 |  |  |
| Standoff                | A1                    | 0.00 | -           | 0.05  |  |  |
| Terminal Thickness      | A3                    |      | 0.127 REF   |       |  |  |
| Overall Length          | D                     |      | 6.00 BSC    |       |  |  |
| Exposed Pad Length      | D2                    | 4.40 | 4.50        | 4.60  |  |  |
| Overall Width           | Е                     |      | 6.00 BSC    |       |  |  |
| Exposed Pad Width       | E2                    | 4.40 | 4.50        | 4.60  |  |  |
| Terminal Width          | b                     | 0.13 | 0.18        | 0.23  |  |  |
| Terminal Length         | L                     | 0.35 | 0.40        | 0.45  |  |  |
| Terminal-to-Exposed-Pad | K                     |      | 0.35 REF    |       |  |  |

Notes:

1. Pin 1 visual index feature may vary, but must be located within the hatched area.


- 2. Package is saw singulated
- 3. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances. REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-21448 Rev A Sheet 2 of 2

## 56-Lead Extremely Thin Quad Flatpack No-Lead Package (TWB) - 6x6x0.4 mm Body [XQFN] With 4.5x4.5 mm Exposed Pad; Atmel Legacy Global Package Code ZIX

**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



## RECOMMENDED LAND PATTERN

|                                  | MILLIMETERS     |      |          |      |  |
|----------------------------------|-----------------|------|----------|------|--|
| Dimension                        | MIN             | NOM  | MAX      |      |  |
| Contact Pitch                    | Contact Pitch E |      | 0.35 BSC |      |  |
| Optional Center Pad Width        | X2              |      |          | 4.60 |  |
| Optional Center Pad Length       | Y2              |      |          | 4.60 |  |
| Contact Pad Spacing              | C1              |      | 5.90     |      |  |
| Contact Pad Spacing              | C2              |      | 5.90     |      |  |
| Contact Pad Width (X56)          | X1              |      |          | 0.15 |  |
| Contact Pad Length (X56)         | Y1              |      |          | 0.85 |  |
| Contact Pad to Center Pad (X56)  | G1              | 0.23 |          |      |  |
| Contact Pad to Contact Pad (X52) | G2              | 0.20 |          |      |  |
| Thermal Via Diameter             | V               |      | 0.33     |      |  |
| Thermal Via Pitch                | EV              |      | 1.20     |      |  |

Notes:

- 1. Dimensioning and tolerancing per ASME Y14.5M
  - BSC: Basic Dimension. Theoretically exact value shown without tolerances.
- 2. For best soldering results, thermal vias, if used, should be filled or tented to avoid solder loss during reflow process

Microchip Technology Drawing C04-23448 Rev A

## APPENDIX A: REVISION HISTORY

## Revision A (October 2020)

Initial edition for firmware revision 1.0.AB - Release

## **PRODUCT IDENTIFICATION SYSTEM**

The table below gives details on the product identification system for maXTouch devices. See "Orderable Part Numbers" below for example part numbers for the mXT336UD-MAUHA1.

To order or obtain information, for example on pricing or delivery, refer to the factory or the listed sales office.

|                       | PART NO. | - <u>xxx</u>  | -     |                     |                         |                        |  |
|-----------------------|----------|---|-------|---------------------|-------------------------|------------------------|--|
|                       | Device   | Package   | 16    | emperature<br>Range | Tape and<br>Reel Option | Pattern                |  |
| Device:               |          | Base devic  | e nan | ne                  |                         |                        |  |
| Package:              |          | А   | =     | QFP (Plas           | tic Quad Flatpac        | k)                     |  |
|                       |          | CC  | =     | UFBGA (L            | Iltra Thin Fine-pit     | tch Ball Grid Array)   |  |
|                       |          | C2  | =     | UFBGA (L            | Iltra Thin Fine-pit     | tch Ball Grid Array)   |  |
|                       |          | NH  | =     | UFBGA (L            | Iltra Thin Fine-pit     | tch Ball Grid Array)   |  |
|                       |          | C4  | =     | X1FBGA (            | Extra Thin Fine-p       | oitch Ball Grid Array) |  |
|                       |          | MA  | =     | XQFN (Su            | per Thin Quad F         | lat No Lead Sawn)      |  |
|                       |          | MA5   | =     | XQFN (Su            | per Thin Quad F         | lat No Lead Sawn)      |  |
| Temperature Range:    | je:      | U   | =     | –40°C to +          | -85°C (Grade 3)         |                        |  |
|                       |          | Т   | =     | –40°C to +          | -85°C (Grade 3)         |                        |  |
|                       |          | В   | =     | –40°C to +          | -105°C (Grade 2)        | )                      |  |
| Tape and Reel Option: | tion:    | Blank   | =     |                     | Packaging (Tube         | or Tray)               |  |
|                       |          | R   | =     | Tape and I          | Reel <sup>(1)</sup>     |                        |  |
| Pattern:              |          | Extension, QTP, SQTP, Code or Special Requirements<br>(Blank Otherwise) |       |                     |                         |                        |  |

check with your Microchip Sales Office for package availability with the Tape and Reel option.

### **Orderable Part Numbers**

| Orderable Part Number                             | Firmware Revision | Description  |
|---|-------------------|--|
| ATMXT336UD-MAUHA1<br>(Supplied in trays)          | 1.0.AB            | 56-pin XQFN 6 $\times$ 6 $\times$ 0.4 mm, RoHS compliant<br>Industrial grade; not suitable for automotive characterization |
| ATMXT336UD-MAURHA1<br>(Supplied in tape and reel) |                   |  |

NOTES:

#### Note the following details of the code protection feature on Microchip devices:

- Microchip products meet the specifications contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is secure when used in the intended manner and under normal conditions.
- There are dishonest and possibly illegal methods being used in attempts to breach the code protection features of the Microchip devices. We believe that these methods require using the Microchip products in a manner outside the operating specifications contained in Microchip's Data Sheets. Attempts to breach these code protection features, most likely, cannot be accomplished without violating Microchip's intellectual property rights.
- Microchip is willing to work with any customer who is concerned about the integrity of its code.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of its code. Code protection does not mean that
  we are guaranteeing the product is "unbreakable." Code protection is constantly evolving. We at Microchip are committed to continuously
  improving the code protection features of our products. Attempts to break Microchip's code protection feature may be a violation of the
  Digital Millennium Copyright Act. If such acts allow unauthorized access to your software or other copyrighted work, you may have a right
  to sue for relief under that Act.

Information contained in this publication is provided for the sole purpose of designing with and using Microchip products. Information regarding device applications and the like is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications.

THIS INFORMATION IS PROVIDED BY MICROCHIP "AS IS". MICROCHIP MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION INCLUDING BUT NOT LIMITED TO ANY IMPLIED WARRANTIES OF NON-INFRINGEMENT, MERCHANTABILITY, AND FITNESS FOR A PARTICULAR PURPOSE OR WARRANTIES RELATED TO ITS CONDITION, QUALITY, OR PERFORMANCE.

IN NO EVENT WILL MICROCHIP BE LIABLE FOR ANY SPECIAL, PUNITIVE, INCIDENTAL INDIRECT, OR CONSEQUENTIAL LOSS, DAMAGE, COST OR EXPENSE OF ANY KIND WHATSOEVER RELATED TO THE INFORMATION OR ITS USE, HOWEVER CAUSED, EVEN IF MICROCHIP HAS BEEN ADVISED OF THE POSSIBILITY OR THE DAMAGES ARE FORESEEABLE. TO THE FULLEST EXTENT ALLOWED BY LAW, MICROCHIP'S TOTAL LIABILITY ON ALL CLAIMS IN ANY WAY RELATED TO THE INFORMATION OR ITS USE WILL NOT EXCEED THE AMOUNT OF FEES, IF ANY, THAT YOU HAVE PAID DIRECTLY TO MICROCHIP FOR THE INFORMATION. Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights unless otherwise stated.

#### Trademarks

The Microchip name and logo, the Microchip logo, Adaptec, AnyRate, AVR, AVR logo, AVR Freaks, BesTime, BitCloud, chipKIT, chipKIT logo, CryptoMemory, CryptoRF, dsPIC, FlashFlex, flexPWR, HELDO, IGLOO, JukeBlox, KeeLoq, Kleer, LANCheck, LinkMD, maXStylus, maXTouch, MediaLB, megaAVR, Microsemi, Microsemi logo, MOST, MOST logo, MPLAB, OptoLyzer, PackeTime, PIC, picoPower, PICSTART, PIC32 logo, PolarFire, Prochip Designer, QTouch, SAM-BA, SenGenuity, SpyNIC, SST, SST Logo, SuperFlash, Symmetricom, SyncServer, Tachyon, TimeSource, tinyAVR, UNI/O, Vectron, and XMEGA are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

AgileSwitch, APT, ClockWorks, The Embedded Control Solutions Company, EtherSynch, FlashTec, Hyper Speed Control, HyperLight Load, IntelliMOS, Libero, motorBench, mTouch, Powermite 3, Precision Edge, ProASIC, ProASIC Plus, ProASIC Plus logo, Quiet-Wire, SmartFusion, SyncWorld, Temux, TimeCesium, TimeHub, TimePictra, TimeProvider, WinPath, and ZL are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Adjacent Key Suppression, AKS, Analog-for-the-Digital Age, Any Capacitor, Anyln, AnyOut, Augmented Switching, BlueSky, BodyCom, CodeGuard, CryptoAuthentication, CryptoAutomotive, CryptoCompanion, CryptoController, dsPICDEM, dsPICDEM.net, Dynamic Average Matching, DAM, ECAN, Espresso T1S, EtherGREEN, IdealBridge, In-Circuit Serial Programming, ICSP, INICnet, Intelligent Paralleling, Inter-Chip Connectivity, JitterBlocker, maxCrypto, maxView, memBrain, Mindi, MiWi, MPASM, MPF, MPLAB Certified Iogo, MPLIB, MPLINK, MultiTRAK, NetDetach, Omniscient Code Generation, PICDEM, PICDEM.net, PICkit, PICtail, PowerSmart, PureSilicon, QMatrix, REAL ICE, Ripple Blocker, RTAX, RTG4, SAM-ICE, Serial Quad I/O, simpleMAP, SimpliPHY, SmartBuffer, SMART-I.S., storClad, SQI, SuperSwitcher, SuperSwitcher II, Switchtec, SynchroPHY, Total Endurance, TSHARC, USBCheck, VariSense, VectorBlox, VeriPHY, ViewSpan, WiperLock, XpressConnect, and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

SQTP is a service mark of Microchip Technology Incorporated in the U.S.A.

The Adaptec logo, Frequency on Demand, Silicon Storage Technology, and Symmcom are registered trademarks of Microchip Technology Inc. in other countries.

GestIC is a registered trademark of Microchip Technology Germany II GmbH & Co. KG, a subsidiary of Microchip Technology Inc., in other countries.

All other trademarks mentioned herein are property of their respective companies.

© 2020, Microchip Technology Incorporated, All Rights Reserved.

ISBN: 978-1-5224-6964-3

For information regarding Microchip's Quality Management Systems, please visit www.microchip.com/quality.



## Worldwide Sales and Service

#### AMERICAS

Corporate Office 2355 West Chandler Blvd. Chandler, AZ 85224-6199 Tel: 480-792-7200 Fax: 480-792-7277 Technical Support: http://www.microchip.com/ support Web Address:

www.microchip.com

Atlanta Duluth, GA Tel: 678-957-9614 Fax: 678-957-1455

Austin, TX Tel: 512-257-3370

Boston Westborough, MA Tel: 774-760-0087 Fax: 774-760-0088

Chicago Itasca, IL Tel: 630-285-0071 Fax: 630-285-0075

Dallas Addison, TX Tel: 972-818-7423 Fax: 972-818-2924

**Detroit** Novi, MI Tel: 248-848-4000

Houston, TX Tel: 281-894-5983

Indianapolis Noblesville, IN Tel: 317-773-8323 Fax: 317-773-5453 Tel: 317-536-2380

Los Angeles Mission Viejo, CA Tel: 949-462-9523 Fax: 949-462-9608 Tel: 951-273-7800

Raleigh, NC Tel: 919-844-7510

New York, NY Tel: 631-435-6000

San Jose, CA Tel: 408-735-9110 Tel: 408-436-4270

**Canada - Toronto** Tel: 905-695-1980 Fax: 905-695-2078

#### ASIA/PACIFIC

Australia - Sydney Tel: 61-2-9868-6733 China - Beijing

Tel: 86-10-8569-7000 China - Chengdu

Tel: 86-28-8665-5511 China - Chongqing Tel: 86-23-8980-9588

**China - Dongguan** Tel: 86-769-8702-9880

China - Guangzhou Tel: 86-20-8755-8029

China - Hangzhou Tel: 86-571-8792-8115

China - Hong Kong SAR Tel: 852-2943-5100

China - Nanjing Tel: 86-25-8473-2460

China - Qingdao Tel: 86-532-8502-7355

China - Shanghai Tel: 86-21-3326-8000

China - Shenyang Tel: 86-24-2334-2829

China - Shenzhen Tel: 86-755-8864-2200

China - Suzhou Tel: 86-186-6233-1526

China - Wuhan Tel: 86-27-5980-5300

China - Xian Tel: 86-29-8833-7252

China - Xiamen Tel: 86-592-2388138

China - Zhuhai Tel: 86-756-3210040

#### ASIA/PACIFIC

India - Bangalore Tel: 91-80-3090-4444

India - New Delhi Tel: 91-11-4160-8631

India - Pune Tel: 91-20-4121-0141 Japan - Osaka

Tel: 81-6-6152-7160 Japan - Tokyo

Tel: 81-3-6880- 3770 Korea - Daegu

Tel: 82-53-744-4301 Korea - Seoul

Tel: 82-2-554-7200

Malaysia - Kuala Lumpur Tel: 60-3-7651-7906

Malaysia - Penang Tel: 60-4-227-8870

Philippines - Manila Tel: 63-2-634-9065

Singapore Tel: 65-6334-8870

Taiwan - Hsin Chu Tel: 886-3-577-8366

Taiwan - Kaohsiung Tel: 886-7-213-7830

Taiwan - Taipei Tel: 886-2-2508-8600

Thailand - Bangkok Tel: 66-2-694-1351

Vietnam - Ho Chi Minh Tel: 84-28-5448-2100

-2100 Netherlands - Drunen

Tel: 31-416-690399 Fax: 31-416-690340

EUROPE

Austria - Wels

Tel: 43-7242-2244-39

Tel: 45-4485-5910

Fax: 45-4485-2829

Tel: 358-9-4520-820

Tel: 33-1-69-53-63-20

Fax: 33-1-69-30-90-79

Germany - Garching

Tel: 49-2129-3766400

Germany - Heilbronn

Germany - Karlsruhe

Tel: 49-7131-72400

Tel: 49-721-625370

Germany - Munich

Tel: 49-89-627-144-0

Fax: 49-89-627-144-44

Germany - Rosenheim

Tel: 49-8031-354-560

Israel - Ra'anana

Italy - Milan

Italy - Padova

Tel: 972-9-744-7705

Tel: 39-0331-742611

Fax: 39-0331-466781

Tel: 39-049-7625286

Tel: 49-8931-9700

Germany - Haan

Finland - Espoo

France - Paris

Fax: 43-7242-2244-393

Denmark - Copenhagen

Norway - Trondheim Tel: 47-7288-4388

Poland - Warsaw Tel: 48-22-3325737

Romania - Bucharest Tel: 40-21-407-87-50

**Spain - Madrid** Tel: 34-91-708-08-90 Fax: 34-91-708-08-91

Sweden - Gothenberg Tel: 46-31-704-60-40

Sweden - Stockholm Tel: 46-8-5090-4654

**UK - Wokingham** Tel: 44-118-921-5800 Fax: 44-118-921-5820