MSC015SMA070S Silicon Carbide N-Channel Power MOSFET

1 Product Overview

The silicon carbide (SiC) power MOSFET product line from Microsemi increases the performance over silicon MOSFET and silicon IGBT solutions while lowering the total cost of ownership for high-voltage applications. The MSC015SMA070S device is a 700 V, 15 mΩ SiC MOSFET in a TO-268 (D3PAK) package.

1—Gate
2—Drain
3—Source
Backside—Drain



1.1 Features

The following are key features of the MSC015SMA070S device:

- Low capacitances and low gate charge
- Fast switching speed due to low internal gate resistance (ESR)
- Stable operation at high junction temperature, $T_{J(max)}$ = 175 °C
- Fast and reliable body diode
- Superior avalanche ruggedness
- RoHS compliant

1.2 Benefits

The following are benefits of the MSC015SMA070S device:

- High efficiency to enable lighter, more compact system
- Simple to drive and easy to parallel
- Improved thermal capabilities and lower switching losses
- Eliminates the need for external freewheeling diode
- Lower system cost of ownership

1.3 Applications

The MSC015SMA070S device is designed for the following applications:

- PV inverter, converter, and industrial motor drives
- Smart grid transmission and distribution
- Induction heating and welding
- H/EV powertrain and EV charger
- Power supply and distribution

2 Device Specifications

This section shows the specifications for the MSC015SMA070S device.

2.1 Absolute Maximum Ratings

The following table shows the absolute maximum ratings of the MSC015SMA070S device.

Table 1 • Absolute Maximum Ratings

Symbol	Characteristic	Ratings	Unit
V_{DSS}	Drain source voltage	700	V
I_D	Continuous drain current at T_C = 25 °C	126	A
	Continuous drain current at T_C = 100 °C	89	
I_{DM}	Pulsed drain current [1]	315	
V_{GS}	Gate-source voltage	23 to –10	V
P_D	Total power dissipation at T_C = 25 °C	370	W
	Linear derating factor	2.47	W/°C

Note:

1. Repetitive rating: pulse width and case temperature limited by maximum junction temperature.

The following table shows the thermal and mechanical characteristics of the MSC015SMA070S device.

Table 2 • Thermal and Mechanical Characteristics

Symbol	Characteristic	Min	Typ	Max	Unit
$R_{\theta JC}$	Junction-to-case thermal resistance		0.27	0.41	°C/W
T_J	Operating junction temperature	–55		175	°C
T_{STG}	Storage temperature	–55		150	
T_L	Soldering temperature for 10 seconds (1.6 mm from case)			260	
Wt	Package weight		0.14		oz
			4.0		g

2.2 Electrical Performance

The following table shows the static characteristics of the MSC015SMA070S device. T_J = 25 °C unless otherwise specified.

Table 3 • Static Characteristics

Symbol	Characteristic	Test Conditions	Min	Typ	Max	Unit
$V_{(BR)DSS}$	Drain-source breakdown voltage	V_{GS} = 0 V, I_D = 100 µA	700			V
$R_{DS(on)}$	Drain-source on resistance [1]	V_{GS} = 20 V, I_D = 40 A		15	19	mΩ
$V_{GS(th)}$	Gate-source threshold voltage	V_{GS} = V_{DS}, I_D = 4 mA	1.9	2.4		V
$\Delta V_{GS(th)}/\Delta T_J$	Threshold voltage coefficient	V_{GS} = V_{DS}, I_D = 4 mA		–3.4		mV/°C
I_{DSS}	Zero gate voltage drain current	V_{DS}, = 700 V, V_{GS} = 0 V			100	µA
		V_{DS} = 700 V, V_{GS} = 0 V T_J = 125 °C			500	
I_{GSS}	Gate-source leakage current	V_{GS} = 20 V/–10 V			±100	nA

Notes:

1. Pulse test: pulse width < 380 µs, duty cycle < 2%.

The following table shows the dynamic characteristics of the MSC015SMA070S device. T_J = 25 °C unless otherwise specified.

Table 4 • Dynamic Characteristics

Symbol	Characteristic	Test Conditions	Min	Typ	Max	Unit
C_{iss}	Input capacitance	V_{GS} = 0 V, V_{DD} = 700 V, V_{AC} = 25 mV, f = 1 MHz		4500		pF
C_{rss}	Reverse transfer capacitance			29		
C_{oss}	Output capacitance			510		
Q_g	Total gate charge	V_{GS} = –5 V/20 V, V_{DD} = 470 V I_D = 40 A		215		nC
Q_{gs}	Gate-source charge			58		
Q_{gd}	Gate-drain charge			35		
$t_{d(on)}$	Turn-on delay time	V_{DD} = 470 V, V_{GS} = -5 V/20 V, I_D = 40 A $R_{G(ext)}$ = 2.5 Ω [1] Freewheeling diode = MSC015SMA070S (V_{GS} = -5 V)		38		ns
t_r	Current rise time			8		
$t_{d(off)}$	Turn-off delay time			55		
t_f	Current fall time			15		
E_{on}	Turn-on switching energy [2]			420		µJ
E_{off}	Turn-off switching energy			90		
$t_{d(on)}$	Turn-on delay time	V_{DD} = 470 V, V_{GS} = -5 V/20 V, I_D = 40 A $R_{G(ext)}$ = 2.5 Ω [1] Freewheeling diode = 2x MSC010SDA070S		30		ns
t_r	Current rise time			8		
$t_{d(off)}$	Turn-off delay time			50		
t_f	Current fall time			8		
E_{on}	Turn-on switching energy [2]			217		µJ
E_{off}	Turn-off switching energy			118		
ESR	Equivalent series resistance	f = 1 MHz, 25 mV, drain short		0.69		Ω
SCWT	Short circuit withstand time	V_{DS} = 560 V, V_{GS} = 20 V		3		µs

Symbol	Characteristic	Test Conditions	Min	Typ	Max	Unit
E_{AS}	Avalanche energy, single pulse	V_{DS} = 150 V, V_{GS} = 20 V, I_D = 40 A		4400		mJ

Notes:

1. R_G is total gate resistance excluding internal gate driver impedance.
2. E_{on} includes energy of the freewheeling diode.

The following table shows the body diode characteristics of the MSC015SMA070S device. T_J = 25 °C unless otherwise specified.

Table 5 • Body Diode Characteristics

Symbol	Characteristic	Test Conditions	Min	Typ	Max	Unit
V_{SD}	Diode forward voltage	I_{SD} = 40 A, V_{GS} = 0 V		3.4		V
		I_{SD} = 40 A, V_{GS} = –5 V		3.8		V
t_{rr}	Reverse recovery time	I_{SD} = 40 A, V_{GS} = –5 V V_{DD} = 470 V dI/dt = –1200 A/µs		40		ns
Q_{rr}	Reverse recovery charge			495		nC
I_{RRM}	Reverse recovery current			19		A

2.3 Typical Performance Curves

This section shows the typical performance curves for the MSC015SMA070S device.

Figure 1 • Drain Current vs. Drain-to-Source Voltage



Figure 2 • Drain Current vs. Drain-to-Source Voltage



Figure 3 • Drain Current vs. Drain-to-Source Voltage



Figure 4 • Drain Current vs. Drain-to-Source Voltage



Figure 5 • RDS(on) vs. Junction Temperature



Figure 6 • Gate Charge Characteristics



Figure 7 • Capacitance vs. Drain-to-Source Voltage



Figure 8 • IDM vs. Gate-to-Source Voltage



Figure 9 • IDM vs. VDS Third Quadrant Conduction



Figure 10 • IDM vs. VDS Third Quadrant Conduction



Figure 11 • VGS(th) vs. Junction Temp.



Figure 12 • Forward Safe Operating Area



Figure 13 • Maximum Transient Thermal Impedance



3 Package Specification

This section shows the package specification of the MSC015SMA070S device.

3.1 Package Outline Drawing

The following figure illustrates the TO-268 package outline of the MSC015SMA070S device.

Figure 14 • Package Outline Drawing



The following table shows the TO-268 dimensions and should be used in conjunction with the package outline drawing.

Table 6 • TO-268 Dimensions

Symbol	Min (mm)	Max (mm)	Min (in.)	Max (in.)
A	4.90	5.10	0.193	0.201
B	15.85	16.20	0.624	0.638
C	18.70	19.10	0.736	0.752
D	1.00	1.25	0.039	0.049
E	13.80	14.00	0.543	0.551
F	13.30	13.60	0.524	0.535
G	2.70	2.90	0.106	0.114
H	1.15	1.45	0.045	0.057
I	1.95	2.21	0.077	0.087
J	0.94	1.40	0.037	0.055
K	2.40	2.70	0.094	0.106
L	0.40	0.60	0.016	0.024
M	1.45	1.60	0.057	0.063
N	0.00	0.18	0.000	0.007
O	12.40	12.70	0.488	0.500
P	5.45 BSC (nom.)		0.215 BSC (nom.)	
Terminal 1	Gate			
Terminal 2	Drain			
Terminal 3	Source			
Terminal 4	Drain			

Microsemi Headquarters
One Enterprise, Aliso Viejo,
CA 92656 USA
Within the USA: +1 (800) 713-4113
Outside the USA: +1 (949) 380-6100
Sales: +1 (949) 380-6136
Fax: +1 (949) 215-4996
Email: sales.support@microsemi.com
www.microsemi.com

Microsemi, a wholly owned subsidiary of Microchip Technology Inc. (Nasdaq: MCHP), offers a comprehensive portfolio of semiconductor and system solutions for aerospace & defense, communications, data center and industrial markets. Products include high-performance and radiation-hardened analog mixed-signal integrated circuits, FPGAs, SoCs and ASICs; power management products; timing and synchronization devices and precise time solutions, setting the world's standard for time; voice processing devices; RF solutions; discrete components; enterprise storage and communication solutions; security technologies and scalable anti-tamper products; Ethernet solutions; Power-over-Ethernet ICs and midspans; as well as custom design capabilities and services. Microsemi is headquartered in Aliso Viejo, California, and has approximately 4,800 employees globally. Learn more at www.microsemi.com.

050-7750 | September 2019 | Released