



注：本板为禁止运输、复制、翻印或修改，以及用其内容进行复制或交流

REV	ECN NO.	CONTENT	CHK	DATE




- NOTES1:
 UL Standard
 1.Rating voltage/current: 300V/30A
 2.withstanding voltage: AC2500V/1Min
 3.Torque value: M3, 4.43Lb.in
 4.Wire range: 26~10AWG
 IEC Standard
 1.1.Rating voltage/current: 450V/32A
 2. Torque value: M3, 0.5Nm
 3.wire range: 15-4.0mm²

- NOTES2:
 1.Housing: PA66(UL94V-0)
 2.Solder Pin: Copper alloy(Sn Plated)
 3.Cage: Brass(Ni Plated)
 4.Screw: Steel(M3,Zn Plated)

- NOTES3:
 1.Pitch: 7.62mm Poles: 02-24P
 2.Stripping length: 7-8mm
 3.Operating temperature: -40℃~+105℃
 4.RoHS Compliance

How to order



Pitch	Range	In	Nominal Dimension	Range
mm		In	mm	

Over 6	Over 10	Over 24	Over 30	Over 60	Over 100	Over 150	Over 150	0.1/10
TO 6	TO 10	TO 24	TO 30	TO 60	TO 100	TO 150	TO 150	∠
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±1.30	±2°

ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTE
DWG	CHK	DATE	UNITS	MM	1/1
APP	DATE	SCALE	SCALE	A4	1/1
CIXI MAIXU ELECTRONICS CO.,LTD			NAME	MX762-762-XXP	
MAIXU 慈溪市迈旭电子有限公司			DWGNO.		