

# ILC7362

# **CMOS Negative LDO Regulator**

#### **Features**

- Ultra-Low Supply Current (3µA typ.)
- All-CMOS Design in SOT-23 and SOT-89 Packages
- ±2% Precision Output Voltage
- Output Current Limit
- Package and Voltage Options allow: 100mA/-6V Regulator 100mA/-5V Regulator 60mA/-3V Regulator

#### **Applications**


- Battery-Operated Systems
- Portable Computers and Cameras
- Cellular/GSM/PHS Phones
- PDAs

#### **General Description**

The ILC7362 is a low quiescent current, negative voltage LDO. It provides up to 60 or 100mA output current with low power consumption and small input-output differential voltage.


The ILC7362 is available in SOT23-3 (max.150mW) or SOT89-3 (max.500mW) package, for a number of fixed voltage and current offerings.


#### **Block Diagram**



ILC7362 PRODUCT SPECIFICATION

## **Pin Configurations**





#### **Pin Definitions**

Pin Number						
SOT-23	SOT-89	Pin Name	Pin Function Description			
1	1	V <sub>OUT</sub>	Regulated Voltage Output			
2	3	V <sub>IN</sub>	Power Supply Input			
3	2	GND	Ground Connection			

## **Absolute Maximum Ratings**

Absolute maximum ratings are the values beyond which the device may be damaged or have its useful life impaired. Functional operation under these conditions is not implied.

Parameter	Min.	Max.	Units	
Supply Voltage: V <sub>IN</sub> to GND		-12	V	
Output Current: I <sub>OUT</sub>		200	mA	
Output Voltage: V <sub>OUT</sub> to GND	0.3	V <sub>IN</sub> - 0.3	V	
Junction Temperature (T <sub>J</sub> )	-40	125	°C	
Storage Temperature	-40	125	°C	
Lead Soldering Temperature, 10 seconds		300	°C	
Continuous Total Power Dissipation	SOT-23		150	mW
(P <sub>D</sub> ) at T <sub>A</sub> =25°C	SOT-89		500	

## **Recommended Operating Conditions**

Parameter	Conditions	Min.	Тур.	Max.	Units
Supply Voltage Range V <sub>IN</sub>		V <sub>OUT</sub> – V <sub>DO</sub>	V <sub>OUT</sub> – 1	-10	V
Ambient Operating Temperature		-30	25	80	°C

PRODUCT SPECIFICATION ILC7362




Figure 1. Test Circuit

**Electrical Specifications ILC7362Cx-60** ( $V_{IN} = V_{OUT} - 1V$ , and  $T_A = 25^{\circ}C$  using circuit in Figure 1, unless otherwise noted.)

Parameter	Symbol	Conditions	Min.	Тур.	Max.	Units
Output Voltage	V <sub>OUT</sub>	I <sub>OUT</sub> = 20mA	0.98	$V_{OUTnom} = -6.0$	1.02	V
			VouTnom		$V_{OUTnom}$	
Maximum Output Current, Note 1	I <sub>OUTMAX</sub> .	-V <sub>OUT</sub> ≥ -0.9V <sub>OUTnom</sub>	100			mA
Load Regulation	$\Delta V_{OUT}$	$1mA \le I_{OUT} \le 50mA$		40	80	mV
Dropout Voltage, Note 2	$V_{DO}$	I <sub>OUT</sub> = 50mA		120	300	mV
		I <sub>OUT</sub> = 100mA		380	600	
Ground Current	I <sub>GND</sub>			3.0	7.0	μΑ
Line Regulation	$\frac{\Delta V_{OUT}}{\Delta V_{IN  x}  V_{OUT}}$	$I_{OUT} = 20mA$ $7V \le -V_{IN} \le 10V$		0.1	0.3	%/V
Output Voltage Temperature Coefficient	$\frac{\Delta V_{OUT}}{\Delta T \times V_{OUT}}$	$I_{OUT} = 30$ mA $-30$ °C $\leq$ T $\leq$ 80°C		<u>+</u> 100		ppm/°C

**Electrical Specifications ILC7362Cx-50** ( $V_{IN} = V_{OUT} - 1V$ , and  $T_A = 25^{\circ}C$  using circuit in Figure 1, unless otherwise noted.)

Parameter	Symbol	Conditions	Min.	Тур.	Max.	Units
Output Voltage	V <sub>OUT</sub>	I <sub>OUT</sub> = 20mA	0.98	$V_{OUTnom} = -5.0$	1.02	V
			VouTnom		$V_{OUTnom}$	
Maximum Output Current, Note 1	I <sub>OUTMAX</sub> .	-V <sub>OUT</sub> ≥ -0.9V <sub>OUTnom</sub>	100			mA
Load Regulation	$\Delta V_{OUT}$	$1mA \le I_{OUT} \le 50mA$		40	80	mV
Dropout Voltage, Note 2	$V_{DO}$	I <sub>OUT</sub> = 50mA		120	300	mV
		I <sub>OUT</sub> = 100mA		380	600	
Ground Current	I <sub>GND</sub>			3.0	7.0	μΑ
Line Regulation	$\frac{\Delta V_{OUT}}{\Delta V_{IN x} V_{OUT}}$	$I_{OUT} = 20\text{mA}$ $7\text{V} \le -\text{V}_{IN} \le 10\text{V}$		0.1	0.3	%/V
Output Voltage Temperature Coefficient	$\frac{\Delta V_{OUT}}{\Delta T \times V_{OUT}}$	$I_{OUT} = 30$ mA $-30$ °C $\leq$ T $\leq$ 80°C		<u>+</u> 100		ppm/ °C

ILC7362 PRODUCT SPECIFICATION

Electrical Specifications ILC7362Cx-30  $(V_{IN} = V_{OUT} - 1V, \text{ and } T_A = 25^{\circ}\text{C} \text{ using circuit in Figure 1, unless otherwise noted.})$ 

Parameter	Symbol	Conditions	Min.	Тур.	Max.	Units
Output Voltage	V <sub>OUT</sub>	I <sub>OUT</sub> = 20mA	0.98 V <sub>OUTnom</sub>	V <sub>OUTnom</sub> = -3.0	1.02 V <sub>OUTnom</sub>	V
Maximum Output Current, Note 1	I <sub>OUTMAX</sub> .	-V <sub>OUT</sub> ≥ -0.9V <sub>OUTnom</sub>	60			mA
Load Regulation	$\Delta V_{OUT}$	$1mA \le I_{OUT} \le 50mA$		40	80	mV
Dropout Voltage, Note 2	$V_{DO}$	I <sub>OUT</sub> = 40mA		120	300	mV
		I <sub>OUT</sub> = 80mA		380	600	
Ground Current	I <sub>GND</sub>			2.5	6.0	μА
Line Regulation	$\frac{\Delta V_{OUT}}{\Delta V_{INx}V_{OUT}}$	$I_{OUT} = 20\text{mA}$ $4\text{V} \le -\text{V}_{IN} \le 10\text{V}$		0.1	0.3	%/V
Output Voltage Temperature Coefficient	$\frac{\Delta V_{OUT}}{\Delta T_x V_{OUT}}$	$I_{OUT} = 30$ mA $-30$ °C $\leq T \leq 80$ °C		±100		ppm/ °C

#### Notes:

<sup>1.</sup>  $\ensuremath{I_{\text{OUTMAX}}}$  is limited also by the maximum allowable power dissipation for the package.

<sup>2.</sup>  $V_{DO}$  is the input to output differential voltage at which the output voltage drop 2% below  $V_{OUT}$ .

PRODUCT SPECIFICATION ILC7362


## **Typical Characteristics**

OUTPUT VOLTAGE V<sub>OUT</sub> (V)


-2.5

# OUTPUT VOLTAGE vs INPUT VOLTAGE ILC7362CM-30 -3.2 Topr=25°C -3.0 -2.8 -2.6 -40mA






#### **OUTPUT VOLTAGE vs INPUT VOLTAGE**




#### **OUTPUT VOLTAGE vs TEMPERATURE**



PRODUCT SPECIFICATION ILC7362


## **Mechanical Dimensions**

#### SOT-23-3



PRODUCT SPECIFICATION ILC7362

#### SOT-89-3



ILC7362 PRODUCT SPECIFICATION

#### **Ordering Information**

Part Number	V <sub>OUT</sub> (V)	Temperature Range (°C)	Package
ILC7362CP50X	-5	−30 to +80 °C	SOT89
ILC7362CP30X	-3	−30 to +80 °C	SOT89
ILC7362CM60X	-6	−30 to +80 °C	SOT23
ILC7362CM50X	-5	−30 to +80 °C	SOT23
ILC7362CM30X	-3	−30 to +80 °C	SOT23

#### **DISCLAIMER**

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS.

#### LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

- Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
- A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

www.fairchildsemi.com

#### back to top

#### **Applications**

- Battery-Operated Systems
- Portable Computers and Cameras
- Cellular/GSM/PHS Phones
- PDAs

#### back to top

#### Product status/pricing/packaging

Product	Product status	Pricing*	Package type	Leads	Packing method
ILC7362CM30X	Full Production	\$0.66	SOT-23	3	TAPE REEL
ILC7362CP30X	Lifetime Buy	\$0.66	N/A	N/A	TAPE REEL

<sup>\* 1,000</sup> piece Budgetary Pricing

#### back to top

<u>Home</u> | <u>Find products</u> | <u>Technical information</u> | <u>Buy products</u> | <u>Support</u> | <u>Company</u> | <u>Contact us</u> | <u>Site index</u> | <u>Privacy policy</u>

© Copyright 2002 Fairchild Semiconductor



back to top

PDAs

• Battery-Operated Systems

Portable Computers and CamerasCellular/GSM/PHS Phones

#### Product status/pricing/packaging

Product	Product status	Pricing*	Package type	Leads	Packing method
ILC7362CM50X	Lifetime Buy	\$0.66	SOT-23	3	TAPE REEL

<sup>\* 1,000</sup> piece Budgetary Pricing

#### back to top

<u>Home</u> | <u>Find products</u> | <u>Technical information</u> | <u>Buy products</u> | <u>Support</u> | <u>Company</u> | <u>Contact us</u> | <u>Site index</u> | <u>Privacy policy</u>

© Copyright 2002 Fairchild Semiconductor