1.5 A, 40 V Schottky Barrier Diode

These Schottky barrier diodes are optimized for low forward voltage drop and low leakage current and are offered in a Chip Scale Package (CSP) to reduce board space. The low thermal resistance enables designers to meet the challenging task of achieving higher efficiency and meeting reduced space requirements.

Features

- Low Forward Voltage Drop 540 mV (Typ.) @ $I_F = 1.5 A$
- Low Reverse Current 20 μ A (Typ.) @ $V_R = 40 \text{ V}$
- 1.5 A of Continuous Forward Current
- ESD Rating Human Body Model: Class 3B
 - Machine Model: Class C
- High Switching Speed
- These Devices are Pb–Free, Halogen Free/BFR Free and are RoHS Compliant

Typical Applications

- LCD and Keypad Backlighting
- Camera Photo Flash
- Buck and Boost dc-dc Converters
- Reverse Voltage and Current Protection
- Clamping & Protection

MAXIMUM RATINGS

Rating	Symbol	Value	Unit
Reverse Voltage	V_R	40	V
Forward Current (DC)	lF	1.5	Α
Forward Surge Current (60 Hz @ 1 cycle)	I _{FSM}	13	Α
Repetitive Peak Forward Current (Pulse Wave = 1 sec, Duty Cycle = 66%)	I _{FRM}	3	Α
ESD Rating: Human Body Model Machine Model	ESD	> 8 > 400	kV V

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.



ON Semiconductor®

www.onsemi.com



MARKING DIAGRAM

DSN2 (0502) CASE 152AU PIN 1

5GM

5G = Specific Device Code M = Date Code

PIN CONNECTIONS



ORDERING INFORMATION

Device	Package	Shipping [†]
NSR15405NXT5G	DSN2 (Pb-Free)	5000 / Tape & Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

THERMAL CHARACTERISTICS

Characteristic	Symbol	Min	Тур	Max	Unit
Thermal Resistance Junction-to-Ambient (Note 1) Total Power Dissipation @ T _A = 25°C	R _{θJA} P _D			255 490	°C/W mW
Thermal Resistance Junction-to-Ambient (Note 2) Total Power Dissipation @ T _A = 25°C	R _{θJA} P _D			95 1.32	°C/W W
Storage Temperature Range	T _{stg}			-40 to +125	°C
Junction Temperature	TJ			+150	°C

- 1. Mounted onto a 4 in square FR-4 board 50 mm sq. 1 oz. Cu 0.06" thick single sided. Operating to steady state.
- 2. Mounted onto a 4 in square FR-4 board 650 mm sq. 1 oz. Cu 0.06" thick single sided. Operating to steady state.




Figure 1. Thermal Response (Note 1)





Figure 2. Thermal Response (Note 2)

ELECTRICAL CHARACTERISTICS (T_A = 25°C unless otherwise noted)

Characteristic	Symbol	Min	Тур	Max	Unit
Reverse Leakage (V _R = 10 V) (V _R = 40 V)	I _R	_ _	2 20	10 75	μА
Forward Voltage (I _F = 10 mA) (I _F = 100 mA) (I _F = 500 mA) (I _F = 1 A) (I _F = 1.5 A)	V _F	- - - -	250 320 410 480 540	290 360 450 520 590	mV
Total Capacitance (V _R = 2.0 V, f = 1.0 MHz)	C _T	_	85	-	pF
Reverse Recovery Time ($I_F = I_R = 10 \text{ mA}$, $I_{R(REC)} = 1.0 \text{ mA}$, Figure 3)	t _{rr}	-	33	-	ns
Peak Forward Recovery Voltage (I _F = 100 mA, t _r = 20 ns, Figure 4)	V_{FRM}	_	460	-	mV

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.



Notes: 1. A 2.0 k Ω variable resistor adjusted for a Forward Current (I_F) of 10 mA.

2. Input pulse is adjusted so $I_{R(peak)}$ is equal to 10 mA.

3. t_p » t_{rr}

Figure 3. Recovery Time Equivalent Test Circuit




Figure 4. Peak Forward Recover Voltage Definition

TYPICAL CHARACTERISTICS





Figure 5. Forward Voltage

Figure 6. Leakage Current








Figure 7. Average Forward Power Dissipation

Figure 8. Average Reverse Power Dissipation










Figure 10. Forward Surge Maximum




DSN2, **1.4x0.6**, **1.00P** (**0502**) CASE 152AU ISSUE A


DATE 08 JUN 2016







RECOMMENDED MOUNTING FOOTPRINT*



See Application Note AND8464/D for more mounting details

NOTES:

- DIMENSIONING AND TOLERANCING PER
 ASME Y14.5M. 1994.
- 2. CONTROLLING DIMENSION: MILLIMETERS.

	MILLIMETERS		
DIM	MIN	MAX	
Α	0.25	0.31	
A1	0.00	0.05	
b	0.45	0.55	
D	1.40 BSC		
E	0.60 BSC		
е	1.00 BSC		
L	0.20	0.30	

GENERIC MARKING DIAGRAM1*

PIN 1


GENERIC
MARKING DIAGRAM2*



XXXX = Specific Device Code YYY = Year Code XX = Specific Device Code M = Date Code

*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G", may or not be present.

CATHODE BAND MONTH CODING



DOCUMENT NUMBER	: 98AON79730F	Electronic versions are uncontrolled except when accessed directly from the Document Repositor Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.	
DESCRIPTION	: DSN2, 1.4X0.6, 1.00P (050	2)	PAGE 1 OF 1

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

^{*}For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and the are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor and see no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:
Email Requests to: orderlit@onsemi.com

ON Semiconductor Website: www.onsemi.com

TECHNICAL SUPPORT North American Technical Support: Voice Mail: 1 800-282-9855 Toll Free USA/Canada Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support:

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative