

SEMICONDUCTOR®


# KA293/KA293A, KA393/KA393A, KA2903 Dual Differential Comparator

## Features


- Single Supply Operation: 2V to 36V
- Dual Supply Operation:  $\pm 1V$  to  $\pm 18V$
- Allow Comparison of Voltages Near Ground Potential
- Low Current Drain 800µA Typ.
- Compatible with all Forms of Logic
- Low Input Bias Current 25nA Typ.
- Low Input Offset Current ±5nA Typ.
- Low Offset Voltage ±1mV Typ.

# Descritpion


The KA293 series consists of two independent voltage comparators designed to operate from a single power supply over a wide voltage range.



# **Internal Block Diagram**



# **Schematic Diagram**



# **Absolute Maximum Ratings**

Parameter	Symbol	Value	Unit
Power Supply Voltage	Vcc	±18 or 36	V
Differential Input Voltage	VI(DIFF)	36	V
Input Voltage	VI	- 0.3 to +36	V
Output Short Circuit to GND	-	Continuous	-
Power Dissipation, Ta = 25°C 8-DIP 8-SOP	PD	1040 480	mW
Operating Temperature KA393/KA393A KA293/KA293A KA2903	Topr	0 ~ + 70 - 25 ~ + 85 - 40 ~ + 85	°C
Storage Temperature	TSTG	- 65 ~ + 150	°C

## **Thermal Data**

Parameter	Symbol	Value	Unit
Thermal Resistance Junction-Ambient Max. 8-DIP 8-SOP	Rθja	120 260	°C/W

# **Electrical Characteristics**

(VCC =5V, TA=25°C, unless otherwise specified)

Baramatar	Symbol	Conditions -		KA293A/KA393A			KA293/KA393			Unit
Parameter	Symbol			Min.	Тур.	Max.	Min.	Тур.	Max.	Unit
Input Offset Voltage	Vio	VO(P) =1.4V, RS =0Ω		-	±1	±2	-	±1	±5	mV
input Onset voltage	VI0	V <sub>CM</sub> = 0 to1.5V Note 1		-	-	±4.0	-	-	±9.0	IIIV
Input Offset Current	lio			-	±5	±50	-	±5	±50	nA
	10		Note 1	-	-	±150	-	-	±150	
Input Bias Current	IBIAS			-	65	250	-	65	250	nA
Input bias Current	IBIAS		Note 1	-	-	400	-	-	400	
Input Common Mode				0	-	VCC -1.5	0	-	Vcc -1.5	V
Voltage Range	VI(R)		Note 1	0	-	Vcc -2	0	-	Vcc -2	V
Supply Current	Icc	$R_L = \infty$ , $V_{CC} =$	5V	-	0.6	1	-	0.6	1	mA
Supply Current		R <sub>L</sub> = ∞, V <sub>CC</sub> = 3	30V	-	0.8	2.5	-	0.8	2.5	
Voltage Gain	Gv	V <sub>CC</sub> =15V, RL≥15KΩ (for large V <sub>O</sub> (P-P)swing)		50	200	-	50	200	-	V/mV
Large Signal Response Time	T <sub>LRES</sub>	$V_I = TTL Logic Swing$ $V_{REF} = 1.4V, V_{RL} = 5V,$ $R_L = 5.1K\Omega$		-	350	-	-	350	-	nS
Response Time	T <sub>RES</sub>	V <sub>RL</sub> =5V, R <sub>L</sub> =5.1KΩ		-	1.4	-	-	1.4	-	μS
Output Sink Current	ISINK	VI(-)≥1V, VI(+) =0V, VO(P)≤1.5V		6	18	-	6	18	-	mA
Output Saturation		$V_{I(-)} \ge 1V, VI(+)$	=0V	-	160	400	-	160	400	mV
Voltage	Voltage VSAT VSAT		Note 1	-	-	700	-	-	700	111.0
Output Leakage	IO(LKG)	$ \begin{array}{c} V_{I(-)} = 0V, \\ V_{I(+)} = 1V \end{array} \qquad \begin{array}{c} V_{O(P)} = 5V \\ V_{O(P)} = 30V \end{array} $		-	0.1	-	-	0.1	-	nA
Current	IU(LKG)			-	-	1.0	-	-	1.0	μΑ

#### NOTE 1

 $\begin{array}{l} {\sf KA393} \ / \ {\sf KA393A} \ : \ 0 \leq {\sf T}_A \leq +70\,^{\circ}{\sf C} \\ {\sf KA293} \ / \ {\sf KA293A} \ : \ -25 \leq {\sf T}_A \leq +85\,^{\circ}{\sf C} \\ {\sf KA2903} \ : \ -40 \leq {\sf T}_A \leq +85\,^{\circ}{\sf C} \end{array}$ 

# Electrical Characteristics (Continued)

(VCC =5V, TA=25°C, unless otherwise specified)

Parameter	Symbol	Condi	Conditions		KA2903			
Farameter	Symbol	Conditions		Min.	Тур.	Max.	Unit	
		VO(P) =1.4V, Rs =0Ω		-	±1	±7	mV	
Input Offset Voltage	Vio	VCM= 0 to 1.5V	Note 1	-	±9	±15	mv	
Input Offeet Current					±5	±50	n۸	
Input Offset Current	lio		Note 1	-	±50	±200	nA	
Input Pige Current				-	65	250		
Input Bias Current	IBIAS		Note 1	-	-	500	nA	
Input Common Mode				0	-	Vcc-1.5	V	
Voltage Range	VI(R)		Note 1	0	-	Vcc-2	V	
Supply Current		$R_L = \infty$ , $V_{CC} = 5V$		-	0.6	1	mA	
Supply Current	ICC	RL = ∞, VCC = 30V		-	1	2.5		
Voltage Gain	Gv	V <sub>CC</sub> =15V, R <sub>L</sub> ≥15KΩ(for large VO(P-P)swing)		25	100	-	V/mV	
Large Signal Response Time	T <sub>LRES</sub>	V <sub>I</sub> =TTL Logic Swing VREF =1.4V, VRL =5V, RL =5.1KΩ		-	350	-	nS	
Response Time	TRES	V <sub>RL</sub> =5V, R <sub>L</sub> =5.1KΩ		-	1.5	-	μS	
Output Sink Current	ISINK	VI(-)≥1V, VI(+) =0V, VO(P) ≤1.5V		6	16	-	mA	
Output Saturation Voltage	VSAT	V <sub>I(-)</sub> ≥1V, VI(+) =0V		-	160	400	mV	
Output Saturation Voltage		ISINK = 4mA	NOTE 1	-	-	700	IIIV	
Output Leakage Current	IO(LKG)	$V_{I(-)} = 0V,$	VO(P) = 5V	-	0.1	-	nA	
Ouipui Leakage Cuiteili		VI(+) = 1V VO(P) = 30V		-	-	1.0	μA	

### NOTE 1

 $\begin{array}{l} \mathsf{KA393} \ / \ \mathsf{KA393A} : 0 \leq \mathsf{T}_A \leq +70^\circ \mathsf{C} \\ \mathsf{KA293} \ / \ \mathsf{KA293A} : -25 \leq \mathsf{T}_A \leq +85^\circ \mathsf{C} \\ \mathsf{KA2903} : -40 \leq \mathsf{T}_A \leq +85^\circ \mathsf{C} \end{array}$ 

# **Typical Performance Characteristics**




Figure 1. Supply Current vs Supply Voltage




Figure 3. Output Saturation Voltage vs Sink Current




Figure 2. Input Current vs Supply Voltage




Figure 4. Response Time for Various Input Overdrive-Negative Transition




Figure 5. Response Time for Various Input Overdrive-Positive Transition

## **Mechanical Dimensions**

## Package

#1

#4

0~15°

# 0.79 $6.40 \pm 0.20$ 0.252 ±0.008 $0.018 \pm 0.004$ **1.524** ±0.10 0.060 ±0.004 $\textbf{0.46} \pm \textbf{0.10}$ #8 $\begin{array}{c} 9.20 \pm \! 0.20 \\ \hline 0.362 \pm \! 0.008 \end{array}$ <u>9.60</u> MAX #5 2.54 0.100 5.08 0.200 MAX $3.30 \pm 0.30$ 0.130 ±0.012 7.62 0.300 $\frac{0.33}{0.013}\,\text{MIN}$ $3.40 \pm 0.20$ $\overline{0.134 \pm 0.008}$ 0.25 +0.10 -0.05 0.010 +0.004 0.010 -0.002

8-DIP


**Dimensions in millimeters** 

# Mechanical Dimensions (Continued)

### Package




8-SOP



### **Mechanical Dimensions** (Continued)

## Package

### **Dimensions in millimeters**



# **Ordering Information**

Product Number	Package	Operating Temperature		
KA393	8-DIP			
KA393A				
KA393D	8-SOP	0 ~ + 70°C		
KA393AD	0-30F			
KA393S	9-SIP			
KA293	8-DIP			
KA293A		-25 ~ + 85°C		
KA293D	8-SOP	-23 ~ + 65 C		
KA293AD	0-30F			
KA2903	8-DIP	-40 ~ + 85°C		
KA2903D	8-SOP	-40 ~ + 65 C		

#### DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS.

#### LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

- Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
- A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

www.fairchildsemi.com

Fairchild Semiconductor			tric   Cross Reference
find products	Home >> Find products >>	Isnace_ Produc	t Folders and Annlica
Products groups         Analog and Mixed         Signal         Discrete         Interface         Logic         Microcontrollers         Non-Volatile         Memory         Optoelectronics         Markets and         applications         New products         Product selection and         parametric search         Cross-reference         search	KA393A Dual Comparator Contents General description   Features   Product status/pricing/packaging   Application notes General description The KA293 series consists of two independent voltage comparators designed to operate from a single power supply over a wide voltage range.	Datasheet <u>Download this</u> <u>datasheet</u> PDF e-mail this datasheet [E- This page <u>Print version</u>	Related Links  Request samples  Datted Line How to order products  Datted Line Product Change Notices (PCNs) Datted Line Support Datted Line Distributor and field sales representatives Datted Line Quality and reliability Datted Line Design tools
technical information buy products	<ul><li>Features</li><li>Single Supply Operation: 2V to 36V</li></ul>	-	
technical support my Fairchild company	<ul> <li>Dual Supply Operation: ± 1V to ±18V</li> <li>Allow Comparison of Voltages Near Ground Potential</li> <li>Low Current Drain 800µA Typ</li> <li>Compatible with all Forms of Logic</li> <li>Low Input Bias Current 25nA Typ</li> </ul>		
	<ul> <li>Low Input Dias Current 25nA Typ</li> <li>Low Input Offset Current ±5nA Typ.</li> </ul>		

• Low Offset Voltage ±1mV Typ

# back to top

Product status/pricing/packaging

Product	Product status	Package type	Leads	Packing method
KA393ADTF	Full Production	SOIC	8	TAPE REEL
KA393AD	Full Production	SOIC	8	RAIL
KA393A	Full Production	DIP	8	RAIL



Application notes

<u>AN-4101: AN-4101 Lithium-Ion Battery Charger and Adapter Using a</u> Fairchild Power Switch (SPS) (424 K) Jul 19, 2002

back to top

<u>Home</u> | <u>Find products</u> | <u>Technical information</u> | <u>Buy products</u> | <u>Support</u> | <u>Company</u> | <u>Contact us</u> | <u>Site index</u> | <u>Privacy policy</u>

© Copyright 2002 Fairchild Semiconductor