# **Power MOSFET**

## 4 Amps, 30 Volts N-Channel SO-8 Dual

## Features

- Designed for use in low voltage, high speed switching applications
- Ultra Low On-Resistance Provides
  - Higher Efficiency and Extends Battery Life
    - $-R_{DS(on)} = 0.048 \ \Omega, V_{GS} = 10 \ V \ (Typ)$
    - $-R_{DS(on)} = 0.065 \Omega$ ,  $V_{GS} = 4.5 V (Typ)$
- Miniature SO-8 Surface Mount Package Saves Board Space
- Diode is Characterized for Use in Bridge Circuits
- Diode Exhibits High Speed, with Soft Recovery

## Applications

- Dc–Dc Converters
- Computers
- Printers
- Cellular and Cordless Phones
- Disk Drives and Tape Drives

### **MAXIMUM RATINGS** (T<sub>J</sub> = $25^{\circ}$ C unless otherwise noted)

	-		
Rating	Symbol	Value	Unit
Drain-to-Source Voltage	V <sub>DSS</sub>	30	Volts
Gate-to-Source Voltage - Continuous	V <sub>GS</sub>	±20	Volts
Drain Current – Continuous @ $T_A = 25^{\circ}C$ – Single Pulse (tp ≤ 10 $\mu$ s)	I <sub>D</sub> I <sub>DM</sub>	4.0 12	Adc Apk
Total Power Dissipation @ T <sub>A</sub> = 25°C (Note 1)	P <sub>D</sub>	2.0	Watts
Operating and Storage Temperature Range	T <sub>J</sub> , T <sub>stg</sub>	–55 to +150	°C
$            Single Pulse Drain-to-Source Avalanche \\             Energy - Starting T_J = 25^\circ C \\              (V_{DD} = 25 Vdc, V_{GS} = 5.0 Vdc, \\              Peak I_L = 4.45 Apk, L = 8 mH, \\              R_G = 25 \Omega)            $	E <sub>AS</sub>	80	mJ
Thermal Resistance – Junction-to-Ambient (Note 1)	$R_{\thetaJA}$	62.5	°C/W
Maximum Lead Temperature for Soldering Purposes for 10 seconds	ΤL	260	°C

1. When surface mounted to an FR4 board using 1" pad size, t  $\leq$  10 s




## **ON Semiconductor®**

### http://onsemi.com

V <sub>DSS</sub>	R <sub>DS(ON)</sub> TYP	I <sub>D</sub> MAX
30 V	48 m $\Omega$ @ V <sub>GS</sub> = 10 V	4.0 A


#### N-Channel





CASE 751 STYLE 11

#### MARKING DIAGRAM & PIN ASSIGNMENTS



WW = Work Week

## **ORDERING INFORMATION**

Device	Package	Shipping <sup>†</sup>
NTMD4N03R2	SO-8	2500/Tape & Reel


<sup>+</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.

## **ELECTRICAL CHARACTERISTICS** ( $T_C = 25^{\circ}C$ unless otherwise noted)

Characteristic			Min	Тур	Max	Unit
OFF CHARACTERISTICS						
Drain-to-Source Breakdown Voltage $(V_{GS} = 0 \text{ Vdc}, I_D = 250 \mu \text{A})$ Temperature Coefficient (Positive)			30 -	_ 32		Vdc mV/°C
Zero Gate Voltage Drain Current $(V_{DS} = 30 \text{ Vdc}, V_{GS} = 0 \text{ Vdc}, T_J = 25^{\circ}\text{C})$ $(V_{DS} = 30 \text{ Vdc}, V_{GS} = 0 \text{ Vdc}, T_J = 125^{\circ}\text{C})$			-		1.0 10	μAdc
Gate-Body Leakage Current (V <sub>GS</sub> = ±20 Vdc, V <sub>DS</sub> = 0 Vdc)			_	_	100	nAdc
ON CHARACTERISTICS (Note 2)						
Gate Threshold Voltage $(V_{DS} = V_{GS}, I_D = 250 \mu Adc)$ Temperature Coefficient (Negative)			1.0	1.9 4.2	3.0	Vdc mV/°C
Static Drain-to-Source On-State Resistance $(V_{GS} = 10 \text{ Vdc}, I_D = 4 \text{ Adc})$ $(V_{GS} = 4.5 \text{ Vdc}, I_D = 2 \text{ Adc})$			-	0.048 0.065	0.060 0.080	Ω
Forward Transconductance $(V_{DS} = 3 \text{ Vdc}, I_D = 2 \text{ Adc})$			-	6.0	_	Mhos
DYNAMIC CHARACTERISTICS						
Input Capacitance		C <sub>iss</sub>	-	285	400	pF
Output Capacitance	(V <sub>DS</sub> = 20 Vdc, V <sub>GS</sub> = 0 Vdc, f = 1.0 MHz)	C <sub>oss</sub>	-	95	135	
Reverse Transfer Capacitance	]	C <sub>rss</sub>	_	35	70	
SWITCHING CHARACTERISTICS (	Notes 2 & 3)					
Turn-On Delay Time		t <sub>d(on)</sub>	-	7.0	15	ns
Rise Time	$(V_{DD} = 20 \text{ Vdc}, I_D = 2 \text{ A},$	t <sub>r</sub>	-	14	30	
Turn-Off Delay Time	- V <sub>GS</sub> = 10 V, R <sub>G</sub> = 2 Ω)	t <sub>d(off)</sub>	-	16	30	
Fall Time		t <sub>f</sub>	-	10	20	
Gate Charge	$(V_{DS} = 10 \text{ Vdc}, V_{GS} = 10 \text{ Vdc}, I_{D} = 3.5 \text{ A})$	QT	-	8.0	16	nC
		Q <sub>1</sub>	1	1.1	-	
		Q <sub>2</sub>	-	1.9	_	
BODY-DRAIN DIODE RATINGS (No	ote 2)	•		•		•
Diode Forward On–Voltage	$(I_{S} = 2 \text{ Adc}, V_{GS} = 0 \text{ V})$ $(I_{S} = 2 \text{ Adc}, V_{GS} = 0 \text{ V}, T_{J} = 150^{\circ}\text{C})$	V <sub>SD</sub>	-	0.82 0.63	1.0 -	Vdc
Reverse Recovery Time	(I <sub>S</sub> = 2 A, V <sub>GS</sub> = 0 V, dI <sub>S</sub> /dt = 100 A/μs)	t <sub>rr</sub>	-	14	_	ns
		ta	-	10	_	
		t <sub>b</sub>	-	4.0	-	1
Reverse Recovery Stored Charge ( $I_S = 2 \text{ A}$ , $dI_S/dt = 100 \text{ A}/\mu\text{s}$ , $V_{GS} = 0 \text{ V}$ )			_	0.008	-	μC

Pulse Test: Pulse Width ≤ 300 μs, Duty Cycle ≤ 2%.
 Switching characteristics are independent of operating junction temperature.

## **TYPICAL MOSFET ELECTRICAL CHARACTERISTICS**



#### POWER MOSFET SWITCHING

Switching behavior is most easily modeled and predicted by recognizing that the power MOSFET is charge controlled. The lengths of various switching intervals ( $\Delta t$ ) are determined by how fast the FET input capacitance can be charged by current from the generator.

The published capacitance data is difficult to use for calculating rise and fall because drain–gate capacitance varies greatly with applied voltage. Accordingly, gate charge data is used. In most cases, a satisfactory estimate of average input current ( $I_{G(AV)}$ ) can be made from a rudimentary analysis of the drive circuit so that

 $t = Q/I_{G(AV)}$ 

During the rise and fall time interval when switching a resistive load,  $V_{GS}$  remains virtually constant at a level known as the plateau voltage,  $V_{SGP}$ . Therefore, rise and fall times may be approximated by the following:

$$\begin{split} t_r &= Q_2 \; x \; R_G / (V_{GG} - V_{GSP}) \\ t_f &= Q_2 \; x \; R_G / V_{GSP} \end{split}$$

where

 $V_{GG}$  = the gate drive voltage, which varies from zero to  $V_{GG}$  $R_G$  = the gate drive resistance

and  $Q_2$  and  $V_{GSP}$  are read from the gate charge curve.

During the turn–on and turn–off delay times, gate current is not constant. The simplest calculation uses appropriate values from the capacitance curves in a standard equation for voltage change in an RC network. The equations are:

$$\begin{split} t_{d(on)} &= R_G \; C_{iss} \; In \; [V_{GG}/(V_{GG}-V_{GSP})] \\ t_{d(off)} &= R_G \; C_{iss} \; In \; (V_{GG}/V_{GSP}) \end{split}$$

The capacitance ( $C_{iss}$ ) is read from the capacitance curve at a voltage corresponding to the off–state condition when calculating  $t_{d(on)}$  and is read at a voltage corresponding to the on–state when calculating  $t_{d(off)}$ .

At high switching speeds, parasitic circuit elements complicate the analysis. The inductance of the MOSFET source lead, inside the package and in the circuit wiring which is common to both the drain and gate current paths, produces a voltage at the source which reduces the gate drive current. The voltage is determined by Ldi/dt, but since di/dt is a function of drain current, the mathematical solution is complex. The MOSFET output capacitance also complicates the mathematics. And finally, MOSFETs have finite internal gate resistance which effectively adds to the resistance of the driving source, but the internal resistance is difficult to measure and, consequently, is not specified.

The resistive switching time variation versus gate resistance (Figure 9) shows how typical switching performance is affected by the parasitic circuit elements. If the parasitics were not present, the slope of the curves would maintain a value of unity regardless of the switching speed. The circuit used to obtain the data is constructed to minimize common inductance in the drain and gate circuit loops and is believed readily achievable with board mounted components. Most power electronic loads are inductive; the data in the figure is taken with a resistive load, which approximates an optimally snubbed inductive load. Power MOSFETs may be safely operated into an inductive load; however, snubbing reduces switching losses.





Figure 7. Capacitance Variation





The switching characteristics of a MOSFET body diode are very important in systems using it as a freewheeling or commutating diode. Of particular interest are the reverse recovery characteristics which play a major role in determining switching losses, radiated noise, EMI and RFI.

System switching losses are largely due to the nature of the body diode itself. The body diode is a minority carrier device, therefore it has a finite reverse recovery time,  $t_{rr}$ , due to the storage of minority carrier charge,  $Q_{RR}$ , as shown in the typical reverse recovery wave form of Figure 14. It is this stored charge that, when cleared from the diode, passes through a potential and defines an energy loss. Obviously, repeatedly forcing the diode through reverse recovery further increases switching losses. Therefore, one would like a diode with short  $t_{rr}$  and low  $Q_{RR}$  specifications to minimize these losses.

The abruptness of diode reverse recovery effects the amount of radiated noise, voltage spikes, and current ringing. The mechanisms at work are finite irremovable circuit parasitic inductances and capacitances acted upon by high di/dts. The diode's negative di/dt during  $t_a$  is directly controlled by the device clearing the stored charge. However, the positive di/dt during  $t_b$  is an uncontrollable diode characteristic and is usually the culprit that induces current ringing. Therefore, when comparing diodes, the ratio of  $t_b/t_a$  serves as a good indicator of recovery abruptness and thus gives a comparative estimate of probable noise generated. A ratio of 1 is considered ideal and values less than 0.5 are considered snappy.

Compared to ON Semiconductor standard cell density low voltage MOSFETs, high cell density MOSFET diodes are faster (shorter  $t_{rr}$ ), have less stored charge and a softer reverse recovery characteristic. The softness advantage of the high cell density diode means they can be forced through reverse recovery at a higher di/dt than a standard cell MOSFET diode without increasing the current ringing or the noise generated. In addition, power dissipation incurred from switching the diode will be less due to the shorter recovery time and lower switching losses.




Figure 10. Diode Forward Voltage versus Current

## SAFE OPERATING AREA


The Forward Biased Safe Operating Area curves define the maximum simultaneous drain–to–source voltage and drain current that a transistor can handle safely when it is forward biased. Curves are based upon maximum peak junction temperature and a case temperature ( $T_C$ ) of 25°C. Peak repetitive pulsed power limits are determined by using the thermal response data in conjunction with the procedures discussed in AN569, "Transient Thermal Resistance – General Data and Its Use."

Switching between the off-state and the on-state may traverse any load line provided neither rated peak current  $(I_{DM})$  nor rated voltage  $(V_{DSS})$  is exceeded, and that the transition time  $(t_r, t_f)$  does not exceed 10 µs. In addition the

total power averaged over a complete switching cycle must not exceed  $(T_{J(MAX)} - T_C)/(R_{\theta JC})$ .

A power MOSFET designated E–FET can be safely used in switching circuits with unclamped inductive loads. For reliable operation, the stored energy from circuit inductance dissipated in the transistor while in avalanche must be less than the rated limit and must be adjusted for operating conditions differing from those specified. Although industry practice is to rate in terms of energy, avalanche energy capability is not a constant. The energy rating decreases non–linearly with an increase of peak current in avalanche and peak junction temperature.

**Starting Junction Temperature** 



Safe Operating Area

## **TYPICAL ELECTRICAL CHARACTERISTICS**




Figure 13. Thermal Response





Figure 14. Diode Reverse Recovery Waveform

#### PACKAGE DIMENSIONS

SO-8 CASE 751-07 **ISSUE AB** 



NOTES:

- DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
  CONTROLLING DIMENSION: MILLIMETER.
  DIMENSION A AND B DO NOT INCLUDE MOLD PROTRUSION.
  MAXIMUM MOLD PROTRUSION 0.15 (0.006)

- PER SIDE.
- 5. DIMENSION D DOES NOT INCLUDE DAMBAR PROTRUSION. ALLOWABLE DAMBAR PROTRUSION SHALL BE 0.127 (0.005) TOTAL IN EXCESS OF THE D DIMENSION AT
- MAXIMUM MATERIAL CONDITION. 751–01 THRU 751–06 ARE OBSOLETE. NEW 6 STANDARD IS 751-07.

	MILLIMETERS		INC	HES	
DIM	MIN	MAX	MIN	MAX	
Α	4.80	5.00	0.189	0.197	
В	3.80	4.00	0.150	0.157	
С	1.35	1.75	0.053	0.069	
D	0.33	0.51	0.013	0.020	
G	1.27 BSC		0.050 BSC		
Н	0.10	0.25	0.004	0.010	
J	0.19	0.25	0.007	0.010	
Κ	0.40	1.27	0.016	0.050	
Μ	0 °	8 °	0 °	8 °	
Ν	0.25	0.50	0.010	0.020	
S	5 80	6 20	0 228	0 244	


STYLE 11 SOURCE 1 PIN 1. 2. GATE 1 3. SOURCE 2 4. GATE 2 5. DRAIN 2 DRAIN 2 6.

- DRAIN 1 7.
- DRAIN <sup>1</sup> 8.

¥

1.52

0.060



\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and in the registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights or the rights of others. SCILLC products are not designed, intended, or authorized for use a components in systems intended for surgical implant into the body, or other applications Intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

#### PUBLICATION ORDERING INFORMATION

#### LITERATURE FULFILLMENT

Literature Distribution Center for ON Semiconductor P.O. Box 5163, Denver, Colorado 80217 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303–675–2176 or 800–344–3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free USA/Canada

Japan: ON Semiconductor, Japan Customer Focus Center 2-9-1 Kamimeguro, Meguro-ku, Tokyo, Japan 153-0051 Phone: 81-3-5773-3850

ON Semiconductor Website: http://onsemi.com

Order Literature: http://www.onsemi.com/litorder

For additional information, please contact your local Sales Representative.