

March 2015

FDD6796A / FDU6796A_F071

N-Channel PowerTrench® MOSFET 25 V, 5.7 m Ω

Features

- Max $r_{DS(on)} = 5.7 \text{ m}\Omega$ at $V_{GS} = 10 \text{ V}$, $I_D = 20 \text{ A}$
- Max $r_{DS(on)}$ = 15.0 m Ω at V_{GS} = 4.5 V, I_D = 15.2 A
- 100% UIL tested
- RoHS Compliant




General Description

This N-Channel MOSFET has been designed specifically to improve the overall efficiency of DC/DC converters using either synchronous or conventional switching PWM controllers. It has been optimized for low gate charge, low $r_{\text{DS(on)}}$ and fast switching speed.

Applications

- Vcore DC-DC for Desktop Computers and Servers
- VRM for Intermediate Bus Architecture



MOSFET Maximum Ratings T_C = 25 °C unless otherwise noted

Symbol	Parameter	Parameter			
V_{DS}	Drain to Source Voltage			25	V
V_{GS}	Gate to Source Voltage			±20	V
I _D	Drain Current -Continuous (Package limited)	T _C = 25 °C		40	
	-Continuous (Silicon limited)	T _C = 25 °C		67	_
	-Continuous	T _A = 25 °C	(Note 1a)	20	Α
	-Pulsed			150	
E _{AS}	Single Pulse Avalanche Energy		(Note 3)	40	mJ
D	Power Dissipation	T _C = 25 °C		42	W
P_{D}	Power Dissipation	T _A = 25 °C	(Note 1a)	3.7	VV
T _J , T _{STG}	Operating and Storage Junction Temperature R	ange		-55 to +175	°C

Thermal Characteristics

$R_{\theta JC}$	Thermal Resistance, Junction to Case	3.6	°C/W
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient (Note 1	a) 40	C/VV

Package Marking and Ordering Information

Device Marking	Device	Package	Reel Size	Tape Width	Quantity
FDD6796A	FDD6796A	D-PAK (TO-252)	13 "	16 mm	2500 units
FDU6796A	FDU6796A_F071	TO-251AA	N/A(Tube)	N/A	75 units

Electrical Characteristics $T_J = 25$ °C unless otherwise noted

Symbol	Parameter	Test Conditions	Min	Тур	Max	Units			
Off Characteristics									
BV_{DSS}	Drain to Source Breakdown Voltage	$I_D = 250 \mu A, V_{GS} = 0 V$	25			V			
$\frac{\Delta BV_{DS}}{\Delta T_{J}}$	Breakdown Voltage Temperature Coefficient	I_D = 250 μ A, referenced to 25 °C		16		mV/°C			
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} = 20 V, V _{GS} = 0 V			1	μΑ			
I_{GSS}	Gate to Source Leakage Current	$V_{GS} = \pm 20 \text{ V}, V_{DS} = 0 \text{ V}$			±100	nA			

On Characteristics

V _{GS(th)}	Gate to Source Threshold Voltage	$V_{GS} = V_{DS}, I_D = 250 \mu A$	1.0	1.9	3.0	V
$\frac{\Delta V_{GS(th)}}{\Delta T_J}$	Gate to Source Threshold Voltage Temperature Coefficient	I_D = 250 μ A, referenced to 25 °C		-6		mV/°C
		$V_{GS} = 10 \text{ V}, I_D = 20 \text{ A}$		4.3	5.7	
r _{DS(on)}	Static Drain to Source On Resistance	V _{GS} = 4.5 V, I _D = 15.2 A		11.1	15.0	mΩ
		V _{GS} = 10 V, I _D = 20 A, T _J = 150 °C		6.5	8.6	
g _{FS}	Forward Transconductance	V _{DS} = 5 V, I _D = 20 A		118		S

Dynamic Characteristics

C _{iss}	Input Capacitance	V 42.V.V 0.V	1336	1780	pF
C _{oss}	Output Capacitance	$V_{DS} = 13 \text{ V}, V_{GS} = 0 \text{ V},$ f = 1 MHz	298	400	pF
C _{rss}	Reverse Transfer Capacitance	1 - 1 101112	266	400	pF
R_g	Gate Resistance		1.2		Ω

Switching Characteristics


t _{d(on)}	Turn-On Delay Time		8	16	ns
t _r	Rise Time	V _{DD} = 13 V, I _D = 20 A,	7	14	ns
t _{d(off)}	Turn-Off Delay Time	$V_{GS} = 10 \text{ V}, R_{GEN} = 6 \Omega$	19	34	ns
t _f	Fall Time		4	10	ns
Q_g	Total Gate Charge	V _{GS} = 0 V to 10 V	24	34	nC
Qg	Total Gate Charge	$V_{GS} = 0 \text{ V to 5 V}$ $V_{DD} = 13 \text{ V},$	14	20	nC
Q _{gs}	Gate to Source Charge	I _D = 20 A	4.0		nC
Q_{gd}	Gate to Drain "Miller" Charge		5.7		nC

Drain-Source Diode Characteristics

Ved Source to Drain Diode Forward Voltage	Source to Drain Diode, Forward Voltage	$V_{GS} = 0 \text{ V}, I_{S} = 3.1 \text{ A}$ (Note 2)		0.8 1	1.2	V
	$V_{GS} = 0 \text{ V}, I_S = 20 \text{ A}$ (Note 2)		0.9	1.3	V	
t _{rr}	Reverse Recovery Time	I _F = 20 A, di/dt = 100 A/μs		15	27	ns
Q _{rr}	Reverse Recovery Charge			4	10	nC

The R_{BJA} is the sum of the junction-to-case and case-to-ambient thermal resistance where the case thermal reference is defined as the solder mounting surface of the drain pins.

R_{BJC} is guaranteed by design while R_{BJA} is determined by the user's board design.



a) 40 °C/W when mounted on a 1 in² pad of 2 oz copper



b) 96 °C/W when mounted on a minimum pad

- 2: Pulse Test: Pulse Width < 300 μ s, Duty cycle < 2.0%. 3: E_{AS} of 40 mJ is based on starting T_J = 25 °C, L = 1 mH, I_{AS} = 9 A, V_{DD} = 23 V, V_{GS} = 10 V. 100% test at L = 0.1 mH, I_{AS} = 21 A.

Typical Characteristics T_J = 25 °C unless otherwise noted




Figure 1. On Region Characteristics




Figure 3. Normalized On Resistance vs Junction Temperature




Figure 5. Transfer Characteristics




Figure 2. Normalized On-Resistance vs Drain Current and Gate Voltage




Figure 4. On-Resistance vs Gate to Source Voltage




Figure 6. Source to Drain Diode Forward Voltage vs Source Current

Typical Characteristics $T_J = 25$ °C unless otherwise noted




Figure 7. Gate Charge Characteristics




Figure 9. Unclamped Inductive Switching Capability




Figure 11. Forward Bias Safe Operating Area




Figure 8. Capacitance vs Drain to Source Voltage




Figure 10. Maximum Continuous Drain Current vs Case Temperature




Figure 12. Single Pulse Maximum Power Dissipation

Typical Characteristics $T_J = 25$ °C unless otherwise noted




Figure 13. Junction-to-Case Transient Thermal Response Curve




Figure 14. Junction-to-Ambient Transient Thermal Response Curve







TRADEMARKS

The following includes registered and unregistered trademarks and service marks, owned by Fairchild Semiconductor and/or its global subsidiaries, and is not intended to be an exhaustive list of all such trademarks.

AccuPower™ F-PFS™ AttitudeEngine™ FRFET®

Global Power ResourceSM Awinda[®] AX-CAP®*

GreenBridge™ BitSiC™ Green FPS™ Build it Now™ Green FPS™ e-Series™

CorePLUS™ Gmax™ CorePOWER™ $\mathsf{GTO}^{\mathsf{TM}}$ CROSSVOLT™ IntelliMAX™ CTL™ ISOPLANAR™

Current Transfer Logic™ Making Small Speakers Sound Louder

DEUXPEED® and Better™ Dual Cool™ MegaBuck™ EcoSPARK® MIČROCOUPLER™ EfficientMax™ MicroFET™

MicroPak™ MicroPak2™ MillerDrive™ MotionMax™ Fairchild Semiconductor®

MotionGrid® FACT Quiet Series™ MTi[®] FACT[®] MTx® FastvCore™ MVN® FETBench™ mWSaver® FPS™ OptoHiT™ OPTOLOGIC® OPTOPLANAR®

Power Supply WebDesigner™ PowerTrench®

PowerXSTI

Programmable Active Droop™ OFFT

QS™ Quiet Series™ RapidConfigure™

Saving our world, 1mW/W/kW at a time™

SignalWise™ SmartMax™ SMART START™

Solutions for Your Success™

SPM® STEALTH™ SuperFET® SuperSOT™-3 SuperSOT™-6 SuperSOT™-8 SupreMOS® SyncFET™ Sync-Lock™

SYSTEM SYSTEM TinyBoost[®] TinyBuck[®] TinyCalc™ TinyLogic[®] TINYOPTO™

TinvPower™ TinyPWM™ TinyWire™ TranSiC™ TriFault Detect™

TRUECURRENT®* սSerDes™

UHC Ultra FRFET™

UniFET™ VCX™ VisualMax™ VoltagePlus™ XSTM. Xsens™ 仙童®

ESBC™

-®

Fairchild®

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION, OR DESIGN. TO OBTAIN THE LATEST, MOST UP-TO-DATE DATASHEET AND PRODUCT INFORMATION, VISIT OUR <u>AIRCHILDSEMI.COM.</u> FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS. THESE SPECIFICATIONS DO NOT EXPAND THE TERMS OF FAIRCHILD'S WORLDWIDE TERMS AND CONDITIONS, SPECIFICALLY THE WARRANTY THEREIN, WHICH COVERS THESE PRODUCTS.

Unless otherwise specified in this data sheet, this product is a standard commercial product and is not intended for use in applications that require extraordinary levels of quality and reliability. This product may not be used in the following applications, unless specifically approved in writing by a Fairchild officer: (1) automotive or other transportation, (2) military/aerospace, (3) any safety critical application - including life critical medical equipment - where the failure of the Fairchild product reasonably would be expected to result in personal injury, death or property damage. Customer's use of this product is subject to agreement of this Authorized Use policy. In the event of an unauthorized use of Fairchild's product, Fairchild accepts no liability in the event of product failure. In other respects, this product shall be subject to Fairchild's Worldwide Terms and Conditions of Sale, unless a separate agreement has been signed by both Parties.

ANTI-COUNTERFEITING POLICY

Fairchild Semiconductor Corporation's Anti-Counterfeiting Policy. Fairchild's Anti-Counterfeiting Policy is also stated on our external website, www.fairchildsemi.com,

Counterfeiting of semiconductor parts is a growing problem in the industry. All manufacturers of semiconductor products are experiencing counterfeiting of their parts. Customers who inadvertently purchase counterfeit parts experience many problems such as loss of brand reputation, substandard performance, failed applications, and increased cost of production and manufacturing delays. Fairchild is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. Fairchild strongly encourages customers to purchase Fairchild parts either directly from Fairchild or from Authorized Fairchild Distributors who are listed by country on our web page cited above. Products customers buy either from Fairchild directly or from Authorized Fairchild Distributors are genuine parts, have full traceability, meet Fairchild's quality standards for handling and storage and provide access to Fairchild's full range of up-to-date technical and product information. Fairchild and our Authorized Distributors will stand behind all warranties and will appropriately address any warranty issues that may arise. Fairchild will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. Fairchild is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

PRODUCT STATUS DEFINITIONS

Definition of Terms

Deminition of Terms		
Datasheet Identification	Product Status	Definition
Advance Information	Formative / In Design	Datasheet contains the design specifications for product development. Specifications may change in any manner without notice.
Preliminary	First Production	Datasheet contains preliminary data; supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve design.
No Identification Needed	Full Production	Datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve the design.
Obsolete	Not In Production	Datasheet contains specifications on a product that is discontinued by Fairchild Semiconductor. The datasheet is for reference information only.

Rev 177

^{*} Trademarks of System General Corporation, used under license by Fairchild Semiconductor.