

October 2008

# FIN1027 / FIN1027A — 3.3V LVDS, 2-Bit, High-Speed, Differential Driver

### **Features**

- Greater than 600Mbs Data Rate
- 3V Power Supply Operation
- 5ns Maximum Differential Pulse Skew
- 1.5ns Maximum Propagation Delay
- Low Power Dissipation
- Power-Off Protection
- Meets or Exceeds the TIA/EIA-644 LVDS Standard
- Flow-through Pinout Simplifies PCB Layout

# Description

This dual driver is designed for high-speed interconnects utilizing Low Voltage Differential Signaling (LVDS) technology. The driver translates LVTTL signal levels to LVDS levels with a typical differential output swing of 350mV, which provides low EMI at ultra-low power dissipation, even at high frequencies. This device is ideal for high-speed transfer of clock or data.

The FIN1027 or FIN1027A can be paired with its companion receiver, the FIN1028, or with any other LVDS receiver.

# **Ordering Information**

Part Number	Operating Temperature Range	© Eco Status	Package	Packing Method
FIN1027M	-40 to +85°C	RoHS 8-Lead Small Outline Package (SOIC) JEDEC MS-012, 0.150 inch Narrow		Trays
FIN1027MX	-40 to +85°C	RoHS	8-Lead Small Outline Package (SOIC) JEDEC MS-012, 0.150 inch Narrow	
FIN1027K8X	-40 to +85°C	Green 8-Lead US8, JEDEC MO-187, Variation CA 3.1mm Wide		Tape and Reel
FIN1027AM	-40 to +85°C	RoHS	8-Lead Small Outline Package (SOIC) JEDEC MS-012, 0.150 inch Narrow	Trays
FIN1027AMX	-40 to +85°C	RoHS	RoHS  8-Lead Small Outline Package (SOIC) JEDEC MS-012, 0.150 inch Narrow  Ta	

For Fairchild's definition of "green" Eco Status, please visit: http://www.fairchildsemi.com/company/green/rohs\_green.html.

# **Pin Configuration**




Figure 1. FIN1027 SOIC Pin Assignment (Top View) Figure 2. FIN1027A SOIC Pin Assignment (Top View)




Figure 3. FIN1027 US8 Pin Assignment (Top View)

# **Pin Definitions**

Name	Pin # FIN1027 SOIC	Pin # FIN1027A SOIC	Pin # FIN1027 US8	Description	
$V_{CC}$	1	1	8	Power Supply	
D <sub>IN1</sub>	2	2	7	LVTTL Data Input	
D <sub>IN2</sub>	3	3	6	LVTTL Data Input	
GND	4	4	5	Ground	
D <sub>OUT2</sub> -	5	5	4	Inverting Driver Output	
D <sub>OUT2+</sub>	6	6	3	Non-Inverting Driver Output	
D <sub>OUT1+</sub>	7	8	2	Non-Inverting Driver Output	
D <sub>OUT1</sub> -	8	7	1	Inverting Driver Output	

# **Function Table**

Input	Out	puts
D <sub>IN</sub>	D <sub>OUT+</sub>	D <sub>OUT-</sub>
LOW	LOW	HIGH
HIGH	HIGH	LOW
OPEN	LOW	HIGH

# **Absolute Maximum Ratings**

Stresses exceeding the absolute maximum ratings may damage the device. The device may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only.

Symbol	Parameter	Min.	Max.	Unit
V <sub>CC</sub>	Supply Voltage	-0.5	4.6	V
D <sub>IN</sub>	DC Input Voltage	-0.5	6.0	V
D <sub>OUT</sub>	DC Output Voltage	-0.5	4.7	V
I <sub>OSD</sub>	Driver Short-Circuit Current	Conti	Continuous	
T <sub>STG</sub>	Storage Temperature Range	-65	+150	°C
$T_J$	Maximum Junction Temperature		+150	°C
TL	Lead Temperature, Soldering, 10 Seconds		+260	°C
ESD	Human Body Model, JESD22-A114		≥6500	V
E2D	Machine Model, JESD22-A115		≥400	V

# **Recommended Operating Conditions**

The Recommended Operating Conditions table defines the conditions for actual device operation. Recommended operating conditions are specified to ensure optimal performance to the datasheet specifications. Fairchild does not recommend exceeding them or designing to Absolute Maximum Ratings.

Symbol	Parameter	Min.	Max.	Unit
V <sub>CC</sub>	Supply Voltage	3.0	3.6	V
V <sub>IN</sub>	Input Voltage	0	V <sub>CC</sub>	V
T <sub>A</sub>	Operating Temperature	-40	+85	°C

### **DC Electrical Characteristics**

All typical values are at  $T_A = 25^{\circ}C$  and  $V_{CC} = 3.3V$ . Over-supply voltage and operating temperature ranges, unless otherwise noted.

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Units
V <sub>OD</sub>	Output Differential Voltage		250	350	450	mV
$\Delta V_{OD}$	V <sub>OD</sub> Magnitude Change from Differential LOW-to-HIGH	B. 4000 Figure 4			25	mV
Vos	Offset Voltage	$R_L = 100\Omega$ , Figure 4	1.125	1.250	1.375	V
ΔVos	Offset Magnitude Change from Differential LOW-to-HIGH				25	mV
l <sub>OFF</sub>	Power-Off Output current	$V_{CC} = 0V$ , $V_{OUT} = 0V$ or 3.6V			±20	μΑ
	Short-Circuit Output Current	V <sub>OUT</sub> = 0V			-8	mA
I <sub>OS</sub>		$V_{OD} = 0V$			±8	
V <sub>IH</sub>	Input HIGH Voltage		2.0		Vcc	V
V <sub>IL</sub>	Input LOW Voltage		GND		0.8	V
I <sub>IN</sub>	Input Current	$V_{IN} = 0V \text{ or } V_{CC}$			±20	μΑ
I <sub>I(OFF)</sub>	Power-Off Input Current	$V_{CC} = 0V$ , $V_{IN} = 0V$ or 3.6V			±20	μΑ
V <sub>IK</sub>	Input Clamp Voltage	I <sub>IK</sub> = -18mA	-1.5			V
/ ·	Barrer Committee Committee	No Load, V <sub>IN</sub> = 0V or V <sub>CC</sub>			12.5	mA
I <sub>CC</sub>	Power Supply Current	$R_L = 100\Omega$ , $V_{IN} = 0V$ or $V_{CC}$			17.0	mA
C <sub>IN</sub>	Input Capacitance			4		pF
Соит	Output Capacitance			6		pF

# **AC Electrical Characteristics**

All typical values are at  $T_A = 25^{\circ}\text{C}$  and  $V_{CC} = 3.3\text{V}$ . Over-supply voltage and operating temperature ranges, unless otherwise noted.

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Units
t <sub>PLHD</sub>	Differential Propagation Delay, LOW-to-HIGH		0.5		1.5	ns
t <sub>PHLD</sub>	Differential Propagation Delay, HIGH-to-LOW		0.5		1.5	ns
t <sub>TLHD</sub>	Differential Output Rise Time (20% to 80%)	$R_L = 100\Omega,$ $C_L = 10pF,$	0.4		1.0	ns
t <sub>THLD</sub>	Differential Output Fall Time (80% to 20%)	Figure 5, Figure 6	0.4		1.0	ns
t <sub>SK(P)</sub>	Pulse Skew   t <sub>PLH</sub> - t <sub>PHL</sub>				0.5	ns
t <sub>SK(LH)</sub> , t <sub>SK(HL)</sub>	Channel-to-Channel Skew <sup>(1)</sup>				0.3	ns
t <sub>SK(PP)</sub>	Part-to-Part Skew <sup>(2)</sup>				1.0	ns

#### Notes:

- 1.  $t_{SK(LH)}$ ,  $t_{SK(HL)}$  is the skew between specified outputs of a single device when the outputs have identical loads and are switching in the same direction.
- 2. t<sub>SK(PP)</sub> is the magnitude of the difference in propagation delay times between any specified terminals of two devices switching in the same direction (either LOW-to-HIGH or HIGH-to-LOW) when both devices operate with the same supply voltage, same temperature, and have identical test circuits.

# **Test Diagrams**





Figure 4. Differential Driver DC Test Circuit



Note A: All input pulses have frequency = 10MHz,  $t_R$  or  $t_F$  =2ns.

Note B:  $C_L$  includes all probe and fixture capacitances.

Figure 5. Differential Driver Propagation Delay and Transition Time Test Circuit




Figure 6. AC Waveforms

# **Typical Performance Characteristics**




Figure 7. Output High Voltage vs. Power Supply Voltage




Figure 9. Output Short Circuit Current vs. Power Supply Voltage




Figure 11. Differential Output Voltage vs. Load Resistor




Figure 8. Output Low Voltage vs. Power Supply Voltage




Figure 10. Differential Output Voltage vs. Power Supply Voltage




Figure 12. Offset Voltage vs. Power Supply Voltage

# **Typical Performance Characteristics** (Continued)




Figure 13. Power Supply Current vs. Frequency




Figure 14. Power Supply Current vs. Power Supply Voltage




Figure 15. Power Supply Current vs. Ambient Temperature




Figure 16. Differential Propagation Delay vs. Power Supply




Figure 17. Differential Propagation Delay vs. Ambient Temperature




Figure 18. Differential Skew (t<sub>PLH</sub>-t<sub>PHL</sub>) vs. Power Supply

# **Typical Performance Characteristics** (Continued)




Figure 19. Differential Pulse Skew (tplh-tphl)




Figure 20. Transition Time vs. Power Supply Voltage




Figure 21. Transition Time vs. Ambient Temperature

# **Physical Dimensions**





Figure 22. 8-Lead, Small Outline Package (SOIC), JEDEC MS-012, 0.150-inch, Narrow Body


Click here for tape and reel specifications, available at: http://www.fairchildsemi.com/products/discrete/pdf/soic8\_tr.pdf


Package drawings are provided as a service to customers considering Fairchild components. Drawings may change in any manner without notice. Please note the revision and/or date on the drawing and contact a Fairchild Semiconductor representative to verify or obtain the most recent revision. Package specifications do not expand the terms of Fairchild's worldwide terms and conditions, specifically the warranty therein, which covers Fairchild products.

Always visit Fairchild Semiconductor's online packaging area for the most recent package drawings: http://www.fairchildsemi.com/packaging/.


# **Physical Dimensions**








#### LAND PATTERN RECOMMENDATION





#### **DETAIL A**

#### NOTES:

- A. CONFORMS TO JEDEC REGISTRATION MO-187
- B. DIMENSIONS ARE IN MILLIMETERS.
- C. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH, AND TIE BAR EXTRUSIONS.
- D. DIMENSIONS AND TOLERANCES PER ANSI Y14.5M, 1982.

#### MAB08AREVC

# Figure 23. 8-Lead US8, JEDEC MO-187, Variation CA 3.1mm Wide

Package drawings are provided as a service to customers considering Fairchild components. Drawings may change in any manner without notice. Please note the revision and/or date on the drawing and contact a Fairchild Semiconductor representative to verify or obtain the most recent revision. Package specifications do not expand the terms of Fairchild's worldwide terms and conditions, specifically the warranty therein, which covers Fairchild products.

Always visit Fairchild Semiconductor's online packaging area for the most recent package drawings: http://www.fairchildsemi.com/packaging/.





#### TRADEMARKS

The following includes registered and unregistered trademarks and service marks, owned by Fairchild Semiconductor and/or its global subsidiaries, and is not intended to be an exhaustive list of all such trademarks.

Build it Now™ CorePLUS™ CorePOWER™

CROSSVOLT™ CTL™

Current Transfer Logic™ EcoSPARK® EfficentMax™ EZSWTCH™\*

Fairchild®

Fairchild Semiconductor® FACT Quiet Series™

FACT<sup>®</sup> FAST® FastvCore™

FlashVVriter® FPS™ F-PEST

FRFET® Global Power Resource SM

Green FPS™ Green FPS™ e-Series™

**GTOTM** IntelliMAX™ ISOPLANAR™ MegaBuck™ MICROCOUPLER™

MicroFET™ MicroPak™ MillerDrive™ MotionMax™ Motion-SPM™ OPTOLOGIC® OPTOPLANAR®

PDP SPM™ Power-SPM™ PowerTrench® PowerXS™

Programmable Active Droop™

QFET\* OSTM

Quiet Series™ RapidConfigure™

Saving our world, 1mWWWkW at a time™ SmartMax™

SMART START™ SPM<sup>®</sup> STEALTH™ SuperFET™ SuperSOT\*\*3 SuperSOT\*\*6 SuperSOT\*\*8 SupreMOS™

SyncFET™

SYSTEM ® The Power Franchise®



UHC® Ultra FRFET™ UniFET™ VCXTM

VisualMax™ XS™

\* EZSWTCH™ and FlashWriter® are trademarks of System General Corporation, used under license by Fairchild Semiconductor.

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION, OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS. THES SPECIFICATIONS DO NOT EXPAND THE TERMS OF FAIRCHILD'S WORLDWIDE TERMS AND CONDITIONS, SPECIFICALLY THE WARRANTY THEREIN, WHICH COVERS THESE PRODUCTS.

#### LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION.

#### As used herein:

- Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user
- 2. A critical component in any component of a life support, device, or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

#### ANTI-COUNTERFEITING POLICY

Fairchild Semiconductor Corporation's Anti-Counterfeiting Policy: Fairchild's Anti-Counterfeiting Policy is also stated on our external website, www.fairchildsemi.com, under Sales Support

Counterfeiting of semiconductor parts is a growing problem in the industry. All manufacturers of semiconductor products are experiencing counterfeiting of their parts. Customers who inadvertently purchase counterfeit parts experience many problems such as loss of brand reputation, substandard performance, failed applications, and increased cost of production and manufacturing delays. Fairchild is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. Fairchild strongly encourages customers to purchase Fairchild parts either directly from Fairchild or from Authorized Fairchild Distributors who are listed by country on our web page cited above. Products customers buy either from Fairchild directly or from Authorized Fairchild Distributors are genuine parts, have full traceability, meet Fairchild's quality standards for handling and storage and provide access to Fairchild's full range of up-to-date technical and product information. Fairchild and our Authorized Distributors will stand behind all warranties and will appropriately address any warranty issues that may arise. Fairchild will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. Fairchild is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

#### PRODUCT STATUS DEFINITIONS

#### Definition of Terms

Datasheet Identification	Product Status	Definition		
Advance Information	Formative / In Design	Datasheet contains the design specifications for product development. Specifications may change in any manner without notice.		
Preliminary	First Production	Datasheet contains preliminary data; supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve design.		
No Identification Needed	Full Production	Datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve the design.		
Obsolete	Not In Production	Datasheet contains specifications on a product that is discontinued by Fairchild Semiconductor. The datasheet is for reference information only.		

Rev. 137