**ON Semiconductor** 

Is Now

# Onsemi

To learn more about onsemi<sup>™</sup>, please visit our website at <u>www.onsemi.com</u>

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product factures, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and asfety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or by customer's technical experts. onsemi products and actal performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application, Buyer shall indemnify and hold onsemi and its officers, employees, subsidiari

# MOSFET - Power, Single N-Channel, DUAL COOL<sup>™</sup>, DFN8 5x6.15

**40 V, 1.0 mΩ, 288 A** 

# NTMFSC1D0N04HL

#### Features

- Advanced Dual-Side Cooled Packaging
- Ultra Low R<sub>DS(on)</sub> to Minimize Conduction Losses
- Low Qg and Qoss to Minimize Charge Losses
- MSL1 Robust Packaging Design
- These Devices are Pb–Free, Halogen Free/BFR Free and are RoHS Compliant

#### **Typical Applications**

- DC-DC Conversion
- Orring FET/Load Switching
- Synchronous Rectification

#### **MAXIMUM RATINGS** (T<sub>J</sub> = 25°C, Unless otherwise specified)

<b>MAXIMOW RATINGS</b> (1) = 23 C, Othess otherwise specified)							
Parameter			Symbol	Value	Unit		
Drain-to-Source Breakdown Voltage			V <sub>(BR)DSS</sub>	40	V		
Gate-to-Source Voltage			V <sub>GS</sub>	±20	V		
Continuous Drain Current R <sub>θJC</sub> (Note 2)	Steady State	, , , , , , , , , , , , , , , , , , , ,		288	A		
Power Dissipation $R_{\theta JC}$ (Note 2)	Slale	-	PD	166	W		
Continuous Drain Current R <sub>θJA</sub> (Note 1, 2)	Steady State	T₄ = 25°C	Ι <sub>D</sub>	43	A		
Power Dissipation $R_{\theta JA}$ (Note 1, 2)	Sidle		PD	3.8	W		
Pulsed Drain Current	$T_A = 25^{\circ}C$	, t <sub>p</sub> = 100 μs	I <sub>DM</sub>	1189	А		
Operating Junction and Storage Tempera- ture Range			T <sub>J</sub> , T <sub>stg</sub>	–55 to +175	°C		
Source Current (Body Diode)			۱ <sub>S</sub>	177	А		
Single Pulse Drain-to-Source Avalanche Energy (I <sub>AV</sub> = 45 A)			E <sub>AS</sub>	304	mJ		
Lead Temperature Soldering Reflow for Sol- dering Purposes (1/8" from case for 10 s)			ΤL	260	°C		

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Surface-mounted on FR4 board using 1 in<sup>2</sup> pad size, 1 oz Cu pad.

The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.




# **ON Semiconductor®**

#### www.onsemi.com

V <sub>(BR)DSS</sub>	R <sub>DS(ON)</sub> MAX	I <sub>D</sub> MAX
40 V	1.0 m $\Omega$ @ 10 V	288 A
	1.5 mΩ @ 4.5 V	288 A








DFN8 5x6.15 CASE 506EG

#### MARKING DIAGRAM



1D0N04 = Specific Device Code A = Assembly Plant Code YWW = Date Code (Year & Week) ZZ = Lot Code

ORDERING INFORMATION

See detailed ordering and shipping information on page 5 of this data sheet.

#### THERMAL CHARACTERISTICS

Symbol	Parameter	Мах	Unit
$R_{ extsf{ heta}JC}$	Junction-to-Case - Steady State (Note 2)	0.9	°C/W
$R_{\theta JT}$	Junction-to-Top Source - Steady State (Note 2)	1.4	
$R_{ hetaJA}$	Junction-to-Ambient - Steady State (Note 2)	39	


#### **ELECTRICAL CHARACTERISTICS** ( $T_J = 25^{\circ}C$ unless otherwise noted)

Parameter	Symbol	Test Conditions		Min	Тур	Мах	Unit
OFF CHARACTERISTICS							
Drain-to-Source Breakdown Voltage	V <sub>(BR)DSS</sub>	$V_{GS}$ = 0 V, $I_D$ = 250 $\mu$ A		40			V
Drain-to-Source Breakdown Voltage Temperature Coefficient	V <sub>(BR)DSS</sub> / T <sub>J</sub>				25		mV/°C
Zero Gate Voltage Drain Current	I <sub>DSS</sub>	V <sub>GS</sub> = 0 V,	$T_J = 25^{\circ}C$			1	μA
		$V_{\rm DS} = 40$ V	T <sub>J</sub> = 125°C			250	
Gate-to-Source Leakage Current	I <sub>GSS</sub>	V <sub>DS</sub> = 0 V, V <sub>GS</sub> = 20 V				100	nA
ON CHARACTERISTICS (Note 3)							
Gate Threshold Voltage	V <sub>GS(TH)</sub>	$V_{GS} = V_{DS}, I_D = 250 \ \mu A$		1.2		2.0	V
Negative Threshold Temperature Coefficient	V <sub>GS(TH)</sub> <sup>/ T</sup> J	$I_D = 250 \ \mu$ A, ref to 25°C			-5.7		mV/°C
Drain-to-Source On Resistance	R <sub>DS(on)</sub>	V <sub>GS</sub> = 10 V, I <sub>D</sub>	= 50 A		0.8	1.0	mΩ
		V <sub>GS</sub> = 4.5 V, I <sub>D</sub>	= 40 A		1.2	1.5	
Forward Trans-conductance	9 <sub>FS</sub>	V <sub>DS</sub> = 15 V, I <sub>D</sub>	= 50A		500		S
Gate-Resistance	R <sub>G</sub>	V <sub>GS</sub> = 0 V, f = 1 MHz			1	2.6	Ω
CHARGES & CAPACITANCES	-						
Input Capacitance	C <sub>ISS</sub>	$V_{GS}$ = 0 V, f = 1 MHz, $V_{DS}$ = 20 V			5960		pF
Output Capacitance	C <sub>OSS</sub>				1360		
Reverse Transfer Capacitance	C <sub>RSS</sub>				59		
Total Gate Charge	Q <sub>G(TOT)</sub>	$V_{GS}$ = 10 V, $V_{DS}$ = 20 V, $I_{D}$ = 50 A			93		nC
Total Gate Charge	Q <sub>G(TOT)</sub>	V <sub>GS</sub> = 4.5 V, V <sub>DS</sub> = 20 V, I <sub>D</sub> = 50 A			43		
Threshold Gate Charge	Q <sub>G(TH)</sub>				8.7		
Gate-to-Source Charge	Q <sub>GS</sub>				15		nC
Gate-to-Drain Charge	Q <sub>GD</sub>				13		
Output Charge	Q <sub>OSS</sub>	V <sub>DD</sub> = 20 V, V <sub>GS</sub> = 0 V			86		nC
SWITCHING CHARACTERISTICS (No	ote 3)						
Turn-On Delay Time	t <sub>d(ON)</sub>	$V_{GS}$ = 4.5 V, $V_{DS}$ = 20 V, $I_{D}$ = 50 A, $R_{G}$ = 2.5 $\Omega$			28		ns
Rise Time	t <sub>r</sub>				36		
Turn-Off Delay Time	t <sub>d(OFF)</sub>				44		
Fall Time	t <sub>f</sub>				17		
DRAIN-SOURCE DIODE CHARACTE	RISTICS				•		
Forward Diode Voltage	V <sub>SD</sub>	V <sub>GS</sub> = 0 V, I <sub>S</sub> = 50 A	$T_J = 25^{\circ}C$		0.78	1.2	V
			T <sub>J</sub> = 150°C		0.6		
Reverse Recovery Time	t <sub>RR</sub>	$V_{GS}$ = 0 V, dI <sub>S</sub> /dt = 100 A/µs, I <sub>S</sub> = 50 A			54		ns
Reverse Recovery Charge	Q <sub>RR</sub>				78		nC


Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions. 3. Switching characteristics are independent of operating junction temperatures.

www.onsemi.com

#### **TYPICAL CHARACTERISTICS**



#### **TYPICAL CHARACTERISTICS**



#### **TYPICAL CHARACTERISTICS**




Figure 13. Transient Thermal Impedance


#### **ORDERING INFORMATION**

Device	Device Marking	Package	Shipping <sup>†</sup>
NTMFSC1D0N04HL	1D0N04	DFN8 5x6.15 (Pb–Free/Halogen Free)	3000 / Tape & Reel

<sup>+</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

DUAL COOL is a registered trademark of Semiconductor Components Industries, LLC (SCILLC) or its subsidiaries in the United States and/or other countries.

#### PACKAGE DIMENSIONS



DFN8 5x6.15, 1.27P, DUAL COOL

1. DIMENSIONING AND TOLERANCING PER

- CONTROLLING DIMENSION: MILLIMETERS
- COPLANARITY APPLIES TO THE EXPOSED PADS AS WELL AS THE TERMINALS.
- DIMENSIONS D1 AND E1 DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS.
- SEATING PLANE IS DEFINED BY THE TERMINALS. "A1" IS DEFINED AS THE DISTANCE FROM THE SEATING PLANE TO THE LOWEST POINT ON THE

MILLIMETERS

NOM 0.90

0.41

0.31

0.25

5,00

4.90

3.82

2.60 REF

0 86 REF

6.15

5.80

3.48

3.30 REF

0.50 REF

0.34 REF

0.30 REF

0.52 REF

1.27 BSC

0.635 BSC

1.40

0.66

0.62

----

MAX.

0.95

0.05

0.05

0.51

0.41

0.30

5,10

5.00

3.97

6.25

5.90

3.58

1.50

0.76

0.72

12°

ON Semiconductor and 💷 are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or deth associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

#### PUBLICATION ORDERING INFORMATION

#### LITERATURE FULFILLMENT:

#### TECHNICAL SUPPORT

ON Semiconductor Website: www.onsemi.com

Email Requests to: orderlit@onsemi.com

North American Technical Support: Voice Mail: 1 800–282–9855 Toll Free USA/Canada Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support: Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative