FAIRCHILD SEMICONDUCTOR™

April 2001

IGBT

SGS10N60RUF

Short Circuit Rated IGBT

General Description

Fairchild's RUF series of Insulated Gate Bipolar Transistors (IGBTs) provide low conduction and switching losses as well as short circuit ruggedness. The RUF series is designed for applications such as motor control, uninterrupted power supplies (UPS) and general inverters where short circuit ruggedness is a required feature.

Features

- Short circuit rated 10us @ T_C = 100°C, V_{GE} = 15V
- High speed switching
- Low saturation voltage : $V_{CE(sat)}$ = 2.2 V @ I_C = 10A
- High input impedance

Application

AC & DC Motor controls, general purpose inverters, robotics, servo controls



TO-220F



Absolute Maximum Ratings

T_C = 25°C unless otherwise noted

Symbol	Description		SGS10N60RUF	Units
V_{CES}	Collector-Emitter Voltage		600	V
V_{GES}	Gate-Emitter Voltage		± 20	V
I_C	Collector Current	@ T_C = 25°C	16	A
	Collector Current	@ T_C = 100°C	10	A
$I_{CM\ (1)}$	Pulsed Collector Current		30	A
T_{SC}	Short Circuit Withstand Time	@ T_C = 100°C	10	µs
P_D	Maximum Power Dissipation	@ T_C = 25°C	55	W
	Maximum Power Dissipation	@ T_C = 100°C	22	W
T_J	Operating Junction Temperature		-55 to +150	°C
T_{stg}	Storage Temperature Range		-55 to +150	°C
T_L	Maximum Lead Temp. for soldering Purposes, 1/8" from case for 5 seconds		300	°C

Notes :
(1) Repetitive rating : Pulse width limited by max. junction temperature

Thermal Characteristics

Symbol	Parameter	Typ.	Max.	Units
$R_{\theta JC}$	Thermal Resistance, Junction-to-Case	--	2.3	°C/W
$R_{\theta JA}$	Thermal Resistance, Junction-to-Ambient	--	62.5	°C/W

Electrical Characteristics of IGBT T_C = 25°C unless otherwise noted

Symbol	Parameter	Test Conditions	Min.	Typ.	Max.	Units
Off Characteristics						
BV_{CES}	Collector-Emitter Breakdown Voltage	V_{GE} = 0V, I_C = 250uA	600	--	--	V
$\Delta B_{VCES}/\Delta T_J$	Temperature Coeff. of Breakdown Voltage	V_{GE} = 0V, I_C = 1mA	--	0.6	--	V/°C
I_{CES}	Collector Cut-off Current	V_{CE} = V_{CES}, V_{GE} = 0V	--	--	250	µA
I_{GES}	G-E Leakage Current	V_{GE} = V_{GES}, V_{CE} = 0V	--	--	± 100	nA
On Characteristics						
$V_{GE(th)}$	G-E Threshold Voltage	I_C = 10mA, V_{CE} = V_{GE}	5.0	6.0	8.5	V
$V_{CE(sat)}$	Collector to Emitter Saturation Voltage	I_C = 10A, V_{GE} = 15V	--	2.2	2.8	V
		I_C = 16A, V_{GE} = 15V	--	2.5	--	V
Dynamic Characteristics						
C_{ies}	Input Capacitance	V_{CE} = 30V, V_{GE} = 0V, f = 1MHz	--	660	--	pF
C_{oes}	Output Capacitance		--	115	--	pF
C_{res}	Reverse Transfer Capacitance		--	25	--	pF
Switching Characteristics						
$t_{d(on)}$	Turn-On Delay Time	V_{CC} = 300 V, I_C = 10A, R_G = 20Ω, V_{GE} = 15V, Inductive Load, T_C = 25°C	--	15	--	ns
t_r	Rise Time		--	30	--	ns
$t_{d(off)}$	Turn-Off Delay Time		--	36	50	nS
t_f	Fall Time		--	158	200	ns
E_{on}	Turn-On Switching Loss		--	141	--	µJ
E_{off}	Turn-Off Switching Loss		--	215	--	µJ
E_{ts}	Total Switching Loss		--	356	500	µJ
$t_{d(on)}$	Turn-On Delay Time	V_{CC} = 300 V, I_C = 10A, R_G = 20Ω, V_{GE} = 15V, Inductive Load, T_C = 125°C	--	16	--	ns
t_r	Rise Time		--	33	--	ns
$t_{d(off)}$	Turn-Off Delay Time		--	42	60	ns
t_f	Fall Time		--	242	350	ns
E_{on}	Turn-On Switching Loss		--	161	--	µJ
E_{off}	Turn-Off Switching Loss		--	452	--	µJ
E_{ts}	Total Switching Loss		--	613	860	µJ
T_{sc}	Short Circuit Withstand Time	V_{CC} = 300 V, V_{GE} = 15V @ T_C = 100°C	10	--	--	µs
Q_g	Total Gate Charge	V_{CE} = 300 V, I_C = 10A, V_{GE} = 15V	--	30	45	nC
Q_{ge}	Gate-Emitter Charge		--	5	10	nC
Q_{gc}	Gate-Collector Charge		--	8	16	nC
Le	Internal Emitter Inductance	Measured 5mm from PKG	--	7.5	--	nH



Fig 1. Typical Output Chacracteristics



Fig 2. Typical Saturation Voltage Characteristics



Fig 3. Saturation Voltage vs. Case Temperature at Variant Current Level



Fig 4. Load Current vs. Frequency



Fig 5. Saturation Voltage vs. V_{GE}



Fig 6. Saturation Voltage vs. V_{GE}



Fig 7. Capacitance Characteristics



Fig 8. Turn-On Characteristics vs. Gate Resistance



Fig 9. Turn-Off Characteristics vs. Gate Resistance



Fig 10. Switching Loss vs. Gate Resistance



Fig 11. Turn-On Characteristics vs. Collector Current



Fig 12. Turn-Off Characteristics vs. Collector Current



Fig 13. Switching Loss vs. Collector Current



Fig 14. Gate Charge Characteristics



Fig 15. SOA Characteristics



Fig 16. Turn-Off SOA Characteristics



Fig 17. Transient Thermal Impedance of IGBT

Package Dimension

TO-220F (FS PKG CODE AQ)



Dimensions in Millimeters

TRADEMARKS

The following are registered and unregistered trademarks Fairchild Semiconductor owns or is authorized to use and is not intended to be an exhaustive list of all such trademarks.

ACEx™
Bottomless™
CoolFET™
CROSSVOLT™
DenseTrench™
DOME™
EcoSPARK™
E^2CMOS™
EnSigna™
FACT™
FACT Quiet Series™
FAST®
FASTr™
GlobalOptoisolator™
GTO™
HiSeC™
ISOPLANAR™
LittleFET™
MicroFET™
MICROWIRE™
OPTOLOGIC™
OPTOPLANAR™
PACMAN™
POP™
PowerTrench®
QFET™
QS™
QT Optoelectronics™
Quiet Series™
SLIENT SWITCHER®
SMART START™
Star* Power™
Stealth™
SuperSOT™-3
SuperSOT™-6
SuperSOT™-8
SyncFET™
TinyLogic™
UHC™
UltraFET®
VCX™

DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS.

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION.

As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, or (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

2. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

PRODUCT STATUS DEFINITIONS

Definition of Terms

Datasheet Identification	Product Status	Definition
Advance Information	Formative or In Design	This datasheet contains the design specifications for product development. Specifications may change in any manner without notice.
Preliminary	First Production	This datasheet contains preliminary data, and supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.
No Identification Needed	Full Production	This datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.
Obsolete	Not In Production	This datasheet contains specifications on a product that has been discontinued by Fairchild semiconductor. The datasheet is printed for reference information only.

SGS10N60RUF

Discrete, Short Circuit Rated IGBT

Contents

Datasheet

Download this datasheet

PDF

e-mail this datasheet

[E-

This pagePrint version

Related Links

Request samples

How to order products

Product Change Notices (PCNs)

Support

Distributor and field sales representatives

Quality and reliability

Design tools

General description

Fairchild's RUF series of Insulated Gate Bipolar Transistors (IGBTs) provide low conduction and switching losses as well as short circuit ruggedness. The RUF series is designed for applications such as motor control, uninterrupted power supplies (UPS) and general inverters where short circuit ruggedness is a required feature.

back to top

Features

- Short Circuit rated 10us @ T_C = 100°C, V_{GE} = 15V
- High Speed Switching
- Low Saturation Voltage : $V_{CE(sat)}$ = 2.2 V @ I_C = 10A
- High Input Impedance

back to top

Applications

AC &DC Motor controls,General Purpose Inverters, Robotics, Servo Controls

back to top

Product status/pricing/packaging

Product	Product status	Pricing*	Package type	Leads	Packing method
SGS10N60RUFTU	Full Production	$1.61	TO-220F	3	RAIL

* 1,000 piece Budgetary Pricing

back to top

Home | Find products | Technical information | Buy products | Support | Company | Contact us | Site index | Privacy policy