

September 1997 Revised June 2005

FST16209 18-Bit Bus Exchange Switch

General Description

The Fairchild Switch FST16209 provides 18-bits of highspeed CMOS TTL-compatible bus switching or exchanging. The low on resistance of the switch allows inputs to be connected to outputs without adding propagation delay or generating additional ground bounce noise.

The device operates as a 18-bit bus switch or a 9-bit bus exchanger, which allows data exchange between the four signal ports via the data-select terminals.

Features


- \blacksquare 4 Ω switch connection between two ports.
- Minimal propagation delay through the switch.
- Low I_{CC}.
- Zero bounce in flow-through mode.
- Control inputs compatible with TTL level.

Ordering Code:

Order Number	Package Number	Package Description				
FST16209MEA	MS48A	48-Lead Small Shrink Outline Package (SSOP), JEDEC MO-118, 0.300" Wide				
FST16209MTD	MTD48	48-Lead Thin Shrink Small Outline Package (TSSOP), JEDEC MO-153, 6.1mm Wide				

Devices also available in Tape and Reel. Specify by appending the suffix letter "X" to the ordering code.

Logic Diagram



Truth Table

S2	S1	S0	A ₁	A ₂	Function
L	L	L	Z	Z	Disconnect
L	L	Н	B ₁	Z	$A_1 = B_1$
L	Н	L	B ₂	Z	$A_1 = B_2$
L	Н	Н	Z	B_1	$A_2 = B_1$
Н	L	L	Z	B_2	$A_2 = B_2$
Н	L	Н	Z	Z	Disconnect
Н	Н	L	B ₁	B_2	$A_1 = B_1, A_2 = B_2$
Н	Н	Н	B ₂	B ₁	$A_1 = B_2, A_2 = B_1$

Connection Diagram



Pin Descriptions

Pin Name	Description				
S2, S1, S0	Data-select inputs				
A ₁ , A ₂	Bus A				
B ₁ , B ₂	Bus B				

Absolute Maximum Ratings(Note 1)

Supply Voltage (V _{CC})	-0.5V to +7.0V
DC Switch Voltage (V _S)	-0.5V to +7.0V
DC Input Voltage (V _{IN})(Note 2)	-0.5V to +7.0V
DC Input Diode Current (I_{IK}) V_{IN} <0V	-50mA
DC Output (I _{OUT}) Sink Current	128mA
DC V _{CC} /GND Current (I _{CC} /I _{GND})	+/- 100mA
Storage Temperature Range (T _{STG})	-65°C to +150 °C

Recommended Operating Conditions (Note 3)

 $\begin{array}{ll} \mbox{Power Supply Operating (V_{CC})} & 4.0 \mbox{V to } 5.5 \mbox{V} \\ \mbox{Input Voltage (V_{IN})} & 0 \mbox{V to } 5.5 \mbox{V} \\ \mbox{Output Voltage (V_{OUT})} & 0 \mbox{V to } 5.5 \mbox{V} \\ \end{array}$

Input Rise and Fall Time (t_r, t_f)

Switch Control Input 0nS/V to 5nS/V Switch I/O 0nS/V to DC Free Air Operating Temperature (T_A) -40 °C to +85 °C

Note 1: The "Absolute Maximum Ratings" are those values beyond which the safety of the device cannot be guaranteed. The device should not be operated at these limits. The parametric values defined in the Electrical Characteristics tables are not guaranteed at the absolute maximum rating. The "Recommended Operating Conditions" table will define the conditions for actual device operation.

Note 2: The input and output negative voltage ratings may be exceeded if the input and output diode current ratings are observed.

Note 3: Unused control inputs must be held HIGH or LOW. They may not float

DC Electrical Characteristics

	Parameter	v _{cc} (v)	T _A	= -40 °C to +8	5 °C	Units	Conditions
Symbol			Min	Typ (Note 4)	Max		
V _{IK}	Clamp Diode Voltage	4.5			-1.2	V	$I_{IN} = -18mA$
V _{IH}	HIGH Level Input Voltage	4.0-5.5	2.0			V	
V _{IL}	LOW Level Input Voltage	4.0-5.5			0.8	V	
I _I	Input Leakage Current	5.5			±1.0	μА	$0 \leq V_{IN} \leq 5.5V$
		0			10	μА	$V_{IN} = 5.5V$
I _{OFF}	OFF-STATE Leakage Current	5.5			±1.0	μΑ	$0 \le A, B \le V_{CC}$
R _{ON}	Switch On Resistance	4.5		4	7	Ω	$V_{IN} = 0V$, $I_{IN} = 64mA$
	(Note 5)	4.5		4	7	Ω	$V_{IN} = 0V$, $I_{IN} = 30mA$
		4.5		8	12	Ω	$V_{IN} = 2.4V, I_{IN} = 15mA$
		4.0		14	20	Ω	$V_{IN} = 2.4V, I_{IN} = 15mA$
I _{CC}	Quiescent Supply Current	5.5			3	μА	$V_{IN} = V_{CC}$ or GND, $I_{OUT} = 0$
ΔI _{CC}	Increase in I _{CC} per Input	5.5			2.5	mA	One Input at 3.4V
							Other Inputs at V _{CC} or GND

Note 4: Typical values are at V_{CC} = 5.0V and T_A = +25°C

Note 5: Measured by the voltage drop between A and B pins at the indicated current through the switch. On Resistance is determined by the lower of the voltages on the two (A or B) pins.

AC Electrical Characteristics

Symbol	Parameter	$T_A = -40$ °C to $+85$ °C, $C_L = 50$ pF, $R_U = R_D = 500$ Ω				Units	Conditions	Figure
		$V_{CC} = 4.5 - 5.5V$		V _{CC} = 4.0V		Units	Conditions	No.
		Min	Max	Min	Max			
t _{PHL} , t _{PLH}	Propagation Delay Bus to Bus (Note 6)		0.25		0.25	ns	V _I = OPEN	Figures 1, 2
t _{PHL} , t _{PLH}	Propagation Delay S to Bus	1.5	7.0		7.0	ns	V _I = OPEN	Figures 1, 2
t _{PZH} , t _{PZL}	Output Enable Time, S to A or B	1.5	7.5		8.0	ns	$V_I = 7V$ for t_{PZL} $V_I = OPEN$ for t_{PZH}	Figures 1, 2
t _{PHZ} , t _{PLZ}	Output Disable Time S to A or B	1.0	8.5		9.0	ns	$V_I = 7V$ for t_{PLZ} $V_I = OPEN$ for t_{PHZ}	Figures 1, 2


Note 6: This parameter is guaranteed by design but is not tested. The bus switch contributes no propagation delay other than the RC delay of the typical On Resistance of the switch and the 50pF load capacitance, when driven by an ideal voltage source (zero output impedance).

Capacitance (Note 7)

Symbol	Parameter	Тур	Max	Units	Conditions
C _{IN}	Control pin Input Capacitance	3		pF	V _{CC} = 5.0V
C _{I/O}	Input/Output Capacitance	10		pF	V _{CC} = 5.0V,
					S0. S1. and S2 = GND

Note 7: T_A = +25°C, f = 1 MHz. Capacitance is characterized but not tested

AC Loading and Waveforms



Note: Input driven by 50 Ω source terminated in 50 Ω Note: C_L includes load and stray capacitance Note: Input PRR = 1.0 MHz, t_W = 500 ns

FIGURE 1. AC Test Circuit





FIGURE 2. AC Waveforms



Physical Dimensions inches (millimeters) unless otherwise noted (Continued) 0.40 TYP -B-8.10 4.05 ALL LEAD TIPS PIN #1 IDENT. 0.50 LAND PATTERN RECOMMENDATION 0.1 C SEE DETAIL A 0.90+0.15 0.09-0.20 0.10±0.05 0.50 ⊕ 0.13@ A BS CS 12.00° TOP & BOTTOM DIMENSIONS ARE IN MILLIMETERS R0.16 GAGE PLANE R0.31 0.25 A. CONFORMS TO JEDEC REGISTRATION MO-153, VARIATION ED, DATE 4/97. B. DIMENSIONS ARE IN MILLIMETERS. SEATING PLANE 0.60±0.10-C. DIMENSIGNS ARE EXCLUSIVE OF BURRS, MOLD FLASH, AND THE BAR EXTRUSIONS. D. DIMENSIONS AND TOLERANCES PER ANSI Y14.5M, 1982. DETAIL A

48-Lead Thin Shrink Small Outline Package (TSSOP), JEDEC MO-153, 6.1mm Wide Package Number MTD48

Technology Description

MTD48REVC

The Fairchild Switch family derives from and embodies Fairchild's proven switch technology used for several years in its 74LVX3L384 (FST3384) bus switch product.

Fairchild does not assume any responsibility for use of any circuitry described, no circuit patent licenses are implied and Fairchild reserves the right at any time without notice to change said circuitry and specifications.

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

- Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
- A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

www.fairchildsemi.com