May 2001 Revised June 2005 FSTU16861 20-Bit Bus Switch with –2V Undershoot Protection

FSTU16861 20-Bit Bus Switch with -2V Undershoot Protection

General Description

FAIRCHILD

SEMICONDUCTO

The Fairchild Switch FSTU16861 provides 20-Bits of highspeed CMOS TTL-compatible bus switching. The low On Resistance of the switch allows inputs to be connected to outputs without adding propagation delay or generating additional ground bounce noise.

The device is organized as a 10-bit or 20-Bit bus switch. When \overline{OE}_1 is LOW, the switch is ON and Port 1A is connected to Port 1B. When \overline{OE}_2 is LOW, Port 2A is connected to Port 2B. When $\overline{\text{OE}}_{X}$ is HIGH, a high impedance state exists between the A and B Ports. The A and B Ports are protected against undershoot to support an extended range to 2.0V below ground. Fairchild's integrated Undershoot Hardened Circuit (UHC™) senses undershoot at the I/O and responds by preventing voltage differentials from developing and turning the switch on. When \overline{OE} is HIGH, the switch is OPEN and a high-impedance state exists between the two ports.

Features

- Undershoot hardened to -2V (A and B Ports)
- \blacksquare 4 Ω switch connection between two ports
- Minimal propagation delay through the switch
- Low I_{CC}
- Zero bounce in flow-through mode Control inputs compatible with TTL level
- See Application Note AN-5008 for details

Ordering Code:


| Order Number | Package Number | Package Description | | | | | |
|------------------------|--|---|--|--|--|--|--|
| FSTU16861MTD | MTD48 | 48-Lead Thin Shrink Small Outline Package (TSSOP), JEDEC MO-153, 6.1mm Wide | | | | | |
| Dovices also ovailable | Devices also available in Tape and Real. Specify by appending the suffix latter "V" to the ordering code | | | | | | |

ending the suffix letter "X" to the ordering

UHC[™] is a trademark of Fairchild Semiconductor Corporation.

FSTU16861

| $\begin{array}{c ccccccccccccccccccccccccccccccccccc$ | Connection Diagram | | | | | | |
|---|--|--|--|--|--|--|--|
| | $\begin{array}{cccccccccccccccccccccccccccccccccccc$ | $\begin{array}{c} \overline{OE}_1 \\ \overline{OE}_2 \\$ | | | | | |



Pin Descriptions

| Pin Name | Description |
|------------------------------------|--------------------|
| $\overline{OE}_1, \overline{OE}_2$ | Bus Switch Enables |
| 1A _n , 2A _n | Bus A |
| 1B _n , 2B _n | Bus B |

Truth Table

| Inp | uts | Inputs/Outputs | | | | |
|-----------------|-----------------|----------------|---------|--|--|--|
| OE ₁ | OE ₂ | 1A, 1B | 2A, 2B | | | |
| L | L | 1A = 1B | 2A = 2B | | | |
| L | Н | 1A = 1B | Z | | | |
| н | L | Z | 2A = 2B | | | |
| н | н | Z | Z | | | |

H = HIGH Voltage Level L = LOW Voltage Level Z = High Impedance

Absolute Maximum Ratings(Note 1)

| - · · · · · | |
|--|------------------|
| Supply Voltage (V _{CC}) | -0.5V to +7.0V |
| DC Switch Voltage (V_S) (Note 2) | -2.0V to +7.0V |
| DC Input Voltage (V _{IN}) (Note 3) | -0.5V to +7.0V |
| DC Input Diode Current (I _{IK}) $V_{IN} < 0V$ | –50 mA |
| DC Output Current (I _{OUT}) | 128 mA |
| DC V _{CC} /GND Current (I _{CC} /I _{GND}) | ±100 mA |
| Storage Temperature Range (T _{STG}) | -65°C to +150 °C |
| | |

Recommended Operating Conditions (Note 4)

| Conditions (Note 4) | |
|--|------------------|
| Power Supply Operating (V_{CC}) | 4.0V to 5.5V |
| Input Voltage (V _{IN}) | 0V to 5.5V |
| Output Voltage (V _{OUT}) | 0V to 5.5V |
| Input Rise and Fall Time (t_r, t_f) | |
| Switch Control Input | 0 ns/V to 5 ns/V |
| Switch I/O | 0 ns/V to DC |
| Free Air Operating Temperature (T _A) | -40 °C to +85 °C |

FSTU16861

Note 1: The "Absolute Maximum Ratings" are those values beyond which the safety of the device cannot be guaranteed. The device should not be operated at these limits. The parametric values defined in the Electrical Characteristics tables are not guaranteed at the absolute maximum rating. The "Recommended Operating Conditions" table will define the conditions for actual device operation.

Note 2: V_S is the voltage observed/applied at either the A or B Ports across the switch.

Note 3: The input and output negative voltage ratings may be exceeded if the input and output diode current ratings are observed.

Note 4: Unused control inputs must be held HIGH or LOW. They may not float.

DC Electrical Characteristics

| | Parameter | V _{cc} | Τ _Α | = −40 °C to +8 | 5 °C | Units | Conditions |
|------------------|---------------------------------------|-----------------|----------------|-----------------|------|-------|--|
| Symbol | | (V) | Min | Typ (Note 5) | Max | | |
| V _{IK} | Clamp Diode Voltage | 4.5 | | | -1.2 | V | I _{IN} = -18 mA |
| V _{IH} | HIGH Level Input Voltage | 4.0-5.5 | 2.0 | | | V | |
| VIL | LOW Level Input Voltage | 4.0-5.5 | | | 0.8 | V | |
| l _l | Input Leakage Current | 5.5 | | | ±1.0 | μA | $0 \le V_{IN} \le 5.5 V$ |
| | | 0 | | | 10 | μA | $V_{IN} = 5.5V$ |
| I _{OZ} | OFF-STATE Leakage Current | 5.5 | | | ±1.0 | μA | $0 \le A, B \le V_{CC}$ |
| R _{ON} | Switch On Resistance | 4.5 | | 4 | 7 | Ω | $V_{IN} = 0V$, $I_{IN} = 64 \text{ mA}$ |
| | (Note 6) | 4.5 | | 4 | 7 | Ω | $V_{IN} = 0V, I_{IN} = 30 \text{ mA}$ |
| | | 4.5 | | 8 | 14 | Ω | $V_{IN} = 2.4V, I_{IN} = 15 \text{ mA}$ |
| | | 4.0 | | 11 | 20 | Ω | $V_{IN} = 2.4V, I_{IN} = 15 \text{ mA}$ |
| I _{CC} | Quiescent Supply Current | 5.5 | | | 3 | μA | $V_{IN} = V_{CC}$ or GND, $I_{OUT} = 0$ |
| ΔI_{CC} | Increase in I _{CC} per Input | 5.5 | | | 2.5 | mA | One Input at 3.4V |
| | | | | | | | Other Inputs at V_{CC} or GND |
| V _{IKU} | Voltage Undershoot | 5.5 | | | -2.0 | V | $0.0\ mA \geq I_{IN} \geq -50\ mA$ |
| | | | | | | | <u>OE</u> = 5.5V |

Note 5: Typical values are at V_{CC} = 5.0V and T_A = +25 $^{\circ}C$

Note 6: Measured by the voltage drop between A and B pins at the indicated current through the switch. On Resistance is determined by the lower of the voltages on the two (A or B) pins.

FSTU16861

AC Electrical Characteristics

| Symbol | Parameter | $T_A = -40$ °C to +85 °C, $C_L = 50$ pF, RU = RD = 500 Ω | | | | Units | Conditions | Figure |
|-------------------------------------|--|--|--|-----|-------------|--------|--|-----------------|
| Cymbol | i arameter | $V_{CC} = 4.$ | CC = 4.5 - 5.5V V _{CC} = 4.0V | | Contaitions | Number | | |
| | | Min | Max | Min | Max | | | |
| t _{PHL} , t _{PLH} | Propagation Delay Bus-to-Bus (Note 7) | | 0.25 | | 0.25 | ns | V _I = OPEN | Figures 2, 3 |
| t _{PZH} , t _{PZL} | Output Enable Time | 1.0 | 5.9 | | 6.4 | ns | $V_I = 7V$ for t_{PZL} $V_I = OPEN$ for t_{PZH} | Figures 2, 3 |
| t _{PHZ} , t _{PLZ} | Output Disable Time | 1.0 | 6.9 | | 7.4 | ns | $V_I = 7V$ for t_{PLZ} $V_I = OPEN$ for t_{PHZ} | Figures 2, 3 |

Note 7: This parameter is guaranteed by design but is not tested. The bus switch contributes no propagation delay other than the RC delay of the typical On Resistance of the switch and the 50pF load capacitance, when driven by an ideal voltage source (zero output impedance).

Capacitance (Note 8)


| Symbol | Parameter | Тур | Max | Units | Conditions |
|------------------|--------------------------------------|-----|-----|-------|---|
| C _{IN} | Control Pin Input Capacitance | 3 | | pF | $V_{CC} = 5.0V, V_{IN} = 0V$ |
| C _{I/O} | Input/Output Capacitance "OFF State" | 6 | | pF | V_{CC} , $\overline{OE} = 5.0V$, $V_{IN} = 0V$ |

Note 8: $T_A = +25^{\circ}C$, f = 1 MHz, Capacitance is characterized but not tested.

Undershoot Characteristic (Note 9)

| Symbol | Parameter | Min | Тур | Max | Units | Conditions |
|---|----------------------------------|-----|-----------------------|-----|-------|------------|
| V _{OUTU} | Output Voltage During Undershoot | 2.5 | V _{OH} - 0.3 | | V | Figure 1 |
| Note 9: This test is intended to characterize the device's protective canabilities by maintaining output signal integrity during an input transient voltage | | | | | | |

Note 9: This test is intended to characterize the device's protective capabilities by maintaining output signal integrity during an input transient voltage undershoot event.







Device Test Conditions


| Parameter | Value | Units |
|------------------|--------------|-------|
| V _{IN} | see Waveform | V |
| $R_1 = R_2$ | 100K | Ω |
| V _{TRI} | 11.0 | V |
| V _{CC} | 5.5 | V |

Transient Input Voltage (V_{IN}) Waveform









48-Lead Thin Shrink Small Outline Package (TSSOP), JEDEC MO-153, 6.1mm Wide Package Number MTD48

Technology Description

The Fairchild Switch family derives from and embodies Fairchild's proven switch technology used for several years in its 74LVX3L384(FST3384) bus switch product.

Fairchild does not assume any responsibility for use of any circuitry described, no circuit patent licenses are implied and Fairchild reserves the right at any time without notice to change said circuitry and specifications.

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

- 1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
- 2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

www.fairchildsemi.com