


NDP5060 / NDB5060 N-Channel Enhancement Mode Field Effect Transistor


General Description


These N-Channel enhancement mode power field effect transistors are produced using Fairchild's proprietary, high cell density, DMOS technology. This very high density process has been especially tailored to minimize on-state resistance, provide superior switching performance, and withstand high energy pulses in the avalanche and commutation modes. These devices are particularly suited for low voltage applications such as automotive, DC/DC converters, PWM motor controls, and other battery powered circuits where fast switching, low in-line power loss, and resistance to transients are needed.

Features

- \blacksquare 26 A, 60 V. $\rm R_{DS(ON)}$ = 0.05 Ω @ $\rm V_{GS}$ = 10 V.
- Critical DC electrical parameters specified at elevated temperature.
- Rugged internal source-drain diode can eliminate the need for an external Zener diode transient suppressor.
- 175°C maximum junction temperature rating.
- High density cell design for extremely low R_{DS(ON)}.
- TO-220 and TO-263 (D²PAK) package for both through hole and surface mount applications.







Absolute Maximum Ratings

T_C = 25°C unless otherwise note

Symbol	Parameter	NDP5060	NDB5060	Units	
V _{DSS}	Drain-Source Voltage	60			
V_{DGR}	Drain-Gate Voltage ($R_{GS} \le 1 \text{ M}\Omega$)	60			
V _{GSS}	Gate-Source Voltage - Continuous	±2	V		
	- Nonrepetitive (t _p < 50 µs)	±40			
I _D	Drain Current - Continuous	26	Α		
	- Pulsed	78			
P _D	Total Power Dissipation @ T _C = 25°C	68	68		
	Derate above 25°C	0.4	5	W/°C	
T_J , T_{STG}	Operating and Storage Temperature Range	-65 to	175	°C	

Symbol	Parameter	Conditions			Тур	Max	Units
DRAIN-S	OURCE AVALANCHE RATINGS (Note 1)	·					-
W _{DSS}	Single Pulse Drain-Source Avalanche Energy	$V_{DD} = 30 \text{ V}, I_{D} = 26 \text{ A}$				100	mJ
AR	Maximum Drain-Source Avalanche Curre	ent				26	Α
OFF CH	ARACTERISTICS						
3V _{DSS}	Drain-Source Breakdown Voltage	$V_{GS} = 0 \text{ V}, I_{D} = 250 \mu\text{A}$		60			V
DSS	Zero Gate Voltage Drain Current	$V_{DS} = 60 \text{ V}, V_{GS} = 0 \text{ V}$				250	μΑ
			T _J = 125°C			1	mA
GSSF	Gate - Body Leakage, Forward	$V_{GS} = 20 \text{ V}, V_{DS} = 0 \text{ V}$				100	nA
GSSR	Gate - Body Leakage, Reverse	V _{GS} = -20 V, V _{DS} = 0 V				-100	nA
ON CHAI	RACTERISTICS (Note 1)						
V _{GS(th)}	Gate Threshold Voltage	$V_{DS} = V_{GS}, I_{D} = 250 \mu\text{A}$		2	2.9	4	V
			T _J = 125°C	1.4	2.2	2.8	
R _{DS(ON)}	Static Drain-Source On-Resistance	$V_{GS} = 10 \text{ V}, I_{D} = 13 \text{ A}$			0.04	0.05	Ω
				0.07	0.08		
D(on)	On-State Drain Current	$V_{GS} = 10 \text{ V}, V_{DS} = 10 \text{ V}$		26			Α
FS	Forward Transconductance	$V_{DS} = 10 \text{ V}, I_{D} = 13 \text{ A}$			9		S
YNAMI	CHARACTERISTICS						
Siss	Input Capacitance	$V_{DS} = 30 \text{ V}, V_{GS} = 0 \text{ V},$ f = 1.0 MHz			630		pF
Coss	Output Capacitance				225		pF
C _{rss}	Reverse Transfer Capacitance				70		pF
WITCH	NG CHARACTERISTICS (Note 1)	•				·	
D(on)	Turn - On Delay Time	$V_{DD} = 30 \text{ V}, I_{D} = 26 \text{ A},$			9	20	nS
r	Turn - On Rise Time	$V_{GS} = 10 \text{ V}, R_{GEN} = 15 \Omega$		95	200	nS	
D(off)	Turn - Off Delay Time			19	40	nS	
f	Turn - Off Fall Time				48	100	nS
Q_g	Total Gate Charge	$V_{DS} = 24 \text{ V},$ $I_{D} = 26 \text{ A}, V_{GS} = 10 \text{ V}$			20	40	nC
Q_{gs}	Gate-Source Charge	$I_D = 26 \text{ A}, \ V_{GS} = 10 \text{ V}$			5		nC
Q_{gd}	Gate-Drain Charge				11		nC

Symbol	Parameter	Min	Тур	Max	Units	
DRAIN-S	OURCE DIODE CHARACTERISTICS	,	<u> </u>		1	4
Is	Maximum Continuos Drain-Source Diode			26	Α	
I _{SM}	Maximum Pulsed Drain-Source Diode Fo			78	Α	
V_{SD}	Drain-Source Diode Forward Voltage	V _{GS} = 0 V, I _S = 13 A (Note 1)		0.9	1.3	V
t _{rr}	Reverse Recovery Time	$V_{GS} = 0 \text{ V}, I_F = 26 \text{ A},$ $dI_F/dt = 100 \text{ A/}\mu\text{s}$		54	120	ns
I _{rr}	Reverse Recovery Current	$dI_{r}/dt = 100 AV\mu s$		2.1	8	А
THERMA	AL CHARACTERISTICS		·			
R _{θJC}	Thermal Resistance, Junction-to-Case			2.2	°C/W	
R _{BJA}	Thermal Resistance, Junction-to-Ambier			62.5	°C/W	

Note: 1. Pulse Test: Pulse Width \leq 300 μ s, Duty Cycle \leq 2.0%.

Typical Electrical Characteristics





Figure 1. On-Region Characteristics.

Figure 2. On-Resistance Variation with Gate Voltage and Drain Current.







Figure 3. On-Resistance Variation with Temperature.

Figure 4. On-Resistance Variation with Drain Current and Temperature.






Figure 5. Transfer Characteristics.

Figure 6. Gate Threshold Variation with Temperature.

Typical Electrical Characteristics (continued)




Figure 7. Breakdown Voltage Variation with Temperature.




Figure 8. Body Diode Forward Voltage Variation with Current and Temperature.




Figure 9. Capacitance Characteristics.




Figure 10. Gate Charge Characteristics.




Figure 11. Switching Test Circuit.





Figure 12. Switching Waveforms.

Typical Electrical Characteristics (continued)






Figure 13. Transconductance Variation with Drain Current and Temperature.

Figure 14. Maximum Safe Operating Area.







Figure 15. Transient Thermal Response Curve.



TO-220 Tape and Reel Data and Package Dimensions, continued


TO-220 (FS PKG Code 37)






Scale 1:1 on letter size paper
Dimensions shown below are in:
inches [millimeters]


Part Weight per unit (gram): 1.4378





TO-263AB/D²PAK Tape and Reel Data and Package Dimensions, continued

TO-263AB/D²PAK Embossed Carrier Tape



User Direction of Feed


Dimensions are in millimeter														
Pkg type	Α0	В0	w	D0	D1	E1	E2	F	P1	P0	K0	Т	Wc	Тс
TO263AB/ D ² PAK (24mm)	10.60 +/-0.10	15.80 +/-0.10	24.0 +/-0.3	1.55 +/-0.05	1.60 +/-0.10	1.75 +/-0.10	22.25 min	11.50 +/-0.10	16.0 +/-0.1	4.0 +/-0.1	4.90 +/-0.10	0.450 +/-0.150	21.0 +/-0.3	0.06 +/-0.02

Notes: A0, B0, and K0 dimensions are determined with respect to the EIA/Jedec RS-481 rotational and lateral movement requirements (see sketches A, B, and C).



Sketch A (Side or Front Sectional View)

Component Rotation




Sketch B (Top View)
Component Rotation




Sketch C (Top View)
Component lateral movement

TO-263AB/D²PAK Reel Configuration: Figure 4.0



13" Diameter Option





W2 max Measured at Hub

Dimensions are in inches and millimeters									
Tape Size	Reel Option	Dim A	Dim B	Dim C	Dim D	Dim N	Dim W1	Dim W2	Dim W3 (LSL-USL)
24mm	13" Dia	13.00 330	0.059 1.5	512 +0.020/-0.008 13 +0.5/-0.2	0.795 20.2	4.00 100	0.961 +0.078/-0.000 24.4 +2/0	1.197 30.4	0.941 - 0.1.079 23.9 - 27.4

TO-263AB/D²PAK Tape and Reel Data and Package Dimensions, continued


TO-263AB/D²PAK (FS PKG Code 45)








Scale 1:1 on letter size paper Dimensions shown below are in: inches [millimeters]

Part Weight per unit (gram): 1.4378









- NOTES: UNLESS OTHERWISE SPECIFIED

 A) ALL DIMENSIONS ARE IN MILLIMETERS.
 B) STANDARD LEAD FINISH:
 200 MICROINCHES / 5.08 MICROMETERS MIN.
 LEAD/TIN 15/85 ON OLIN 194 COPPER OR
 EQUIVALENT.
 C) MAXIMUM YERTICAL BURR ON HEATSINK NOT
 TO EXCEED 0.003 INCH / 0.05mm.
 D) NO PACKAGE CHIPS, CRACKS OR SURFACE
 IDENTIFICATION ALLOWED AFTER FORMING.
 E) REFERENCE JEDEC, TO—265, ISSUE C,
 VARIATION AB, DATED 2/92.

TRADEMARKS

The following are registered and unregistered trademarks Fairchild Semiconductor owns or is authorized to use and is not intended to be an exhaustive list of all such trademarks.

FACT $^{\text{TM}}$ QFET $^{\text{TM}}$ FACT Quiet Series $^{\text{TM}}$ QS $^{\text{TM}}$

 $\begin{array}{lll} \mathsf{FAST}^{\circledast} & \mathsf{Quiet}\,\mathsf{Series^{\mathsf{TM}}} \\ \mathsf{FASTr^{\mathsf{TM}}} & \mathsf{SuperSOT^{\mathsf{TM}}\text{-}3} \\ \mathsf{GTO^{\mathsf{TM}}} & \mathsf{SuperSOT^{\mathsf{TM}}\text{-}6} \\ \mathsf{HiSeC^{\mathsf{TM}}} & \mathsf{SuperSOT^{\mathsf{TM}}\text{-}8} \\ \end{array}$

DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS.

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, or (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

2. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

PRODUCT STATUS DEFINITIONS

Definition of Terms

Datasheet Identification	Product Status	Definition
Advance Information	Formative or In Design	This datasheet contains the design specifications for product development. Specifications may change in any manner without notice.
Preliminary	First Production	This datasheet contains preliminary data, and supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.
No Identification Needed	Full Production	This datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.
Obsolete	Not In Production	This datasheet contains specifications on a product that has been discontinued by Fairchild semiconductor. The datasheet is printed for reference information only.