Power MOSFET

60 V, 5.7 m Ω , 98 A, Single N-Channel

Features

- Low R_{DS(on)} to Minimize Conduction Losses
- High Current Capability
- Avalanche Energy Specified
- AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb–Free, Halogen Free/BFR Free and are RoHS Compliant

MAXIMUM RATINGS (T_J = 25°C unless otherwise noted)

Parameter			Symbol	Value	Unit
Drain-to-Source Voltage			V_{DSS}	60	V
Gate-to-Source Voltage	Gate-to-Source Voltage			±20	V
Continuous Drain Cur-		T _C = 25°C	I _D	98	Α
rent R _{θJC} (Note 1)	Steady	T _C = 100°C		69	
Power Dissipation R _{θJC}	State	T _C = 25°C	P _D	115	W
(Note 1)		T _C = 100°C		58	
Continuous Drain Cur-		T _A = 25°C	I _D	18	Α
rent R _{θJA} (Notes 1 & 2)	Steady State	T _A = 100°C		13	
Power Dissipation R _{θJA}		T _A = 25°C	P_{D}	4.1	W
(Notes 1 & 2)		T _A = 100°C		2.0	
Pulsed Drain Current	T _A = 25°	C, t _p = 10 μs	I _{DM}	367	Α
Current Limited by Package (Note 3)	T _A	= 25°C	I _{Dmaxpkg}	60	Α
Operating Junction and Storage Temperature			T _J , T _{stg}	-55 to 175	°C
Source Current (Body Diode)			IS	96	Α
Single Pulse Drain-to-Source Avalanche Energy (T _J = 25°C, V _{DD} = 50 V, V _{GS} = 10 V, $I_{L(pk)}$ = 37 A, L = 0.3 mH, R_G = 25 Ω)			E _{AS}	205	mJ
Lead Temperature for Soldering Purposes (1/8" from case for 10 s)			TL	260	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL RESISTANCE MAXIMUM RATINGS

Parameter	Symbol	Value	Unit
Junction-to-Case - Steady State (Drain)	$R_{\theta JC}$	1.3	°C/W
Junction-to-Ambient - Steady State (Note 2)	$R_{\theta JA}$	37	


- The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.
- 2. Surface-mounted on FR4 board using a 650 mm², 2 oz. Cu pad.
- 3. Continuous DC current rating. Maximum current for pulses as long as 1 second are higher but are dependent on pulse duration and duty cycle.



ON Semiconductor®

www.onsemi.com


V _{(BR)DSS}	R _{DS(on)}	I _D	
60 V	5.7 m Ω @ 10 V	98 A	





DPAK CASE 369C (Surface Mount) STYLE 2

MARKING DIAGRAMS & PIN ASSIGNMENT



A = Assembly Location*

Y = Year WW = Work Week V5862N = Device Code G = Pb-Free Package

* The Assembly Location Code (A) is front side optional. In cases where the Assembly Location is stamped in the package bottom (molding ejecter pin), the front side assembly code may be blank.

ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 2 of this data sheet.

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise noted)

Parameter	Symbol	Test Condition		Min	Тур	Max	Unit
OFF CHARACTERISTICS					•		•
Drain-to-Source Breakdown Voltage	V _{(BR)DSS}	$V_{GS} = 0 \text{ V}, I_D = 250 \mu\text{A}$		60			V
Drain-to-Source Breakdown Voltage Temperature Coefficient	V _{(BR)DSS} /T _J				47		mV/°C
Zero Gate Voltage Drain Current	I _{DSS}	$V_{GS} = 0 \text{ V},$ $T_{J} = 25^{\circ}\text{C}$			1	1.0	μΑ
		$V_{DS} = 60 \text{ V}$	T _J = 125°C		1	100	1
Gate-to-Source Leakage Current	I _{GSS}	V _{DS} = 0 V, V _{GS}	; = ±20 V			±100	nA
ON CHARACTERISTICS (Note 4)					•		•
Gate Threshold Voltage	V _{GS(TH)}	$V_{GS} = V_{DS}, I_D$	= 250 μΑ	2.0		4.0	V
Threshold Temperature Coefficient	V _{GS(TH)} /T _J				-9.7		mV/°C
Drain-to-Source On Resistance	R _{DS(on)}	V _{GS} = 10 V, I _E	₎ = 48 A		4.4	5.7	mΩ
Forward Transconductance	gFS	V _{DS} = 15 V, I _D	₎ = 10 A		18		S
CHARGES, CAPACITANCES AND GA	TE RESISTANC	ES					
Input Capacitance	C _{iss}	$V_{GS} = 0 \text{ V, f} = 1.0 \text{ MHz,}$ $V_{DS} = 25 \text{ V}$			5050	6000	pF
Output Capacitance	C _{oss}				500	600	1
Reverse Transfer Capacitance	C _{rss}				300	420	1
Total Gate Charge	Q _{G(TOT)}				82		nC
Threshold Gate Charge	Q _{G(TH)}	$V_{GS} = 10 \text{ V}, V_{DS} = 48 \text{ V},$ $I_{D} = 48 \text{ A}$			5.2		1
Gate-to-Source Charge	Q_{GS}				24		1
Gate-to-Drain Charge	Q_{GD}				27		1
Gate Resistance	R_{G}				0.6		Ω
SWITCHING CHARACTERISTICS (Not	e 5)						
Turn-On Delay Time	t _{d(on)}				18		ns
Rise Time	t _r	V_{GS} = 10 V, V_{DD} = 48 V, I_{D} = 48 A, R_{G} = 2.5 Ω			70		1
Turn-Off Delay Time	t _{d(off)}				35		1
Fall Time	t _f				60		1
DRAIN-SOURCE DIODE CHARACTER	RISTICS				•		•
Forward Diode Voltage	V_{SD}	V _{GS} = 0 V,	T _J = 25°C		0.9	1.2	V
		I _S = 48 A	T _J = 100°C		0.75		1
Reverse Recovery Time	t _{RR}	V _{GS} = 0 V, dls/dt = 100 A/μs, I _S = 48 A			38		ns
Charge Time	ta				20		1
Discharge Time	tb				18		1
Reverse Recovery Charge	Q _{RR}				40		nC
						1	

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions. 4. Pulse Test: Pulse Width \leq 300 μ s, Duty Cycle \leq 2%.

ORDERING INFORMATION

Order Number	Package	Shipping [†]
NVD5862NT4G	DPAK (Pb-Free)	2500 / Tape & Reel
NVD5862NT4G-VF01	DPAK (Pb-Free)	2500 / Tape & Reel

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

^{5.} Switching characteristics are independent of operating junction temperatures.

TYPICAL CHARACTERISTICS




Figure 6. Drain-to-Source Leakage Current

vs. Voltage

Figure 5. On-Resistance Variation with

Temperature

TYPICAL CHARACTERISTICS




Figure 7. Capacitance Variation

Figure 8. Gate-to-Source vs. Total Charge




Figure 9. Resistive Switching Time Variation vs. Gate Resistance

Figure 10. Diode Forward Voltage vs. Current




Figure 11. Maximum Rated Forward Biased Safe Operating Area

Figure 12. Maximum Avalanche Energy versus
Starting Junction Temperature

175

TYPICAL CHARACTERISTICS





Figure 13. Thermal Response

PACKAGE DIMENSIONS

DPAK (SINGLE GAUGE)

CASE 369C **ISSUE F**




- 1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994. CONTROLLING DIMENSION: INCHES.
- THERMAL PAD CONTOUR OPTIONAL WITHIN DI-MENSIONS b3, L3 and Z. DIMENSIONS D AND E DO NOT INCLUDE MOLD
- FLASH, PROTRUSIONS, OR BURRS. MOLD FLASH, PROTRUSIONS, OR GATE BURRS SHALL NOT EXCEED 0.006 INCHES PER SIDE.
 5. DIMENSIONS D AND E ARE DETERMINED AT THE
- OUTERMOST EXTREMES OF THE PLASTIC BODY.
- 6. DATUMS A AND B ARE DETERMINED AT DATUM
- 7. OPTIONAL MOLD FEATURE

	INCHES		MILLIM	MILLIMETERS		
DIM	MIN	MAX	MIN	MAX		
Α	0.086	0.094	2.18	2.38		
A1	0.000	0.005	0.00	0.13		
b	0.025	0.035	0.63	0.89		
b2	0.028	0.045	0.72	1.14		
b3	0.180	0.215	4.57	5.46		
С	0.018	0.024	0.46	0.61		
c2	0.018	0.024	0.46	0.61		
D	0.235	0.245	5.97	6.22		
E	0.250	0.265	6.35	6.73		
е	0.090	BSC	2.29	2.29 BSC		
Н	0.370	0.410	9.40	10.41		
L	0.055	0.070	1.40	1.78		
L1	0.114 REF		2.90	REF		
L2	0.020 BSC		0.51	BSC		
L3	0.035	0.050	0.89	1.27		
L4		0.040		1.01		
Z	0.155		3.93			

STYLE 2:

- PIN 1. GATE
 - 2. DRAIN 3. SOURCE
 - DRAIN

SOLDERING FOOTPRINT*



mm SCALE 3:1

*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and in are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages.

Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free

Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910 Japan Customer Focus Center

Phone: 81-3-5817-1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative