Preferred Device

Small Signal MOSFET 50 mAmps, 30 Volts

N-Channel SC-70/SOT-323

These miniature surface mount MOSFETs low RDS(on) assure minimal power loss and conserve energy, making these devices ideal for use in small power management circuitry. Typical applications are dc-dc converters, power management in portable and battery-powered products such as computers, printers, PCMCIA cards, cellular and cordless telephones.

- Low RDS(on) Provides Higher Efficiency and Extends Battery Life
- Miniature SC-70/SOT-323 Surface Mount Package Saves Board Space

MAXIMUM RATINGS (T.J = 25°C unless otherwise noted)

Rating	Symbol	Value	Unit
Drain-to-Source Voltage	V _{DS}	20	Vdc
Gate-to-Source Voltage - Pulse	VGS	± 20	Vdc
Drain Current – Continuous @ T _A = 25°C	ID	50	mAdc
Total Power Dissipation @ T _A = 25°C (Note 1.) Derate above 25°C	PD	100	mW
Operating and Storage Temperature Range	T _J , T _{stg}	- 55 to 150	°C
Maximum Lead Temperature for Soldering Purposes, for 10 seconds	TL	260	°C

Mounted on G10/FR4 glass epoxy board using minimum recommended footprint.





ON Semiconductor™

http://onsemi.com


50 mAMPS 30 VOLTS RDS(on) = 50 Ω

N-Channel





PIN ASSIGNMENT



ORDERING INFORMATION

Device	Package	Shipping
MMBF1374T1	SC-70/ SOT-323	3000 Tape & Reel

Preferred devices are recommended choices for future use and best overall value.


ELECTRICAL CHARACTERISTICS ($T_A = 25^{\circ}C$ unless otherwise noted)


CI	Symbol	Min	Тур	Max	Unit	
OFF CHARACTERISTICS				•	•	•
Drain-to-Source Breakdown Voltage (V _{GS} = 0 Vdc, I _D = 10 μA)		V(BR)DSS	30	_	_	Vdc
Zero Gate Voltage Drain Current (VDS = 16 Vdc, VGS = 0 Vdc)	IDSS	_	-	1.0	μAdc	
Gate-Body Leakage Current (VG	IGSS	-	_	1.0	μAdc	
ON CHARACTERISTICS (Note 2.)						
Gate Threshold Voltage (V _{DS} = V _{GS} , I _D = 250 μAdc)	VGS(th)	-	2	2.8	Vdc	
Static Drain-to-Source On-Resistance (V _{GS} = 4.5 Vdc, I _D = 10 mAdc)		rDS(on)	-	27	50	Ω
Forward Transconductance (VDS	9FS	-	450	_	mMhos	
DYNAMIC CHARACTERISTICS						
Input Capacitance	(V _{DS} = 5.0 V)	C _{iss}	_	45	-	pF
Output Capacitance	(V _{DS} = 5.0 V)	Coss	-	25	-	1
Transfer Capacitance	(V _{DG} = 5.0 V)	C _{rss}	_	5.0	_	
SWITCHING CHARACTERISTICS	(Note 3.)					•
Turn-On Delay Time		^t d(on)	_	2.5	_	ns
Rise Time	$(V_{DD} = 15 \text{ Vdc}, I_{D} = 50 \text{ mAdc},$	t _r	-	2.5	-	1
Turn-Off Delay Time	$R_L = 50 \Omega$	t _d (off)	-	15	-	
Fall Time		t _f	-	0.8	_	1

Pulse Test: Pulse Width ≤ 300 μs, Duty Cycle ≤ 2%.
 Switching characteristics are independent of operating junction temperature.

PACKAGE DIMENSIONS

SC-70/SOT-323 CASE 419-04 ISSUE L





- NOTES:

 1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
 2. CONTROLLING DIMENSION: INCH.

	INCHES		MILLIMETERS		
DIM	MIN	MAX	MIN	MAX	
Α	0.071	0.087	1.80	2.20	
В	0.045	0.053	1.15	1.35	
С	0.032	0.040	0.80	1.00	
D	0.012	0.016	0.30	0.40	
G	0.047	0.055	1.20	1.40	
Н	0.000	0.004	0.00	0.10	
J	0.004	0.010	0.10	0.25	
K	0.017 REF		0.425 REF		
L	0.026 BSC 0.650		BSC		
N	0.028 REF		0.700 REF		
S	0.079	0.095	2 00	2 40	

STYLE 8: PIN 1. Gate 2. Source 3. Drain

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer.

PUBLICATION ORDERING INFORMATION

NORTH AMERICA Literature Fulfillment:

Literature Distribution Center for ON Semiconductor P.O. Box 5163, Denver, Colorado 80217 USA

Phone: 303–675–2175 or 800–344–3860 Toll Free USA/Canada **Fax**: 303–675–2176 or 800–344–3867 Toll Free USA/Canada

Email: ONlit@hibbertco.com

Fax Response Line: 303-675-2167 or 800-344-3810 Toll Free USA/Canada

N. American Technical Support: 800-282-9855 Toll Free USA/Canada

EUROPE: LDC for ON Semiconductor - European Support

German Phone: (+1) 303–308–7140 (Mon–Fri 2:30pm to 7:00pm CET)

Email: ONlit-german@hibbertco.com

French Phone: (+1) 303–308–7141 (Mon–Fri 2:00pm to 7:00pm CET)

Email: ONlit-french@hibbertco.com

English Phone: (+1) 303–308–7142 (Mon–Fri 12:00pm to 5:00pm GMT)

Email: ONlit@hibbertco.com

EUROPEAN TOLL-FREE ACCESS*: 00-800-4422-3781

*Available from Germany, France, Italy, UK, Ireland

CENTRAL/SOUTH AMERICA:

Spanish Phone: 303-308-7143 (Mon-Fri 8:00am to 5:00pm MST)

Email: ONlit-spanish@hibbertco.com

Toll-Free from Mexico: Dial 01-800-288-2872 for Access -

then Dial 866-297-9322

ASIA/PACIFIC: LDC for ON Semiconductor – Asia Support

Phone: 303-675-2121 (Tue-Fri 9:00am to 1:00pm, Hong Kong Time)

Toll Free from Hong Kong & Singapore:

001-800-4422-3781 Email: ONlit-asia@hibbertco.com

JAPAN: ON Semiconductor, Japan Customer Focus Center

4-32-1 Nishi-Gotanda, Shinagawa-ku, Tokyo, Japan 141-0031

Phone: 81–3–5740–2700

Email: r14525@onsemi.com

ON Semiconductor Website: http://onsemi.com

For additional information, please contact your local

Sales Representative.