

FDZ2552P

Monolithic Common Drain P-Channel 2.5V Specified PowerTrench® BGA MOSFET

General Description


Combining Fairchild's advanced 2.5V specified PowerTrench process with state-of-the-art BGA packaging, the FDZ2552P minimizes both PCB space and $R_{\rm DS(ON)}.$ This monolithic common drain BGA MOSFET embodies a breakthrough in packaging technology which enables the device to combine excellent thermal transfer characteristics, high current handling capability, ultra-low profile packaging, low gate charge, and low $R_{\rm DS(ON)}.$


Applications

- · Battery management
- Load switch
- · Battery protection

Features

- -5.5 A, -20 V. $R_{DS(ON)}$ = 45 m Ω @ V_{GS} = -4.5 V $R_{DS(ON)}$ = 75 m Ω @ V_{GS} = -2.5 V
- Occupies only 0.10 cm² of PCB area: 1/3 the area of SO-8
- Ultra-thin package: less than 0.80 mm height when mounted to PCB
- Outstanding thermal transfer characteristics: significantly better than SO-8
- Ultra-low Q_g x R_{DS(ON)} figure-of-merit
- · High power and current handling capability





Absolute Maximum Ratings T_{A=25°C} unless otherwise noted

Symbol	Parameter		Ratings	Units
V_{DSS}	Drain-Source Voltage		-20	V
V_{GSS}	Gate-Source Voltage		±12	V
I _D	Drain Current - Continuous	(Note 1a)	- 5.5	Α
	Pulsed		-20	
P _D	Power Dissipation (Steady State)	(Note 1a)	2.1	W
T_J , T_{STG}	Operating and Storage Junction Temperature Range		-55 to +150	°C

Thermal Characteristics

$R_{\theta JA}$	Thermal Resistance, Junction-to-Ambient	(Note 1a)	60	°C/W
$R_{\theta JB}$	Thermal Resistance, Junction-to-Ball	(Note 1)	6.3	
R _{θJC}	Thermal Resistance, Junction-to-Case	(Note 1)	0.6	

Package Marking and Ordering Information

Device Marking	Device	Reel Size	Tape width	Quantity
2552P	FDZ2552P	7"	12mm	3000 units

Symbol	Parameter	Test Conditions	Min	Тур	Max	Units
Off Char	acteristics	1	I.			
BV _{DSS}	Drain-Source Breakdown Voltage	$V_{GS} = 0 \text{ V}, \qquad I_{D} = -250 \mu\text{A}$	-20			V
<u>ΔBV_{DSS}</u> ΔT _J	Breakdown Voltage Temperature Coefficient	$I_D = -250 \mu A$, Referenced to 25°C		-17		mV/°C
I_{DSS}	Zero Gate Voltage Drain Current	$V_{DS} = -16 \text{ V}, V_{GS} = 0 \text{ V}$			-1	μA
I _{GSSF}	Gate-Body Leakage, Forward	$V_{GS} = -12 \text{ V}, V_{DS} = 0 \text{ V}$ $V_{GS} = 12 \text{ V}, V_{DS} = 0 \text{ V}$			-100	nA
GSSR	Gate-Body Leakage, Reverse	$V_{GS} = 12 \text{ V}, \qquad V_{DS} = 0 \text{ V}$			100	nA
On Char	acteristics (Note 2)					
$V_{GS(th)}$	Gate Threshold Voltage	$V_{DS} = V_{GS}$, $I_D = -250 \mu\text{A}$	-0.6	-0.9	-1.5	٧
$\frac{\Delta V_{GS(th)}}{\Delta T_J}$	Gate Threshold Voltage Temperature Coefficient	$I_D = -250 \mu A$, Referenced to 25°C		3		mV/°C
$R_{DS(on)}$	Static Drain–Source On–Resistance	$ \begin{aligned} &V_{GS} = -4.5 \ V, & I_D = -5.5 \ A \\ &V_{GS} = -2.5 \ V, & I_D = -4.5 \ A \\ &V_{GS} = -4.5 \ V, I_D = -5.5 A, T_J = 125 ^{\circ} C \end{aligned} $		37 57 50	45 75 65	mΩ
g FS	Forward Transconductance	$V_{DS} = -5 \text{ V}, \qquad I_{D} = -5.5 \text{ A}$		15		S
Dvnamic	Characteristics					
C _{iss}	Input Capacitance	$V_{DS} = -10 \text{ V}, V_{GS} = 0 \text{ V},$		884		pF
C _{oss}	Output Capacitance	f = 1.0 MHz		258		pF
C _{rss}	Reverse Transfer Capacitance			103		pF
Switchin	g Characteristics (Note 2)					
t _{d(on)}	Turn-On Delay Time	$V_{DD} = -10 \text{ V}, I_{D} = -1 \text{ A},$		12	22	ns
t _r	Turn-On Rise Time	$V_{\text{GS}} = -4.5 \text{ V}, R_{\text{GEN}} = 6 \ \Omega$		9	18	ns
$t_{d(off)}$	Turn-Off Delay Time			36	58	ns
t _f	Turn-Off Fall Time			24	38	ns
Q_g	Total Gate Charge	$V_{DS} = -10 \text{ V}, I_{D} = -5.5 \text{ A},$		9	13	nC
Q_{gs}	Gate-Source Charge	$V_{GS} = -4.5 \text{ V}$		2		nC
Q_{gd}	Gate-Drain Charge			3		nC
Drain-So	ource Diode Characteristics	and Maximum Ratings				
Is	Maximum Continuous Drain-Source	Diode Forward Current			-1.8	Α
V_{SD}	Drain-Source Diode Forward Voltage	$V_{GS} = 0 \text{ V}, I_S = -1.8 \text{ A} \text{(Note 2)}$		-0.76	-1.2	V
t _{rr}	Diode Reverse Recovery Time	$I_F = -5.5 \text{ A},$		25		nS
Q _{rr}	Diode Reverse Recovery Charge	$d_{iF}/d_{t} = 100 \text{ A/}\mu\text{s}$		26		nC

Notes: 1. R_{eJA} is determined with the device mounted on a 1 in² 2 oz. copper pad on a 1.5 x 1.5 in. board of FR-4 material. The thermal resistance from the junction to the circuit board side of the solder ball, R_{eJB} , is defined for reference. For R_{eJC} , the thermal reference point for the case is defined as the top surface of the copper chip carrier. R_{eJC} and R_{eJB} are guaranteed by design while R_{eJA} is determined by the user's board design.




a) 60 °C/W when mounted on a 1in² pad of 2 oz copper



o) 108°C/W when mounted on a minimum pad of 2 oz copper

Scale 1 : 1 on letter size paper
1. 2. Pulse Test: Pulse Width < 300µs, Duty Cycle < 2.0%



Typical Characteristics




Figure 1. On-Region Characteristics.




Figure 3. On-Resistance Variation with Temperature.




Figure 5. Transfer Characteristics.




Figure 2. On-Resistance Variation with Drain Current and Gate Voltage.




Figure 4. On-Resistance Variation with Gate-to-Source Voltage.





Figure 6. Body Diode Forward Voltage Variation with Source Current and Temperature.

Typical Characteristics






Figure 7. Gate Charge Characteristics.



DRAIN CURRENT (A) 10 V_{GS} = -4.5V SINGLE PULSE 0.1 مَـ $R_{\theta JA} = 108^{\circ}C/W$ $T_A = 25^{\circ}C$ 0.01 0.1 10

Figure 8. Capacitance Characteristics.




Figure 9. Maximum Safe Operating Area.

-V_{DS}, DRAIN-SOURCE VOLTAGE (V)






Figure 11. Transient Thermal Response Curve.

Thermal characterization performed using the conditions described in Note 1b. Transient thermal response will change depending on the circuit board design.

TRADEMARKS

The following are registered and unregistered trademarks Fairchild Semiconductor owns or is authorized to use and is not intended to be an exhaustive list of all such trademarks.

	$ACEx^{TM}$	FAST®	ISOPLANAR™	Power247™	SuperFET™
	ActiveArray™	FASTr™	LittleFET™	PowerSaver™	SuperSOT™-3
	Bottomless™	FPS™	$MICROCOUPLER^{TM}$	PowerTrench®	SuperSOT™-6
	CoolFET™	FRFET™	MicroFET™	QFET®	SuperSOT™-8
	$CROSSVOLT^{\text{TM}}$	GlobalOptoisolator™	MicroPak™	QS^{TM}	SyncFET™
	DOME™	GTO™ .	MICROWIRE™	QT Optoelectronics™	TinyLogic [®]
	EcoSPARK™	HiSeC™	MSXTM	Quiet Series™	TINYOPTO™
	E ² CMOS TM	I ² C TM	MSXPro™	RapidConfigure™	TruTranslation™
	EnSigna™	<i>i-</i> Lo [™]	OCX^{TM}	RapidConnect™	UHC™
	FACT™	ImpliedDisconnect™	OCXPro™	μSerDes™	UltraFET®
	FACT Quiet Serie	es [™]	OPTOLOGIC®	SILENT SWITCHER®	VCX TM
Across the board. Around the world.™		OPTOPLANAR™	SMART START™		
	The Power France		PACMAN™	SPM TM	
				<u> </u>	

DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS.

POPTM

LIFE SUPPORT POLICY

 $Programmable \ Active \ Droop^{\tiny\mathsf{TM}}$

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

- 1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, or (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the
- 2. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

Stealth™

PRODUCT STATUS DEFINITIONS

Definition of Terms

Datasheet Identification	Product Status	Definition		
Advance Information	Formative or In Design	This datasheet contains the design specifications for product development. Specifications may change in any manner without notice.		
Preliminary	First Production	This datasheet contains preliminary data, and supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.		
No Identification Needed	Full Production	This datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.		
Obsolete	Not In Production	This datasheet contains specifications on a product that has been discontinued by Fairchild semiconductor. The datasheet is printed for reference information only.		

Rev. I11