



FDFS6N303 N-Channel MOSFET with Schottky Diode

General Description

The FDFS6N303 incorporates a high cell density MOSFET and low forward drop (0.35V) Schottky diode into a single surface mount power package. The MOSFET and Schottky diode are isolated inside the package. The general purpose pinout has been chosen to maximize flexibility and ease of use. This product is particularly suited for switching applications such as DC/DC buck, boost, synchronous, and non-synchronous converters where the MOSFET is driven as low as 4.5V and fast switching, high efficiency and small PCB footprint is desirable.

Features

- 6 A, 30 V. $R_{DS(ON)} = 0.035 \Omega @ V_{GS} = 10 \text{ V}$.
 $R_{DS(ON)} = 0.055 \Omega @ V_{GS} = 4.5 \text{ V}$.
- $V_F < 0.28 \text{ V @ } 0.1 \text{ A}$
 $V_F < 0.42 \text{ V @ } 3 \text{ A}$
 $V_F < 0.50 \text{ V @ } 6 \text{ A}$.
- Schottky and MOSFET incorporated into single power surface mount SO-8 package.
- General purpose pinout for design flexibility.
- Ideal for DC/DC converter applications.



MOSFET Maximum Ratings $T_A = 25^\circ\text{C}$ unless otherwise noted

Symbol	Parameter	FDFS6N303	Units
V_{DSS}	Drain-Source Voltage	30	V
V_{GSS}	Gate-Source Voltage	± 20	V
I_D	Drain Current - Continuous (Note 1a)	6	A
	- Pulsed	30	
P_D	Power Dissipation for Dual Operation	2	W
	Power Dissipation for Single Operation (Note 1a)	1.6	
	(Note 1c)	0.9	
T_J, T_{STG}	Operating and Storage Temperature Range	-55 to 150	$^\circ\text{C}$

Schottky Diode Maximum Ratings $T_A = 25^\circ\text{C}$ unless otherwise noted

V_{RRM}	Repetitive Peak Reverse Voltage	30	V
I_O	Average Forward Current (Note 1a)	2	A

Electrical Characteristics (T_A = 25 °C unless otherwise noted)

MOSFET ELECTRICAL CHARACTERISTICS

Symbol	Parameter	Conditions	Min	Typ	Max	Units
BV _{DSS}	Drain-Source Breakdown Voltage	V _{GS} = 0 V, I _D = 250 μA	30			V
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} = 24 V, V _{GS} = 0 V			1	μA
		T _J = 125°C			20	μA
I _{GSSF}	Gate - Body Leakage, Forward	V _{GS} = 20 V, V _{DS} = 0 V			100	nA
I _{GSSR}	Gate - Body Leakage, Reverse	V _{GS} = -20 V, V _{DS} = 0 V			-100	nA
V _{GS(th)}	Gate Threshold Voltage	V _{DS} = V _{GS} , I _D = 250 μA	1	1.7	3	V
R _{DS(on)}	Static Drain-Source On-Resistance	V _{GS} = 10 V, I _D = 6 A		0.025	0.035	Ω
		V _{GS} = 4.5 V, I _D = 4.8 A		0.043	0.055	
g _{FS}	Forward Transconductance	V _{DS} = 10 V, I _D = 6 A		12		S
I _{D(on)}	On-State Drain Current	V _{GS} = 10 V, V _{DS} = 5 V	15			A
C _{iss}	Input Capacitance	V _{DS} = 15 V, V _{GS} = 0 V,		350		pF
C _{oss}	Output Capacitance	f = 1.0 MHz		220		pF
C _{rss}	Reverse Transfer Capacitance			80		pF
Q _g	Total Gate Charge	V _{DS} = 15 V, I _D = 6 A, V _{GS} = 10 V		12	17	nC
t _{D(on)}	Turn - On Delay Time	V _{DD} = 10 V, I _D = 1 A,		7.5	15	ns
t _r	Turn - On Rise Time	V _{GS} = 4.5 V, R _{GEN} = 6 Ω		12	25	ns
t _{D(off)}	Turn - Off Delay Time			13	25	ns
t _f	Turn - Off Fall Time			6	15	ns

MOSFET DRAIN-SOURCE DIODE CHARACTERISTICS AND MAXIMUM RATINGS

I _S	Maximum Continuous Drain-Source Diode Forward Current				1.3	A
V _{SD}	Drain-Source Diode Forward Voltage	V _{GS} = 0 V, I _S = 1.3 A (Note 2)		0.8	1.2	V

SCHOTTKY DIODE CHARACTERISTICS


B _V	Reverse Breakdown Voltage	I _R = 1 mA	30			V
I _R	Reverse Leakage	V _R = 30 V			0.5	mA
V _F	Forward Voltage	I _F = 0.1 A			280	mV
		I _F = 3 A			420	
		I _F = 6 A			500	

THERMAL CHARACTERISTICS


R _{θJA}	Thermal Resistance, Junction-to-Ambient	(Note 1a)		78		°C/W
R _{θJC}	Thermal Resistance, Junction-to-Case	(Note 1)		40		°C/W

Notes:


- R_{θJA} is the sum of the junction-to-case and case-to-ambient thermal resistance where the case thermal reference is defined as the solder mounting surface of the drain pins. R_{θJC} is guaranteed by design while R_{θCA} is determined by the user's board design.



a. 78°C/W on a 0.5 in² pad of 2oz copper.



b. 125°C/W on a 0.02 in² pad of 2oz copper.



c. 135°C/W on a 0.003 in² pad of 2oz copper.

- Scale 1 : 1 on letter size paper
 2. Pulse Test: Pulse Width ≤ 300μs, Duty Cycle ≤ 2.0%.

Typical Electrical Characteristics




Figure 1. On-Region Characteristics.




Figure 2. On-Resistance Variation with Drain Current and Gate Voltage.




Figure 3. On-Resistance Variation with Temperature.




Figure 4. On-Resistance Variation with Gate-to-Source Voltage.




Figure 5. Transfer Characteristics.




Figure 6. Body Diode Forward Voltage Variation with Source Current and Temperature.

Typical Fet And Schottky Electrical Characteristics




Figure 7. Gate Charge Characteristics.




Figure 8. Capacitance Characteristics.




Figure 9. Schottky Diode Forward Voltage.




Figure 10. Schottky Diode Reverse Current.




Figure 11. Transient Thermal Response Curve.

Thermal characterization performed using the conditions described in note 1c.
Transient thermal response will change depending on the circuit board design.

TRADEMARKS

The following are registered and unregistered trademarks Fairchild Semiconductor owns or is authorized to use and is not intended to be an exhaustive list of all such trademarks.

ACEx™	FACT Quiet Series™	LittleFET™	Power247™	SuperSOT™-6
ActiveArray™	FAST®	MICROCOUPLER™	PowerTrench®	SuperSOT™-8
Bottomless™	FASTr™	MicroFET™	QFET®	SyncFET™
CoolFET™	FRFET™	MicroPak™	QS™	TinyLogic®
CROSSVOLT™	GlobalOptoisolator™	MICROWIRE™	QT Optoelectronics™	TINYOPTO™
DOMET™	GTO™	MSX™	Quiet Series™	TruTranslation™
EcoSPARK™	HiSeC™	MSXPro™	RapidConfigure™	UHC™
E ² CMOS™	I ² C™	OCX™	RapidConnect™	UltraFET®
EnSigna™	ImpliedDisconnect™	OCXPro™	SILENT SWITCHER®	VCX™
FACT™	ISOPLANAR™	OPTOLOGIC®	SMART START™	
Across the board. Around the world.™	OPTOPLANAR™	SPM™		
The Power Franchise™	PACMAN™	Stealth™		
Programmable Active Droop™	POP™	SuperSOT™-3		

DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS.

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION.

As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, or (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.
2. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

PRODUCT STATUS DEFINITIONS

Definition of Terms

Datasheet Identification	Product Status	Definition
Advance Information	Formative or In Design	This datasheet contains the design specifications for product development. Specifications may change in any manner without notice.
Preliminary	First Production	This datasheet contains preliminary data, and supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.
No Identification Needed	Full Production	This datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.
Obsolete	Not In Production	This datasheet contains specifications on a product that has been discontinued by Fairchild semiconductor. The datasheet is printed for reference information only.