February 1996



SEMICONDUCTOR TM


NDS9405 Single P-Channel Enhancement Mode Field Effect Transistor

General Description

These P-Channel enhancement mode power field effect transistors are produced using Fairchild's proprietary, high cell density, DMOS technology. This very high density process is been especially tailored to minimize on-state resistance, provide superior switching performance, and withstand high energy pulses in the avalanche and commutation modes. These devices are particularly suited for low voltage applications such as notebook computer power management and other battery powered circuits where fast switching, low in-line power loss, and resistance to transients are needed.

Features


- -4.3A, -20V. $R_{DS(ON)} = 0.10\Omega @ V_{GS} = -10V$
- High density cell design for extremely low R_{DS(ON)}
- High power and current handling capability in a widely used surface mount package.





Absolute Maximum Ratings $T_{A} = 25^{\circ}C$ unless otherwise noted


| Symbol | Parameter | NDS9405 | Units |
|-----------------------------------|--|------------|-------|
| V _{DSS} | Drain-Source Voltage | -20 | V |
| V _{GSS} | Gate-Source Voltage | ± 20 | V |
| D | Drain Current - Continuous T _A = 25°C (Note 1a) | ± 4.3 | A |
| | - Continuous T _A = 70°C (Note 1a) | ± 3.3 | |
| | - Pulsed $T_A = 25^{\circ}C$ | ± 20 | |
| P _D | Maximum Power Dissipation (Note 1a) | 2.5 | W |
| | (Note 1b) | 1.2 | |
| | (Note 1c) | 1 | |
| Γ _J , T _{stg} | Operating and Storage Temperature Range | -55 to 150 | C° |
| THERMA | L CHARACTERISTICS | | · |
| ۲ _{өја} | Thermal Resistance, Junction-to-Ambient (Note 1a) | 50 | °C/W |
| ۲ _{өлс} | Thermal Resistance, Junction-to-Case (Note 1) | 25 | °C/W |


| Symbol | Parameter | Conditions | | Min | Тур | Max | Units |
|---------------------|-----------------------------------|--|------------------------|-------|-------|------|-------|
| OFF CHA | RACTERISTICS | | | | | | |
| BV _{DSS} | Drain-Source Breakdown Voltage | V _{gs} = 0 V, I _p = -250 μA | | -20 | | | V |
| I _{DSS} | Zero Gate Voltage Drain Current | V _{DS} = -16 V, V _{GS} = 0 V | | | | -2 | μA |
| | | | T _J = 55°C | | | -25 | μA |
| I _{GSSF} | Gate - Body Leakage, Forward | V _{GS} = 20 V, V _{DS} = 0 V | · | | | 100 | nA |
| | Gate - Body Leakage, Reverse | V _{gs} = -20 V, V _{ps} = 0 V | | | | -100 | nA |
| ON CHAR | ACTERISTICS (Note 2) | | | | | | |
| $V_{\text{GS(th)}}$ | Gate Threshold Voltage | $V_{\text{DS}} = V_{\text{GS}}, I_{\text{D}} = -250 \mu\text{A}$ | | -0.5 | -1.65 | -3 | V |
| | | | T_= 125°C | -0.85 | | -2.6 |] |
| R _{DS(ON)} | Static Drain-Source On-Resistance | V _{gs} = -10 V, I _p = -2 A | | | 0.053 | 0.1 | Ω |
| | | | T _J = 125°C | | 0.075 | 0.15 | 1 |
| | | $V_{gg} = -4.5 V, I_{p} = -2 A$ | · | | 0.08 | 0.16 | 1 |
| | | | T_= 125°C | | 0.12 | 0.24 | 1 |
| I _{D(on)} | On-State Drain Current | V _{GS} = -10 V, V _{DS} = -5 V | · | -20 | | | Α |
| | | V _{GS} = -4.5, V _{DS} = -5V | | -5 | | | 1 |
| 9 _{FS} | Forward Transconductance | V _{DS} = -15 V, I _D = -4.3 A | | | 9 | | S |
| | CHARACTERISTICS | | | | | | |
| C _{iss} | Input Capacitance | $V_{DS} = -10 V, V_{GS} = 0 V,$ f = 1.0 MHz | | | 1425 | | pF |
| C _{oss} | Output Capacitance | | | | 850 | | pF |
| C _{rss} | Reverse Transfer Capacitance | | | | 430 | | pF |
| SWITCHIN | IG CHARACTERISTICS (Note 2) | | | 1 | | | |
| t _{D(on)} | Tum - On Delay Time | $V_{DD} = -10 V, I_D = -1 A,$ | | | 17 | 30 | ns |
| ţ, | Turn - On Rise Time | V_{GEN} = -10 V, R_{GEN} = 6 Ω | | | 24 | 80 | ns |
| t _{D(off)} | Turn - Off Delay Time | | | | 56 | 200 | ns |
| t _r | Turn - Off Fall Time | | | | 30 | 200 | ns |
| Q _g | Total Gate Charge | $V_{DS} = -10 V,$ $I_{D} = -4.3 A, V_{GS} = -10 V$ | | | | 40 | nC |
| Q _{gs} | Gate-Source Charge | | | | | 5 | nC |
| Q_{gd} | Gate-Drain Charge | | | | | 25 | nC |













July 1999, Rev. B





TRADEMARKS

The following are registered and unregistered trademarks Fairchild Semiconductor owns or is authorized to use and is not intended to be an exhaustive list of all such trademarks.

ACExTM CoolFETTM CROSSVOLTTM E²CMOSTM FACTTM FACT Quiet SeriesTM FAST[®] FAST[®] FASTrTM GTOTM HiSeCTM ISOPLANAR™ MICROWIRE™ POP™ PowerTrench® QFET™ QS™ Quiet Series™ SuperSOT™-3 SuperSOT™-6 SuperSOT™-8 SyncFET™ TinyLogic™ UHC™ VCX™

DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS.

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, or (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user. 2. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

PRODUCT STATUS DEFINITIONS

Definition of Terms

| Datasheet Identification | Product Status | Definition |
|--------------------------|---------------------------|---|
| Advance Information | Formative or In Design | This datasheet contains the design specifications for product development. Specifications may change in any manner without notice. |
| Preliminary | First Production | This datasheet contains preliminary data, and supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design. |
| No Identification Needed | Full Production | This datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design. |
| Obsolete | Not In Production | This datasheet contains specifications on a product that has been discontinued by Fairchild semiconductor. The datasheet is printed for reference information only. |