

May 2007

FDFC3N108

N-Channel 1.8V Specified PowerTrench^o MOSFET with Schottky Diode

General Description

This N-Channel 1.8V specified MOSFET uses Fairchild's advanced low voltage PowerTrench process. It is combined with a low forward drop Schottky that is isolated from the MOSFET, providing a compact power solution for battery power management and DC/DC converter applications.

Applications

- Battery management/Charger Application
- DC/DC Conversion

Features


- 3 A, 20 V $R_{DS(ON)} = 70 \text{ m}\Omega$ @ $V_{GS} = 4.5 \text{ V}$ $R_{DS(ON)} = 95 \text{ m}\Omega$ @ $V_{GS} = 2.5 \text{ V}$
- · Low gate charge
- High performance trench technology for extremely low R_{DS(ON)}





Pin 1

SuperSOT™-6



MOSFET Maximum Ratings TA=25°C unless otherwise noted

Symbol	Parameter		Ratings	Units
V _{DSS}	Drain-Source Voltage		20	V
V _{GSS}	Gate-Source Voltage		±12	V
I _D	Drain Current - Continuous	(Note 1a)	3	А
	– Pulsed		12	
P _D	Maximum Power Dissipation	(Note 1a)	0.96	W
		(Note 1b)	0.90	
		(Note 1c)	0.70	
T _J , T _{stg}	Operating and Storage Junction Temperat	ture Range	-55 to +150	°C

Schottky Diode Maximum Ratings

V_{RRM}	Repetitive Peak reverse voltage	20	V
Io	Average Forward Current	2.0	Α

Thermal Characteristics

$R_{\theta JA}$	Thermal Resistance, Junction-to-Ambient	(Note 1a)	130	°C/W
Raic	Thermal Resistance, Junction-to-Case	(Note 1)	60	

Package Marking and Ordering Information

Device Marking	Device	Reel Size	Tape width	Quantity
.108	FDFC3N108	7"	8mm	3000 units

Symbol	Parameter	Test	Conditions	Min	Тур	Max	Units
Off Char	acteristics	•			•	I.	I.
BV _{DSS}	Drain–Source Breakdown Voltage	$V_{GS} = 0 V$,	I _D = 250 μA	20			V
ΔBV _{DSS} ΔT _J	Breakdown Voltage Temperature Coefficient	$I_D = 250 \mu A, F$	Referenced to 25°C		12		mV/°C
I _{DSS}	Zero Gate Voltage Drain Current	$V_{DS} = 16 \text{ V},$	V _{GS} = 0 V			1	μΑ
I _{GSS}	Gate-Body Leakage	$V_{GS} = \pm 12 \text{ V},$	V _{DS} = 0 V			±100	nA
On Chara	acteristics (Note 2)			•		•	
V _{GS(th)}	Gate Threshold Voltage	$V_{DS} = V_{GS}$	I _D = 250 μA	0.5	0.9	1.5	V
$\Delta V_{GS(th)} \over \Delta T_J$	Gate Threshold Voltage Temperature Coefficient		Referenced to 25°C		-3		mV/°C
R _{DS(on)}	Static Drain–Source On–Resistance	$V_{GS} = 4.5 \text{ V},$ $V_{GS} = 2.5 \text{ V},$ $V_{GS} = 4.5 \text{ V},$			56 73 78	70 95 106	mΩ
I _{D(on)}	On–State Drain Current	$V_{GS} = 4.5 \text{ V},$		12			Α
g FS	Forward Transconductance	$V_{DS} = 5 V$,	$I_D = 3 A$		10		S
Dvnamic	Characteristics			•		•	
C _{iss}	Input Capacitance	V _{DS} = 10 V,	V - 0 V		355		pF
C _{oss}	Output Capacitance	f = 1.0 MHz	v _{GS} – U v,		85		pF
C _{rss}	Reverse Transfer Capacitance				45		pF
R _G	Gate Resistance	$V_{GS} = 15 \text{ mV},$	f = 1.0 MHz		2.0		Ω
Switchin	g Characteristics (Note 2)	I			1	ı	
t _{d(on)}	Turn-On Delay Time	$V_{DD} = 10 \text{ V},$	I _D = 1 A.		6	12	ns
t _r	Turn-On Rise Time	$V_{GS} = 4.5 \text{ V},$	-		7	14	ns
t _{d(off)}	Turn-Off Delay Time	1			20	36	ns
t _f	Turn-Off Fall Time	1			1	2	ns
Qg	Total Gate Charge	V _{DS} = 10V,	I _D = 3 A,		3.5	4.9	nC
Q _{gs}	Gate-Source Charge	$V_{GS} = 4.5 \text{ V}$.5,		0.7		nC
Q _{gd}	Gate-Drain Charge	-			1.0		nC
Drain-Sc	ource Diode Characteristics	and Maxin	num Ratings		1		
I _s	Maximum Continuous Drain-Source			1		0.8	Α
V _{SD}	Drain–Source Diode Forward Voltage		I _S = 0.8 A (Note 2)			1.2	V
t _{rr}	Diode Reverse Recovery Time	I _F = 3 A,			12		nS
Q _{rr}	Diode Reverse Recovery Charge	$d_{iF}/d_t = 100 \text{ A/}$	μs		3		nC
Schottky	Diode Characteristic	•			•		
I _R	Reverse Leakage	V _R = 20V	T _J = 25 °C T _J = 100 °C			250 10	μA mA
V _F	Forward Voltage	I _F = 1A	, 0 :55 5		363	425	mV
		$I_F = 2A$			449	550	

Electrical Characteristics

T_A = 25°C unless otherwise noted

Notes

 R_{8,JA} is the sum of the junction-to-case and case-to-ambient thermal resistance where the case thermal reference is defined as the solder mounting surface of the drain pins. R_{8,JC} is guaranteed by design while R_{9CA} is determined by the user's board design.



 a) 130 °C/W when mounted on a 0.125 in² pad of 2 oz. copper.



b) 140 °C/W when mounted on a .004 in² pad of 2 oz copper



c) 180 C°/W when mounted on a minimum pad.

Scale 1:1 on letter size paper

2. Pulse Test: Pulse Width < 300µs, Duty Cycle < 2.0%

Typical Characteristics




Figure 1. On-Region Characteristics.




Figure 3. On-Resistance Variation with Temperature.




Figure 5. Transfer Characteristics.




Figure 2. On-Resistance Variation with Drain Current and Gate Voltage.




Figure 4. On-Resistance Variation with Gate-to-Source Voltage.





Figure 6. Body Diode Forward Voltage Variation with Source Current and Temperature.

Typical Characteristics








Figure 7. Gate Charge Characteristics.








Figure 9. Schottky Diode Forward Voltage.

Figure 10. Schottky Diode Reverse Current.




Figure 11. Transient Thermal Response Curve.

Thermal characterization performed using the conditions described in Note 1b Transient thermal response will change depending on the circuit board design.





TRADEMARKS

The following are registered and unregistered trademarks and service marks Fairchild Semiconductor owns or is authorized to use and is not intended to be an exhaustive list of all such trademarks.

ACEx [®]	Green FPS™ e-Series™	Power-SPM™	SyncFET™
Build it Now™	GTO™	PowerTrench [®]	The Power Franchise®
CorePLUS™	i-Lo™	Programmable Active Droop™	U TM
$CROSSVOLT^{TM}$	IntelliMAX™	QFET [®]	TinyBoost™
CTL™	ISOPLANAR™	QS™	TinyBuck™
Current Transfer Logic™	MegaBuck™	QT Optoelectronics™	TinyLogic [®]
EcoSPARK [®]	MICROCOUPLER™	Quiet Series™	TINYOPTO™
FACT Quiet Series™	MicroPak™	RapidConfigure™	TinyPower™
FACT [®]	Motion-SPM™	SMART START™	TinyPWM™
FAST [®]	OPTOLOGIC [®]	SPM [®]	TinyWire™
FastvCore™	OPTOPLANAR [®]	STEALTH™	µSerDes™
FPS™	PDP-SPM™	SuperFET™	UHC®
FRFET [®]	Power220 [®]	SuperSOT™-3	UniFET™
Global Power Resource SM	Power247 [®]	SuperSOT™-6	VCX™
Green FPS™	POWEREDGE [®]	SuperSOT™-8	

DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION, OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS. THESE SPECIFICATIONS DO NOT EXPAND THE TERMS OF FAIRCHILD'S WORLDWIDE TERMS AND CONDITIONS, SPECIFICALLY THE WARRANTY THEREIN, WHICH COVERS THESE PRODUCTS.

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION.

As used herein:

- 1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
- 2. A critical component in any component of a life support, device, or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

PRODUCT STATUS DEFINITIONS

Definition of Terms

Datasheet Identification	Product Status	Definition
Advance Information	Formative or In Design	This datasheet contains the design specifications for product development. Specifications may change in any manner without notice.
Preliminary	First Production	This datasheet contains preliminary data; supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve design.
No Identification Needed	Full Production	This datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve design.
Obsolete	Not In Production	This datasheet contains specifications on a product that has been discontinued by Fairchild Semiconductor. The datasheet is printed for reference information only.

Rev. I28