


January 2007

1N/FDLL 914/A/B / 916/A/B / 4148 / 4448 **Small Signal Diode**







THE PLACEMENT OF THE EXPANSION GAP HAS NO RELATIONSHIP TO THE LOCATION OF THE CATHODE TERMINAL

LL-34 COLOR BAND MARKING

DEVICE	1ST BAND	2ND BAND
FDLL914	BLACK	BROWN
FDLL914A	BLACK	GRAY
FDLL914B	BROWN	BLACK
FDLL916	BLACK	RED
FDLL916A	BLACK	WHITE
FDLL916B	BROWN	BROWN
FDLL4148	BLACK	BROWN
FDLL4448	BROWN	BLACK

-1st band denotes cathode terminal and has wider width

Absolute Maximum Ratings* Ta=25°C unless otherwise noted

Symbol	Parameter	Value	Units
V _{RRM}	Maximum Repetitive Reverse Voltage	100	V
I _O	Average Rectified Forward Current	200	mA
I _F	DC Forward Current	300	mA
i _f	Recurrent Peak Forward Current	400	mA
I _{FSM}	Non-repetitive Peak Forward Surge Current Pulse Width = 1.0 second Pulse Width = 1.0 microsecond	1.0 4.0	A A
T _{STG}	Storage Temperature Range	-65 to +200	°C
TJ	Operating Junction Temperature	175	°C

^{*} These ratings are limiting values above which the serviceability of the diode may be impaired.

Thermal Characteristics

Symbol Parameter		Max.	Units	
Cymbol	T didiffeter	1N/FDLL 914/A/B / 4148 / 4448	Omis	
P_{D}	Power Dissipation	500	mW	
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient	300	°C/W	

These ratings are based on a maximum junction temperature of 200 degrees C.
 These are steady state limits. The factory should be consulted on applications involving pulsed or low duty cycle operations.

Electrical Characteristics* T_A=25°C unless otherwise noted

Symbol	Parameter	Test Conditions	Min.	Max.	Units
V _R	Breakdown Voltage	$I_R = 100 \mu A$ $I_R = 5.0 \mu A$	100 75		V V
V _F	1N916 1N914/916/414 1N914A/916 1N916	1 :	620 630	720 730 1.0 1.0 1.0	mV mV V V
I _R	Reverse Leakage	V _R = 20V V _R = 20V, T _A = 150°C V _R = 75V		25 50 5.0	nA μA μA
Ст	Total Capacitance 1N916A/B/4448 1N914A/B/4148	V _R = 0, f = 1.0MHz V _R = 0, f = 1.0MHz		2.0 4.0	pF pF
t _{rr}	Reverse Recovery Time	$I_F = 10mA, V_R = 6.0V (600mA)$ $I_{rr} = 1.0mA, R_L = 100\Omega$		4.0	ns

^{*} Non-recurrent square wave PW = 8.3ms

Typical Characteristics




Figure 1. Reverse Voltage vs Reverse Current BV - 1.0 to $100\mu A$





Figure 3. Forward Voltage vs Forward Current VF - 1 to $100 \mu A$



GENERAL RULE: The Reverse Current of a diode will approximately double for every ten (10) Degree C increase in Temperature

Figure 2. Reverse Current vs Reverse Voltage IR - 10 to 100V




Figure 4. Forward Voltage vs Forward Current VF - 0.1 to 10mA

Typical Characteristics (Continued)




Figure 5. Forward Voltage vs Forward Current VF - 10 to 800mA




Figure 7. Total Capacitance




Figure 9. Average Rectified Current $(I_{F(AV)})$ vs Ambient Temperature (T_A)





Figure 6. Forward Voltage vs Ambient Temperature VF - 0.01 - 20 mA (- 40 to +65°C)



IF = 10mA , IRR = 1.0 mA , Rloop = 100 Ohms
Figure 8. Reverse Recovery Time vs
Reverse Recovery Current




Figure 10. Power Derating Curve

UniFET™

 VCX^{TM}

Wire™



FAIRCHILD SEMICONDUCTOR TRADEMARKS

The following are registered and unregistered trademarks Fairchild Semiconductor owns or is authorized to use and is not intended to be an exhaustive list of all such trademarks.

 OCX^{TM} $ACEx^{TM}$ SILENT SWITCHER® FACT Quiet Series™ $OCXPro^{TM}$ ActiveArray™ GlobalOptoisolator™ SMART START™ OPTOLOGIC® SPM™ Bottomless™ **GTO™ OPTOPLANAR™** Build it Now™ HiSeC™ Stealth™ I^2C^{TM} PACMANTM CoolFET™ SuperFET™ $CROSSVOLT^{\rm TM}$ i-Lo™ РОРТМ SuperSOT™-3 Power247™ DOME™ ImpliedDisconnect™ SuperSOT™-6 EcoSPARK™ PowerEdge™ IntelliMAX™ SuperSOT™-8 E²CMOS™ ISOPLANAR™ PowerSaver™ SyncFET™ PowerTrench® TCM^TM EnSigna™ LittleFET™ FACT[®] $\mathsf{MICROCOUPLER}^{\mathsf{TM}}$ QFET[®] TinyBoost™ $\mathsf{FAST}^{\mathbb{R}}$ QSTM TinyBuck™ MicroFET™ FASTr™ QT Optoelectronics™ TinyPWM™ MicroPak™ FPS™ MICROWIRE™ Quiet Series™ TinyPower™ RapidConfigure™ FRFET™ TinyLogic[®] MSX™ MSXPro™ RapidConnect™ TINYOPTO™ μSerDes™ Across the board. Around the world.™ TruTranslation™ ScalarPump™ **UHC®**

The Power Franchise®

Programmable Active Droop™

DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS. THESE SPECIFICATIONS DO NOT EXPAND THE TERMS OF FAIRCHILD'S WORLDWIDE TERMS AND CONDITIONS, SPE-CIFICALLY THE WARRANTY THEREIN, WHICH COVERS THESE PRODUCTS.

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION.

As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, or (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

2. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

PRODUCT STATUS DEFINITIONS

Definition of Terms

Datasheet Identification	Product Status	Definition
Advance Information	Formative or In Design	This datasheet contains the design specifications for product development. Specifications may change in any manner without notice.
Preliminary	First Production	This datasheet contains preliminary data, and supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.
No Identification Needed	Full Production	This datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.
Obsolete	Not In Production	This datasheet contains specifications on a product that has been discontinued by Fairchild semiconductor. The datasheet is printed for reference information only.

Rev. 122

Search:

Go

DATASHEETS, SAMPLES, BUY TECHNICAL INFORMATION APPLICATIONS DESIGN CENTER SUPPORT COMPANY INVESTORS MY F.

Home >> Find products >>

1N914B

High Conductance Fast Diode

Contents

- Product status/pricing/packaging
- Order Samples
- Models
- Qualification Support

BUY

Datasheet Download this datasheet



e-mail this datasheet



Related Links

Request samples

How to order products

Product Change Notices (PCNs)

Support

Sales support

Quality and reliability

Design center

This page **Print version**

Product status/pricing/packaging

BUY

Product	Product status	Pb-free Status	Pricing*	Package type	Leads	Packing method	Package Marking Convention**
1N914B	Full Production	Full Production	\$0.0116	DO-35	2	BULK	Line 1: \$Y (Fairchild logo) Line 2: 91 Line 3: 4B
1N914BTR	Full Production	Full Production	\$0.0116	DO-35	2	TAPE REEL	Line 1: \$Y (Fairchild logo) Line 2: 91 Line 3: 4B
1N914BTR_NL	Full Production	Full Production	N/A	DO-35	2	TAPE REEL	Line 1: \$Y (Fairchild logo) Line 2: 91 Line 3: 4B
1N914B_S62Z	Full Production		N/A	DO-35	2	BULK	Line 1: \$Y (Fairchild logo)

		Full Production					<u>Line 2:</u> 91 <u>Line 3:</u> 4B
1N914B_T50A	Full Production	Full Production	N/A	DO-35	2	AMMO	Line 1: \$Y (Fairchild logo) Line 2: 91 Line 3: 4B
1N914B_T50R	Full Production	Full Production	N/A	DO-35	2		Line 1: \$Y (Fairchild logo) Line 2: 91 Line 3: 4B

^{*} Fairchild 1,000 piece Budgetary Pricing

** A sample button will appear if the part is available through Fairchild's on-line samples program. If there is no sample button, please contact a Fairchild distributor to obtain samples



Indicates product with Pb-free second-level interconnect. For more information click here.

Package marking information for product 1N914B is available. Click here for more information.

back to top

Models

Package & leads	Condition	Temperature range	Vcc range	Software version	Revision date
		PSPICE			
DO-35-2	<u>Electrical</u>	25°C	N/A	N/A	N/A
DO-30-2	<u>Electrical</u>	-40°C to 65°C	0V to 4V	OrCAD 10.3	May 31, 2007

back to top

Qualification Support

Click on a product for detailed qualification data

Product
<u>1N914B</u>
1N914BTR
1N914BTR_NL
1N914B_S62Z

1N914B_T50A 1N914B_T50R

back to top

© 2007 Fairchild Semiconductor



Products | Design Center | Support | Company News | Investors | My Fairchild | Contact Us | Site Index | Privacy Policy | Site Terms & Conditions | Standard Terms & Conditions |