




MOTOROLA

QUAD 2-PORT REGISTER


The MC54/74F399 is the logical equivalent of a quad 2-input multiplexer feeding into four edge-triggered flip flops. A common Select input determines which of the two 4-bit words is accepted. The selected data enters the flip-flops on the rising edge of the clock. The MC54/74F399 is the 16-pin version of the MC54/74F398, with only the Q outputs of the flip-flops available.

- Select Inputs from Two Data Sources
- Fully Positive Edge-Triggered Operation

CONNECTION DIAGRAM (TOP VIEW)



LOGIC DIAGRAM




NOTE:

This diagram is provided only for the understanding of logic operations and should not be used to estimate propagation delays.

MC54/74F399

QUAD 2-PORT REGISTER

FAST™ SCHOTTKY TTL



J SUFFIX
CERAMIC
CASE 620-09



N SUFFIX
PLASTIC
CASE 648-08




D SUFFIX
SOIC
CASE 751B-03

ORDERING INFORMATION

MC54FXXXJ Ceramic
MC74FXXXN Plastic
MC74FXXXD SOIC

LOGIC SYMBOL



V_{CC} = PIN 16

GND = PIN 8

MC54/74F399

FUNCTIONAL DESCRIPTION

The MC54/74F399 is a high-speed quad 2-port register. It will select four bits of data from either of two sources (Ports) under control of a common Select input (S). The selected data is transferred to a 4-bit output register synchronous with the LOW-to-HIGH transition of the Clock input (CP). The 4-bit D-

type output register is fully edge-triggered. The Data inputs (I_0x , I_1x) and Select input (S) must be stable only a setup time prior to and hold time after the LOW-to-HIGH transition of the Clock input for predictable operation.

FUNCTION TABLE

Inputs			Output
S	I_0	I_1	Q
I	I	X	L
I	h	X	H
h	X	I	L
h	X	h	H

H = HIGH Voltage Level

L = LOW Voltage Level

h = HIGH Voltage Level one setup time prior to the LOW-to-HIGH clock transition

I = LOW Voltage Level one setup time prior to the LOW-to-HIGH clock transition

X = Don't Care

GUARANTEED OPERATING RANGES

Symbol	Parameter	Limits			Min	Typ	Max	Unit
		Min	Typ	Max				
V _{CC}	Supply Voltage	54, 74	4.5	5.0	5.5			V
T _A	Operating Ambient Temperature Range	54	-55	25	125			°C
		74	0	25	70			
I _{OH}	Output Current — High	54, 74					-1.0	mA
I _{OL}	Output Current — Low	54, 74					20	mA

DC CHARACTERISTICS OVER OPERATING TEMPERATURE RANGE (unless otherwise specified)

Symbol	Parameter	Limits			Unit	Test Conditions	
		Min	Typ	Max			
V _{IH}	Input HIGH Voltage	2.0			V	Guaranteed Input HIGH Voltage	
V _{IL}	Input LOW Voltage			0.8	V	Guaranteed Input LOW Voltage	
V _{IK}	Input Clamp Diode Voltage			-1.2	V	I _{IN} = -18 mA	V _{CC} = MIN
V _{OH}	Output HIGH Voltage	54, 74	2.5	3.4	V	I _{OH} = -1.0 mA	V _{CC} = 4.5 V
		74	2.7	3.4	V	I _{OH} = -1.0 mA	V _{CC} = 4.75 V
V _{OL}	Output LOW Voltage		0.35	0.5	V	I _{OL} = 20 mA	V _{CC} = MIN
I _{IH}	Input HIGH Current			20	μA	V _{IN} = 2.7 V	V _{CC} = MAX
				100	μA	V _{IN} = 7.0 V	
I _{IL}	Input LOW Current			-0.6	mA	V _{IN} = 0.5 V	V _{CC} = MAX
I _{OS}	Output Short Circuit Current (Note 2)	-60		-150	mA	V _{OUT} = 0 V	V _{CC} = MAX
I _{CC}	Power Supply Current		22	34	mA	V _{CC} = MAX	V _{IN} = GND CP = ✓

NOTES:

- For conditions shown as MIN or MAX, use the appropriate value specified under guaranteed operating ranges.
- Not more than one output should be shorted at a time, nor for more than 1 second.

MC54/74F399

AC CHARACTERISTICS

Symbol	Parameter	54/74F			54F		74F		Unit	
		$T_A = +25^\circ C$			$T_A = -55^\circ C \text{ to } +125^\circ C$		$T_A = 0^\circ C \text{ to } 70^\circ C$			
		$V_{CC} = +5.0V$			$V_{CC} = 5.0 V \pm 10\%$		$V_{CC} = 5.0 V \pm 10\%$			
Min	Typ	Max	Min	Max	Min	Max	Min	Max		
f_{max}	Maximum Clock Frequency	100	140		80		100		MHz	
t_{PLH}	Propagation Delay	3.0	5.7	7.5	3.0	9.5	3.0	8.5	ns	
t_{PHL}	CP to Q	3.0	6.8	9.5	3.0	11.5	3.0	10.0	ns	

AC OPERATING REQUIREMENTS

Symbol	Parameter	54/74F			54F		74F		Unit	
		$T_A = +25^\circ C$			$T_A = -55^\circ C \text{ to } +125^\circ C$		$T_A = 0^\circ C \text{ to } 70^\circ C$			
		$V_{CC} = +5.0V$			$V_{CC} = 5.0 V \pm 10\%$		$V_{CC} = 5.0 V \pm 10\%$			
Min	Typ	Max	Min	Max	Min	Max	Min	Max		
$t_S(H)$	Setup Time, HIGH or LOW	3.0			4.5		3.0		ns	
$t_S(L)$	I_n to CP	3.0			4.5		3.0		ns	
$t_h(H)$	Hold Time, HIGH or LOW	1.0			1.5		1.0		ns	
$t_h(L)$	I_n to CP	1.0			1.5		1.0		ns	
$t_S(H)$	Setup Time, HIGH or LOW	7.5			9.5		8.5		ns	
$t_S(L)$	S to CP	7.5			9.5		8.5		ns	
$t_h(H)$	Hold Time, HIGH or LOW	0			0		0		ns	
$t_h(L)$	S to CP	0			0		0		ns	
$t_w(H)$	CP Pulse Width HIGH or LOW	4.0			4.0		4.0		ns	
$t_w(L)$		5.0			7.0		5.0		ns	