

# **RC6334**

# **Quad Video Amplifier**

#### **Features**

- · Quad video amplifier
- 175 MHz -3 dB Bandwidth (Ay = 2)
- 50 MHz ±0.1 dB gain flatness
- Unity gain stable
- 0.06% differential gain (AV = 1, RL =  $150\Omega$ )
- $0.06^{\circ}$  differential phase (Ay = 1, RL =  $150\Omega$ )
- High CMRR (95dB), High PSRR (80 dB)
- Dual ±5V power supply
- Low offset 3.0 mV typical
- 14-pin narrow SO package
- 250V/µs slew rate
- Fast settling time: 0.1% in 15 ns
- TTL or CMOS compatible

### **Applications**


- · RGB amplifiers
- · Video instrumentation amplifier
- Selectable gain amplifier
- Active filters
- Set-top box Buffers/Drivers

# **Description**


The RC6334 consists of four low power, wide band voltage feedback operational amplifiers. Each channel is capable of delivering a load current of at least 35mA.

The amplifiers are optimized for video applications where low differential gain and low phase distortion are significant requirements.

## **Block Diagram**



# **Pin Assignments**



#### **Pin Definitions**

Pin Name	Pin Number	Pin Function Description		
IN1-	6	Amplifier 1 inverting input		
IN1+	5	Amplifier 1 non-inverting input		
IN2-	13	Amplifier 2 inverting input		
IN2+	12	Amplifier 2 non-inverting input		
IN3-	9	Amplifier 3 inverting input		
IN3+	10	Amplifier 3 non-inverting input		
IN4-	2	Amplifier 4 inverting input		
IN4+	3	Amplifier 4 non-inverting input		
OUT1	7	Amplifier 1 output		
OUT2	14	Amplifier 2 output		
OUT3	8	Amplifier 3 output		
OUT4	1	Amplifier 4 output		
Vcc	4	Analog positive supply		
VEE	11	Analog negative supply		

# **Absolute Maximum Ratings**

(beyond which the device may be damaged)<sup>1</sup>

Parameter		Min	Тур	Max	Units
Vcc	Positive power supply			7	V
VEE	Negative power supply			-7	V
	Differential input voltage			10	V
	Operating Temperature	0		+70	°C
	Storage Temperature	-40		±125	°C
	Junction Temperature			150	°C
Lead Soldering (10 seconds)				240	°C
Short circuit tolerance:  No more than one output can be shorted to ground.					

#### Notes:

# **Operating Conditions**

Parameter		Min	Тур	Max	Units
VCC Power Supply Voltage		4.75	5.0	5.25	V
VEE	VEE Negative Supply Voltage		-5.0	-5.25	V
θJΑ	SO14 Thermal Resistance		105		°C/W

<sup>1.</sup> Functional operation under any of these conditions is NOT implied.

RC6334 PRODUCT SPECIFICATION

#### **DC Characteristics**

VCC = 5V, VEE = -5V, AV = 2,  $R_{LOAD}$  = 150 $\Omega$ ,  $T_A$  = 0°C to 70°C, unless otherwise specified. Open Loop.

Parameter		Conditions	Min	Тур	Max	Units
Vos	Input Offset Voltage	No Load		3	±10	mV
ΔVos/ΔΤ	Offset Voltage Drift <sup>1</sup>			±6	±30	μV/°C
IB	Input Bias Current			±1	±5	μΑ
ΔΙΒ/ΔΤ	Input Bias Current Drift <sup>1</sup>			±8	±40	nA/°C
Rin	Input Resistance <sup>1</sup>		1			MΩ
Cin	Input Capacitance <sup>1</sup>			0.5	2	pF
CMIR	Common Mode Input Range		±2.5			V
CMRR	Common Mode Rejection Ratio	No Load	70	100		dB
PSRR	Power Supply Rejection Ratio	No Load	65	80		dB
Is	Quiescent Supply Current	No Load		33	48	mA
Rout	Output Impedance (Closed Loop) <sup>1</sup>	Enabled, At DC		0.2		Ω
lout	Output Current	Per Amplifier	35			mA
Vout	Output Voltage Swing	No Load	±2.5	±3.0		V
		RL = 150Ω	±2.5	±3.0		V
AVOL	Open-loop Gain		60	75		dB

#### Note:

### **AC Characteristics**


 $V_{CC}$  = 5V,  $V_{EE}$  = -5V,  $A_V$  = 2,  $T_A$  = 0 to 70°C,  $R_{LOAD}$  = 150 $\Omega$ ,  $R_G$  =  $R_F$  = 250 $\Omega$ ,  $C_L$  = 10 pF, unless otherwise specified. Closed Loop. Guaranteed by Design. See Typical Test Circuit.

Parameter		Conditions M		Тур	Max	Units		
Frequency Response								
BW	-3 dB Bandwidth (A∨ = 2)	Vout = 0.4 Vpp		+175		MHz		
		Vout = 0.8 Vpp	75	90		MHz		
Flat	±0.1 dB Bandwidth	VOUT = 0.4 Vpp	50	60		MHz		
Peak	Maximum Small Signal AC Peaking	Vout = 0.8 Vpp		0.01		dB		
XTALK	Crosstalk Isolation	@ 5 MHz		50		dB		
Time Do	omain Response		•					
tr1, tf1	Rise and Fall Time 10% to 90%	2V Output Step		10	15	ns		
ts	Settling Time to 0.1%	2V Output Step		15		ns		
OS	Overshoot	2V Output Step		5		%		
US	Undershoot	2V Output Step		2		%		
SR	Slew Rate	V <sub>OUT</sub> = ±2.0V	200	250		V/μs		
Distorti	on		•					
HD <sub>2</sub>	2nd Harmonic Dist. @ 20 MHz	Vout = 0.8 Vpp		-48		dB		
HD <sub>3</sub>	3nd Harmonic Dist. @ 20 MHz	VOUT = 0.8 Vpp		-56		dB		
Video P	erformance		•					
DG	Diff. Gain (p-p), NTSC & PAL	$R_L = 150\Omega$ , $V_{OUT} = \pm 1.5V$		0.06		%		
DP	Diff. Phase (p-p), NTSC & PAL	$R_L = 150\Omega$ , $V_{OUT} = \pm 1.5V$		0.06		Deg.		
NF	Noise Floor	>100kHz		-130		dB rms		

3

<sup>1.</sup> Guaranteed by design.

#### **Test Circuit**



# **Applications Discussion**

#### **Capacitive Load**

The RC6334 can drive a capacitive load from 10 to over 50 pF. In back terminated video applications, bandwidth will only be limited by the RC time constants of the external output components. When driving a  $75\Omega$  cable, place the  $75\Omega$  source termination resistor as close to the amplifier output as possible.

#### **DC** Accuracy

Since the RC6334 is a voltage-feedback amplifier, the inverting and non-inverting inputs have similar impedances and bias currents. To minimize offset voltage, match the source resistances seen by inverting and non-inverting inputs.

### **Feedback Components**

Because the RC6334 is a voltage-feedback amplifier, it facilitates using reactive (capacitive and inductive) feedback components for implementing filters, integrators, sample/hold circuits, etc. The feedback network and the parasitic capacitance at the inverting (summing junction) input create a pole and affect the transfer function of the circuit. For stable operation, minimize the parasitic capacitance and equivalent resistance of the components used in the feedback circuit.

#### **Circuit Board**

High-frequency applications require good grounding, power supply decoupling, low parasitic capacitance and inductance, and good isolation between the inputs to minimize their crosstalk. Avoid coupling from output to input to prevent positive feedback.

RC6334 PRODUCT SPECIFICATION

### **Notes:**

### **Notes:**


RC6334 PRODUCT SPECIFICATION


# **Mechanical Dimensions – 14 Pin SOIC Package**


Symbol	Inches		Millim	Notes	
	Min.	Max.	Min.	Max.	notes
Α	.053	.069	1.35	1.75	
A1	.004	.010	0.10	0.25	
В	.013	.020	0.33	0.51	
С	.008	.010	0.19	0.19 0.25	
D	.336	.345	8.54	8.76	2
Е	.150	.158	3.81	4.01	2
е	.050	BSC	1.27	BSC	
Н	.228	.244	5.79	6.20	
h	.010	.020	0.25	0.50	
L	.016	.050	0.40	1.27	3
N	14		1	4	6
α	0°	8°	0°	8°	
ccc	_	.004	<b>—</b> 0.10		

#### Notes:

- 1. Dimensioning and tolerancing per ANSI Y14.5M-1982.
- 2. "D" and "E" do not include mold flash. Mold flash or protrusions shall not exceed .010 inch (0.25mm).
- 3. "L" is the length of terminal for soldering to a substrate.
- 4. Terminal numbers are shown for reference only.
- 5. "C" dimension does not include solder finish thickness.
- 6. Symbol "N" is the maximum number of terminals.







# **Ordering Information**

Product Number Temperature Range		Screening	Package	Package Marking
RC6334M	0° to 70°C	Commercial	14 Pin Narrow SOIC	RC6334M

#### LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

- Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
- A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

www.fairchildsemi.com

