

# MC74AC86, MC74ACT86

## Quad 2-Input Exclusive-OR Gate

- Outputs Source/Sink 24 mA





Figure 1. Pinout: 14-Lead Packages Conductors  
(Top View)




ON Semiconductor®


<http://onsemi.com>



PDIP-14  
N SUFFIX  
CASE 646



SO-14  
D SUFFIX  
CASE 751A



TSSOP-14  
DT SUFFIX  
CASE 948G



EIAJ-14  
M SUFFIX  
CASE 965

### MAXIMUM RATINGS\*

Rating	Symbol	Value	Unit
DC Supply Voltage (Referenced to GND)	V <sub>CC</sub>	-0.5 to +7.0	V
DC Input Voltage (Referenced to GND)	V <sub>in</sub>	-0.5 to V <sub>CC</sub> +0.5	V
DC Output Voltage (Referenced to GND)	V <sub>out</sub>	-0.5 to V <sub>CC</sub> +0.5	V
DC Input Current, per Pin	I <sub>in</sub>	±20	mA
DC Output Sink/Source Current, per Pin	I <sub>out</sub>	±50	mA
DC V <sub>CC</sub> or GND Current per Output Pin	I <sub>CC</sub>	±50	mA
Storage Temperature	T <sub>stg</sub>	-65 to +150	°C

\*Maximum Ratings are those values beyond which damage to the device may occur. Functional operation should be restricted to the Recommended Operating Conditions.

### ORDERING INFORMATION

Device	Package	Shipping
MC74AC86N	PDIP-14	25 Units/Rail
MC74ACT86N	PDIP-14	25 Units/Rail
MC74AC86D	SOIC-14	55 Units/Rail
MC74AC86DR2	SOIC-14	2500 Tape & Reel
MC74ACT86D	SOIC-14	55 Units/Rail
MC74ACT86DR2	SOIC-14	2500 Tape & Reel
MC74AC86DT	TSSOP-14	96 Units/Rail
MC74AC86DTR2	TSSOP-14	2500 Tape & Reel
MC74ACT86DT	TSSOP-14	96 Units/Rail
MC74ACT86DTR2	TSSOP-14	2500 Tape & Reel
MC74AC86M	EIAJ-14	50 Units/Rail
MC74ACT86M	EIAJ-14	50 Units/Rail
MC74ACT86MEL	EIAJ-14	2000 Tape & Reel

### DEVICE MARKING INFORMATION

See general marking information in the device marking section on page 266 of this data sheet.

# MC74AC86, MC74ACT86

## RECOMMENDED OPERATING CONDITIONS

Symbol	Parameter		Min	Typ	Max	Unit
V <sub>CC</sub>	Supply Voltage	'AC	2.0	5.0	6.0	V
		'ACT	4.5	5.0	5.5	
V <sub>in</sub> , V <sub>out</sub>	DC Input Voltage, Output Voltage (Ref. to GND)		0		V <sub>CC</sub>	V
t <sub>r</sub> , t <sub>f</sub>	Input Rise and Fall Time (Note 1) 'AC Devices except Schmitt Inputs	V <sub>CC</sub> @ 3.0 V	—	150	—	ns/V
		V <sub>CC</sub> @ 4.5 V	—	40	—	
		V <sub>CC</sub> @ 5.5 V	—	25	—	
t <sub>r</sub> , t <sub>f</sub>	Input Rise and Fall Time (Note 2) 'ACT Devices except Schmitt Inputs	V <sub>CC</sub> @ 4.5 V	—	10	—	ns/V
		V <sub>CC</sub> @ 5.5 V	—	8.0	—	
T <sub>J</sub>	Junction Temperature (PDIP)		—	—	140	°C
T <sub>A</sub>	Operating Ambient Temperature Range		-40	25	85	°C
I <sub>OH</sub>	Output Current – High		—	—	-24	mA
I <sub>OL</sub>	Output Current – Low		—	—	24	mA

1. V<sub>in</sub> from 30% to 70% V<sub>CC</sub>; see individual Data Sheets for devices that differ from the typical input rise and fall times.  
 2. V<sub>in</sub> from 0.8 V to 2.0 V; see individual Data Sheets for devices that differ from the typical input rise and fall times.

## DC CHARACTERISTICS

Symbol	Parameter	V <sub>CC</sub> (V)	74AC		Unit	Conditions		
			T <sub>A</sub> = +25°C					
			Typ	Guaranteed Limits				
V <sub>IH</sub>	Minimum High Level Input Voltage	3.0 4.5 5.5	1.5 2.25 2.75	2.1 3.15 3.85	V	V <sub>OUT</sub> = 0.1 V or V <sub>CC</sub> – 0.1 V		
V <sub>IL</sub>	Maximum Low Level Input Voltage	3.0 4.5 5.5	1.5 2.25 2.75	0.9 1.35 1.65	V	V <sub>OUT</sub> = 0.1 V or V <sub>CC</sub> – 0.1 V		
V <sub>OH</sub>	Minimum High Level Output Voltage	3.0 4.5 5.5	2.99 4.49 5.49	2.9 4.4 5.4	V	I <sub>OUT</sub> = -50 μA		
		3.0 4.5 5.5	— — —	2.56 3.86 4.86	V	*V <sub>IN</sub> = V <sub>IL</sub> or V <sub>IH</sub> I <sub>OH</sub> -12 mA -24 mA -24 mA		
V <sub>OL</sub>	Maximum Low Level Output Voltage	3.0 4.5 5.5	0.002 0.001 0.001	0.1 0.1 0.1	V	I <sub>OUT</sub> = 50 μA		
		3.0 4.5 5.5	— — —	0.36 0.36 0.36	V	*V <sub>IN</sub> = V <sub>IL</sub> or V <sub>IH</sub> I <sub>OL</sub> 12 mA 24 mA 24 mA		
I <sub>IN</sub>	Maximum Input Leakage Current	5.5	—	±0.1	μA	V <sub>I</sub> = V <sub>CC</sub> , GND		
I <sub>OLD</sub>	†Minimum Dynamic Output Current	5.5	—	—	mA	V <sub>OLD</sub> = 1.65 V Max		
I <sub>OHD</sub>		5.5	—	—	mA	V <sub>OHD</sub> = 3.85 V Min		
I <sub>CC</sub>	Maximum Quiescent Supply Current	5.5	—	4.0	μA	V <sub>IN</sub> = V <sub>CC</sub> or GND		

\*All outputs loaded; thresholds on input associated with output under test.

†Maximum test duration 2.0 ms, one output loaded at a time.

NOTE: I<sub>IN</sub> and I<sub>CC</sub> @ 3.0 V are guaranteed to be less than or equal to the respective limit @ 5.5 V V<sub>CC</sub>.

# MC74AC86, MC74ACT86

**AC CHARACTERISTICS** (For Figures and Waveforms – See Section 3 of the ON Semiconductor FACT Data Book, DL138/D)

Symbol	Parameter	$V_{CC}^*$ (V)	74AC			74AC		Unit	Fig. No.		
			$T_A = +25^\circ C$			$T_A = -40^\circ C$ to $+85^\circ C$					
			Min	Typ	Max	Min	Max				
$t_{PLH}$	Propagation Delay Inputs to Outputs	3.3 5.0	2.0 1.5	6.0 4.5	11.5 8.5	1.5 1.0	12.5 9.0	ns	3-5		
$t_{PHL}$	Propagation Delay Inputs to Outputs	3.3 5.0	2.0 1.5	6.5 4.5	11.5 8.5	1.5 1.0	12.5 9.5	ns	3-5		

\*Voltage Range 3.3 V is  $3.3 V \pm 0.3 V$ .

Voltage Range 5.0 V is  $5.0 V \pm 0.5 V$ .

## DC CHARACTERISTICS

Symbol	Parameter	$V_{CC}$ (V)	74ACT		74ACT		Unit	Conditions		
			$T_A = +25^\circ C$		$T_A = -40^\circ C$ to $+85^\circ C$					
			Typ	Guaranteed Limits	Typ	Guaranteed Limits				
$V_{IH}$	Minimum High Level Input Voltage	4.5 5.5	1.5 1.5	2.0 2.0	2.0 2.0		V	$V_{OUT} = 0.1 V$ or $V_{CC} - 0.1 V$		
$V_{IL}$	Maximum Low Level Input Voltage	4.5 5.5	1.5 1.5	0.8 0.8	0.8 0.8		V	$V_{OUT} = 0.1 V$ or $V_{CC} - 0.1 V$		
$V_{OH}$	Minimum High Level Output Voltage	4.5 5.5	4.49 5.49	4.4 5.4	4.4 5.4		V	$I_{OUT} = -50 \mu A$		
		4.5 5.5	– –	3.86 4.86	3.76 4.76		V	$*V_{IN} = V_{IL}$ or $V_{IH}$ $I_{OH} = -24 mA$		
$V_{OL}$	Maximum Low Level Output Voltage	4.5 5.5	0.001 0.001	0.1 0.1	0.1 0.1		V	$I_{OUT} = 50 \mu A$		
		4.5 5.5	– –	0.36 0.36	0.44 0.44		V	$*V_{IN} = V_{IL}$ or $V_{IH}$ $I_{OL} = 24 mA$		
$I_{IN}$	Maximum Input Leakage Current	5.5		$\pm 0.1$	$\pm 1.0$		$\mu A$	$V_I = V_{CC}, GND$		
$\Delta I_{CCT}$	Additional Max. $I_{CC}$ /Input	5.5	0.6	–	1.5	mA		$V_I = V_{CC} - 2.1 V$		
$I_{OLD}$	†Minimum Dynamic Output Current	5.5	–	–	75	mA		$V_{OLD} = 1.65 V$ Max		
$I_{OHD}$		5.5	–	–	-75	mA		$V_{OHD} = 3.85 V$ Min		
$I_{CC}$	Maximum Quiescent Supply Current	5.5	–	4.0	40	$\mu A$		$V_{IN} = V_{CC}$ or GND		

\*All outputs loaded; thresholds on input associated with output under test.

†Maximum test duration 2.0 ms, one output loaded at a time.

# MC74AC86, MC74ACT86

**AC CHARACTERISTICS** (For Figures and Waveforms – See Section 3 of the ON Semiconductor FACT Data Book, DL138/D)

Symbol	Parameter	$V_{CC}^*$ (V)	74ACT			74ACT		Unit	Fig. No.		
			$T_A = +25^\circ C$ $C_L = 50 \text{ pF}$			$T_A = -40^\circ C$ to $+85^\circ C$ $C_L = 50 \text{ pF}$					
			Min	Typ	Max	Min	Max				
$t_{PLH}$	Propagation Delay	5.0	1.5	8.5	9.5	1.0	10.0	ns	3–5		
$t_{PHL}$	Propagation Delay	5.0	1.5	7.0	9.5	1.0	10.5	ns	3–5		







\*Voltage Range 5.0 V is  $5.0 \text{ V} \pm 0.5 \text{ V}$ .

## CAPACITANCE

Symbol	Parameter	Value Typ	Unit	Test Conditions
$C_{IN}$	Input Capacitance	4.5	pF	$V_{CC} = 5.0 \text{ V}$
$C_{PD}$	Power Dissipation Capacitance	35	pF	$V_{CC} = 5.0 \text{ V}$

# MC74AC86, MC74ACT86

## MARKING DIAGRAMS



A = Assembly Location

WL, L = Wafer Lot

YY, Y = Year

WW, W = Work Week