

Zener Voltage Regulators

300 mW SOD-323 Surface Mount Tight Tolerance Portfolio

MM3ZxxxST1G Series, SZMM3ZxxxST1G Series

This series of Zener diodes is packaged in a SOD-323 surface mount package that has a power dissipation of 300 mW. They are designed to provide voltage regulation protection and are especially attractive in situations where space is at a premium. They are well suited for applications such as cellular phones, hand-held portables, and high density PC boards.

Specification Features

- Standard Zener Breakdown Voltage Range 3.3 V to 36 V
- Steady State Power Rating of 300 mW
- Small Body Outline Dimensions:
 - 0.067" x 0.049" (1.7 mm x 1.25 mm)
- Low Body Height: 0.035" (0.9 mm)
- Package Weight: 4.507 mg/unit
- ESD Rating of Class 3 (> 16 kV) per Human Body Model
- Tight Tolerance V_Z
- SZ Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb–Free, Halogen Free/BFR Free and are RoHS Compliant*

Mechanical Characteristics:

CASE: Void-free, transfer-molded plastic

FINISH: All external surfaces are corrosion resistant

MAXIMUM CASE TEMPERATURE FOR SOLDERING PURPOSES:

260°C for 10 Seconds

LEADS: Plated with Pb–Sn or Sn only (Pb–Free) **POLARITY:** Cathode indicated by polarity band

FLAMMABILITY RATING: UL 94 V-0

MOUNTING POSITION: Any



SOD-323 CASE 477 STYLE 1



MARKING DIAGRAM



XX = Specific Device Code

M = Date Code*

= Pb-Free Package

(Note: Microdot may be in either location)

*Date Code orientation may vary depending upon manufacturing location.

ORDERING INFORMATION

Device	Package	Shipping [†]
MM3ZxxxST1G	SOD-323 (Pb-Free)	3,000 / Tape & Reel
SZMM3ZxxxST1G	SOD-323 (Pb-Free)	3,000 / Tape & Reel
MM3ZxxxST3G	SOD-323 (Pb-Free)	10,000 / Tape & Reel

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

DEVICE MARKING INFORMATION

See specific marking information in the device marking column of the Electrical Characteristics table on page 3 of this data sheet.

MM3ZxxxST1G Series, SZMM3ZxxxST1G Series

MAXIMUM RATINGS

Rating	Symbol	Max	Unit
Total Device Dissipation FR-4 Board, (Note 1) @ T _A = 25°C Derate above 25°C	P _D	300 2.4	mW mW/°C
Thermal Resistance from Junction-to-Ambient	$R_{ heta JA}$	416	°C/W
Junction and Storage Temperature Range	T _J , T _{stg}	-65 to +150	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.


1. FR-4 printed circuit board, single-sided copper, mounting pad 1 cm².

ELECTRICAL CHARACTERISTICS

(T_A = 25°C unless otherwise noted,

 $V_F = 0.9 \text{ V Max.}$ @ $I_F = 10 \text{ mA for all types}$

Symbol	Parameter
VZ	Reverse Zener Voltage @ I _{ZT}
I _{ZT}	Reverse Current
Z _{ZT}	Maximum Zener Impedance @ I _{ZT}
I _{ZK}	Reverse Current
Z _{ZK}	Maximum Zener Impedance @ I _{ZK}
I _R	Reverse Leakage Current @ V _R
V _R	Reverse Voltage
IF	Forward Current
V _F	Forward Voltage @ I _F
ΘVZ	Maximum Temperature Coefficient of V _Z
С	Max. Capacitance @V _R = 0 and f = 1 MHz



MM3ZxxxST1G Series, SZMM3ZxxxST1G Series

ELECTRICAL CHARACTERISTICS ($V_F = 0.9 \text{ Max} @ I_F = 10 \text{ mA}$ for all types)

	Device Marking	Test Current Izt mA	Zener Voltage VZ		Z _{ZK} I _Z = 0.5	Z _{ZT} I _Z = IZT @ 10%	Max IR @ VR		d _{VZ} /dt (mV/k) @ I _{ZT1} = 5 mA		C pF Max @
Device*			Min	Max	mA Ω	Mod Ω Max	μΑ	٧	Min	Max	V _R = 0 f = 1 MHz
MM3Z2V4ST1G	T2	5.0	2.29	2.51	1000	100	50	1.0	-3.5	0	450
MM3Z2V7ST1G	ТЗ	5.0	2.59	2.81	1000	100	20	1.0	-3.5	0	450
MM3Z3V0ST1G	T4	5.0	2.90	3.11	1000	100	10	1.0	-3.5	0	450
MM3Z3V3ST1G	T5	5.0	3.32	3.53	1000	95	5.0	1.0	-3.5	0	450
MM3Z3V6ST1G	T6	5.0	3.49	3.71	1000	90	5.0	1.0	-3.5	0	450
MM3Z3V9ST1G	T7	5.0	3.89	4.16	1000	90	3.0	1.0	-3.5	-2.5	450
MM3Z4V3ST1G	Т8	5.0	4.17	4.43	1000	90	3.0	1.0	-3.5	0	450
MM3Z4V7ST1G	T9	5.0	4.55	4.75	800	80	3.0	2.0	-3.5	0.2	260
MM3Z5V1ST1G	TA	5.0	4.98	5.2	500	60	2.0	2.0	-2.7	1.2	225
MM3Z5V6ST1G	TC	5.0	5.49	5.73	200	40	1.0	2.0	-2.0	2.5	200
MM3Z6V2ST1G	TE	5.0	6.06	6.33	100	10	3.0	4.0	0.4	3.7	185
MM3Z6V8ST1G	TF	5.0	6.65	6.93	160	15	2.0	4.0	1.2	4.5	155
MM3Z7V5ST1G	TG	5.0	7.28	7.6	160	15	1.0	5.0	2.5	5.3	140
MM3Z8V2ST1G	TH	5.0	8.02	8.36	160	15	0.7	5.0	3.2	6.2	135
MM3Z9V1ST1G	TK	5.0	8.85	9.23	160	15	0.5	6.0	3.8	7.0	130
MM3Z10VST1G	WB	5.0	9.80	10.20	160	15	0.5	6.0	4.5	8.0	130
MM3Z11VST1G	WC	5.0	10.78	11.22	160	20	0.1	8.0	5.4	9.0	130
MM3Z12VST1G	TN	5.0	11.74	12.24	80	25	0.1	8.0	6.0	10	130
MM3Z13VST1G	TQ	5.0	12.91	13.49	160	30	0.1	8.0	7.0	11	120
MM3Z15VST1G	TP	5.0	14.34	14.98	80	40	0.1	11	8.8	12.7	130
MM3Z16VST1G	TU	5.0	15.85	16.51	80	40	0.05	11.2	10.4	14	105
MM3Z18VST1G	TW	5.0	17.56	18.35	80	45	0.05	12.6	12.4	16	100
MM3Z20VST1G	U8	5.0	19.48	20.46	100	55	0.05	14.0	14.4	18	85
MM3Z22VST1G	WP	5.0	21.54	22.47	100	55	0.05	15.4	16.4	20	85
MM3Z24VST1G	WT	5.0	23.72	24.78	120	70	0.05	16.8	18.4	22	80
MM3Z27VST1G	WQ	5.0	26.19	27.53	300	80	0.05	18.9	21.4	25.3	70
MM3Z30VST1G	WV	5.0	29.19	30.69	300	80	0.05	21.0	24.4	29.4	70
MM3Z33VST1G	WR	5.0	32.15	33.79	300	80	0.05	23.2	27.4	33.4	70
MM3Z36VST1G	WU	5.0	35.07	36.87	500	90	0.05	25.2	30.4	37.4	70
MM3Z39VST1G	WN	2.0	38.22	39.78	500	130	0.05	27.3	33.4	41.2	45

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

*Include SZ-prefix devices where applicable.

MM3ZxxxST1G Series, SZMM3ZxxxST1G Series

TYPICAL CHARACTERISTICS




Figure 1. Effect of Zener Voltage on Zener Impedance

Figure 2. Typical Forward Voltage




Figure 3. Typical Capacitance

Figure 4. Typical Leakage Current





Figure 5. Zener Voltage versus Zener Current (V_Z Up to 9 V)


Figure 6. Steady State Power Derating




SOD-323 CASE 477-02 **ISSUE H**


DATE 13 MAR 2007

SCALE 4:1





SOLDERING FOOTPRINT*




*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

NOTES:

- VIES:
 1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
 2. CONTROLLING DIMENSION: MILLIMETERS.
- 3. LEAD THICKNESS SPECIFIED PER L/F DRAWING WITH SOLDER PLATING.
- DIMENSIONS A AND B DO NOT INCLUDE MOLD
- FLASH, PROTRUSIONS OR GATE BURRS.
 5. DIMENSION L IS MEASURED FROM END OF RADIUS.

	MIL	LIMETE	ERS	INCHES			
DIN	MIN	NOM	MAX	MIN	NOM	MAX	
Α	0.80	0.90	1.00	0.031	0.035	0.040	
A1	0.00	0.05	0.10	0.000	0.002	0.004	
A3	(0.15 REI	F	0.006 REF			
b	0.25	0.32	0.4	0.010	0.012	0.016	
С	0.089	0.12	0.177	0.003	0.005	0.007	
D	1.60	1.70	1.80	0.062	0.066	0.070	
E	1.15	1.25	1.35	0.045	0.049	0.053	
L	0.08			0.003			
HE	2.30	2.50	2.70	0.090	0.098	0.105	

GENERIC MARKING DIAGRAM*



XX = Specific Device Code M = Date Code

*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot " ■", may or may not be present.

PIN 1. CATHODE (POLARITY BAND) 2. ANODE

NO POLARITY

Electronic versions are uncontrolled except when accessed directly from the Document Repository. **DOCUMENT NUMBER:** 98ASB17533C Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. **DESCRIPTION:** SOD-323 **PAGE 1 OF 1**

ON Semiconductor and (III) are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

onsemi, Onsemi, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. Onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA class 3 medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

 $\textbf{Technical Library:} \ \underline{www.onsemi.com/design/resources/technical-documentation}$

onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at

www.onsemi.com/support/sales